


Specifications

Model Name		4WB55FT5U	4WB65FT5U	4WB75FT5U	4WB86FT5U
LCD Panel	Installation	Landscape			
	LCD component	55" Class (54.6" diagonal) TFT LCD	65" Class (64.5" diagonal) TFT LCD	75" Class (75.0" diagonal) TFT LCD	86" Class (85.6" diagonal) TFT LCD
	Max. Resolution	3,840 x 2,160 pixels			
	Max. colours	Approx. 1.07 billion colours			
	Pixel Pitch (H x V)	0.3148 mm x 0.3148 mm	0.3718 mm x 0.3718 mm	0.4324 mm x 0.4324 mm	0.4935 mm x 0.4935 mm
	Brightness (typical)	270 cd/m ²	300 cd/m ²	350 cd/m ²	
	Contrast ratio (typical)	1,300 : 1	1,300 : 1	1,200 : 1	
	Viewing Angle	178° / 178°			
Active Screen Area (W x H)		43.14" x 24.27"	57.13" x 33.07"	65.91" x 37.91"	75.30" x 42.40"
Computer input signal		VGA, SVGA, XGA, WXGA, SXGA, SXGA+, 1080P, UHD supported			
Sync signal		Horizontal/vertical separate (TTL: positive/negative)			
Plug & Play		VESA DDC2B			
Input Terminals	Video ^{*1}	HDMI x 3, Analog AV (3.5 mm-diameter mini stereo jack) x 1, ANT/Cable x 1, USB x 2			
	Serial (RS-232C) ^{*1}	RS-232C (3.5 mm-diameter mini stereo jack) x 1			
	Audio ^{*1}	Analog AV (3.5 mm-diameter mini stereo jack) x 1			
Output Terminals	Audio	Audio (3.5 mm-diameter mini stereo jack (L/R)) x 1			
USB Port		USB x 2			
LAN Terminal		Ethernet (10/100 BASE-T)			
Wireless LAN		IEEE 802.11b/g/n/ac			
Speakers Output		8W + 8W			
Touch Panel	Detection method	IR (infrared blocking detection method)			
	Computer connector	USB Type C x 1 (a USB cable and a C to A adapter included)			
Power Requirement ^{*2}		AC 120 V, 60 Hz			
Operating temperature ^{*3}		32°F to 104°F (0°C to 40°C)			
Operating humidity		20% to 80% (no condensation)			
Power consumption		130 W	180 W	300 W	380 W
Dimensions (W x D x H) (approx.) (display only)		49.8" x 3.3" x 29.5"	58.4" x 3.3" x 34.4"	67.1" x 3.4" x 39.2"	77.0" x 4.2" x 45.0"
Weight (approx.) (display only)		51.6 lbs (23.4kg)	69.0 lbs (31.3kg)	112.4 lbs (51kg)	150.4 lbs (68.2kg)
Main Accessories		Remote control unit, AAA size battery (x2), Quick Setup Guide, RS-232C conversion cable, USB-C to USB-A conversion adapter, Touch Pen (x2), External IR receiver, USB Flash Drive, Screws for VESA mountings (only for 55 and 65 inch models)			


*1 Use a commercially available connection cable for PC and other video connections. *2 The AC power cord is an inlet type. The cable is bundled (2 pins). *3 Temperature conditions may change when using the monitor together with optional equipment. In such cases, please check the temperature conditions specified by the optional equipment.

Dimensions


4WB55FT5U




4WB65FT5U



4WB75FT5U



4WB86FT5U



Units: inch (mm)

*1. Active area *2. Thinnest part *3. Including projecting parts



SHARP
Be Original.

SHARP ELECTRONICS OF CANADA LTD.
335 Britannia Road East, Ste. 101
Mississauga, Ontario L4Z 1W9
1-800-567-4277 • www.sharp.ca

Printed in Canada.
VSG-VS-4WB-E-PDF-04/2023

Sharp is a registered trademark of Sharp Corporation. The terms HDMI, High-Definition Multimedia Interface and the HDMI logo are trademarks or registered trademarks of HDMI Licensing Administrator, Inc. Manufactured under license from Dolby Laboratories. Dolby and the double-D symbol are trademarks of Dolby Laboratories. All other brand names and product names may be trademarks or registered trademarks of their respective owners. All screen images appearing in this brochure are simulated. Design and specifications are subject to change without prior notice.