

HDMI™ Cables

Selection Guide



PERFORMANCE SERIES

Premium Reliability.



PLUS SERIES

Pro Essentials.



CORE SERIES

Everyday Basics.



Untangle Cable Confusion

With An Organized Buying Experience from C2G HDMI™ Cables.

Streamline your connectivity solutions with our high-quality line of HDMI™ cables meticulously organized for you. Our thoughtfully curated product offering ensures quick and hassle-free selection, saving you valuable time. Experience superior convenience and efficiency in your buying process, as we prioritize ease of access and top-notch performance in every cable we deliver.




New Series Easy as 1-2-3

We've reorganized our HDMI™ cable lines into three series (**Performance**, **Plus** and **Core**) to make it easier for you to find the cable you need. Visit our website at www.legrandav.com/c2g to explore the full range of C2G HDMI cables and find the perfect solution for your needs.



PERFORMANCE SERIES

Premium Reliability.



Your go-to for certified cables, active copper cables, and active optical cables. When failure is not an option, count on C2G Performance Series HDMI Cables for total reliability.



PLUS SERIES

Pro Essentials.



Your go-to for basic in-wall cables, plenum cables, and slim cables. A broad selection of cables for a variety of applications – at the right price.



CORE SERIES

Everyday Basics.



This is your go-to for basic 4K HDMI cable - offering reliable connectivity at the most affordable price. C2G's Core Series provides you with reliable cables for office or commercial use.



PERFORMANCE SERIES

Premium Reliability.

Your go-to for certified cables, active copper cables, and active optical cables. When failure is not an option, count on C2G Performance Series for total reliability

C2G Performance Series HDMI™ Cables are 100% tested for verified performance and designed to meet the needs of commercial AV applications, from computers to projectors and monitors, AV presentation furniture, or in-wall applications. C2G'S Performance Series includes HDMI-certified cables, highly flexible cables for tight spaces, ultra high-speed cables for 8K resolutions, and active optical HDMI cables for extended lengths needs.

- **100% Tested** – All Performance Series HDMI cables are tested at the production line to ensure they meet our standards—providing the peace of mind they will perform as expected.
- **Commercial Grade Connectors** – Compact overmolding with integrated finger grips on all sides makes these cables easy to insert and remove in limited access spaces and high-density environments. Additionally, the gripping connector shell provides two times the port retention of a standard connector, reducing the chances of an accidental disconnect.



- **Gold-plated connectors** for increased electrical conductivity and enhanced durability.
- **Lifetime Warranty** – C2G Performance Series Cables are backed by a lifetime warranty* for extra peace of mind.

PERFORMANCE SERIES Certified Premium High Speed HDMI Cable – 4K 60Hz, CMG (FT4). For applications requiring HDMI certification.

- Rigorously tested for HDMI certification, this premium line provides the highest level of guarantee, making it the preferred choice for mission-critical applications



Item #	Length	Certification	Signal Type	Connector	Active/Passive	Maximum Bandwidth	Maximum Resolution	Maximum Refresh Rate	Cable Diameter (in)	Minimum Bend Radius (in)	Jacket Rating
50181	3ft (0.9m)	Premium	HDMI 2.0	Gripping	Passive	18 Gbps	4K	60Hz	6mm	70mm	CMG, CL2/FT4
50182	6ft (1.8m)	Premium	HDMI 2.0	Gripping	Passive	18 Gbps	4K	60Hz	6mm	70mm	CMG, CL2/FT4
50184	10ft (3m)	Premium	HDMI 2.0	Gripping	Passive	18 Gbps	4K	60Hz	6mm	70mm	CMG, CL2/FT4
50185	12ft (3.7m)	Premium	HDMI 2.0	Gripping	Passive	18 Gbps	4K	60Hz	6mm	70mm	CMG, CL2/FT4
50186	15ft (4.6m)	Premium	HDMI 2.0	Gripping	Passive	18 Gbps	4K	60Hz	6.5mm	75mm	CMG, CL2/FT4
50188	20ft (6.1m)	Premium	HDMI 2.0	Gripping	Passive	18 Gbps	4K	60Hz	9.5mm	90mm	CMG, CL2/FT4
C2G50196	25ft (7.6m)	Premium	HDMI 2.0	Gripping	Passive	18 Gbps	4K	60Hz	9.0mm	90mm	CMG, CL2/FT4

*Performance Series HDMI Active Optical HDMI Cable and Performance Series Ultra Flexible Active Cable offer a 5-Year Warranty.





PERFORMANCE SERIES Ultra Flexible High Speed HDMI Cable - 4K 60Hz In-Wall, CMG (FT4) Rated. Your go-to 4K cable for tight spaces.

- The ¼ inch (6.5 mm) minimum bend radius makes these cables perfect for installations in any tight space
- For connecting a variety of devices from computers and projectors and monitors, in-wall or short connections on a conference room table or lectern

Item #	Length	Certification	Signal Type	Connector	Active/Passive	Maximum Bandwidth	Maximum Resolution	Maximum Refresh Rate	Cable Diameter (in)	Minimum Bend Radius (in)	Jacket Rating
C2G10373	1ft (0.3m)	No	HDMI 2.0	Gripping	Passive	18 Gbps	4K	60Hz	6mm	48mm	CMG FT4
C2G10374	1.5ft (0.5m)	No	HDMI 2.0	Gripping	Passive	18 Gbps	4K	60Hz	6mm	48mm	CMG FT4
C2G10375	2ft (0.6m)	No	HDMI 2.0	Gripping	Passive	18 Gbps	4K	60Hz	6mm	48mm	CMG FT4
C2G10376	3ft (0.9m)	No	HDMI 2.0	Gripping	Passive	18 Gbps	4K	60Hz	6mm	48mm	CMG FT4
C2G10377	6ft (1.8m)	No	HDMI 2.0	Gripping	Passive	18 Gbps	4K	60Hz	6mm	48mm	CMG FT4
C2G10378	10ft (3m)	No	HDMI 2.0	Gripping	Passive	18 Gbps	4K	60Hz	6mm	48mm	CMG FT4
C2G10379	12ft (3.7m)	No	HDMI 2.0	Gripping	Active	18 Gbps	4K	60Hz	6mm	48mm	CMG FT4
C2G10380	15ft (4.6m)	No	HDMI 2.0	Gripping	Active	18 Gbps	4K	60Hz	6mm	48mm	CMG FT4
C2G10381	20ft (6.1m)	No	HDMI 2.0	Gripping	Active	18 Gbps	4K	60Hz	6mm	48mm	CMG FT4
C2G10382	25ft (7.6m)	No	HDMI 2.0	Gripping	Active	18 Gbps	4K	60Hz	6mm	48mm	CMG FT4
C2G10383	35ft (10.7m)	No	HDMI 2.0	Gripping	Active	18 Gbps	4K	60Hz	9.5mm	76mm	CMG FT4
C2G10384	50ft (15.2m)	No	HDMI 2.0	Gripping	Active	18 Gbps	4K	60Hz	9.5mm	76mm	CMG FT4



PERFORMANCE SERIES Certified Ultra High Speed HDMI Cable - 8K 60Hz. When quality matters, choose our best 8K cable.

- Ideal for computers and displays requiring high bandwidth solutions and video resolutions up to 8K
- Perfect for high-resolution applications in video production, broadcasting and other business and applications

Item #	Length	Certification	Signal Type	Connector	Active/Passive	Maximum Bandwidth	Maximum Resolution	Maximum Refresh Rate	Cable Diameter (in)	Minimum Bend Radius (in)	Jacket Rating
C2G10452	2ft (0.6m)	Ultra	HDMI 2.1	Gripping	Passive	48 Gbps	8K	60Hz	6mm	48mm	CMG FT4
C2G10453	3ft (0.9m)	Ultra	HDMI 2.1	Gripping	Passive	48 Gbps	8K	60Hz	6mm	48mm	CMG FT4
C2G10454	6ft (1.8m)	Ultra	HDMI 2.1	Gripping	Passive	48 Gbps	8K	60Hz	6mm	48mm	CMG FT4
C2G10455	10ft (3m)	Ultra	HDMI 2.1	Gripping	Passive	48 Gbps	8K	60Hz	6mm	48mm	CMG FT4
C2G10456	12ft (3.7m)	Ultra	HDMI 2.1	Gripping	Passive	48 Gbps	8K	60Hz	8mm	64mm	CMG FT4



PERFORMANCE SERIES High Speed HDMI Active Optical Cable (AOC) - 4K 60Hz Plenum Rated. For extended length needs.

- Choose active optical HDMI cables when you need to reach up to 300 feet, without sacrificing signal strength or image quality
- Ideal for extending HDMI signals in classrooms, meeting spaces, and other commercial applications requiring high speed HDMI features and video resolutions

Item #	Length	Certification	Signal Type	Connector	Active/Passive	Maximum Bandwidth	Maximum Resolution	Maximum Refresh Rate	Cable Diameter (in)	Minimum Bend Radius (in)	Jacket Rating
C2G41480	15ft (4.6m)	No	HDMI 2.0	Gripping	Active Optical	18 Gbps	4K	60Hz	4.8mm	70mm	CMP
C2G41481	20ft (6.1m)	No	HDMI 2.0	Gripping	Active Optical	18 Gbps	4K	60Hz	4.8mm	70mm	CMP
C2G41482	25ft (7.6m)	No	HDMI 2.0	Gripping	Active Optical	18 Gbps	4K	60Hz	4.8mm	70mm	CMP
C2G41483	35ft (10.7m)	No	HDMI 2.0	Gripping	Active Optical	18 Gbps	4K	60Hz	4.8mm	70mm	CMP
C2G41484	50ft (15.2m)	No	HDMI 2.0	Gripping	Active Optical	18 Gbps	4K	60Hz	4.8mm	70mm	CMP
C2G41485	75ft (22.8m)	No	HDMI 2.0	Gripping	Active Optical	18 Gbps	4K	60Hz	4.8mm	70mm	CMP
C2G41486	100ft (30.5m)	No	HDMI 2.0	Gripping	Active Optical	18 Gbps	4K	60Hz	5.5mm	75mm	CMP
C2G41487	125ft (38.1m)	No	HDMI 2.0	Gripping	Active Optical	18 Gbps	4K	60Hz	5.5mm	75mm	CMP
C2G41488	150ft (45.7m)	No	HDMI 2.0	Gripping	Active Optical	18 Gbps	4K	60Hz	5.5mm	75mm	CMP
C2G41489	200ft (61m)	No	HDMI 2.0	Gripping	Active Optical	18 Gbps	4K	60Hz	5.5mm	75mm	CMP
C2G41490	250ft (76.2m)	No	HDMI 2.0	Gripping	Active Optical	18 Gbps	4K	60Hz	5.5mm	75mm	CMP
C2G41491	300ft (91.4m)	No	HDMI 2.0	Gripping	Active Optical	18 Gbps	4K	60Hz	5.5mm	75mm	CMP



PLUS SERIES

Pro Essentials.



Whether you need HDMI™ cable for tight spaces or installations with plenum requirements, C2G's Plus Series offers a broad selection of HDMI cables for a variety of applications – at the right price. The Plus Series includes in-wall rated high speed and ultra high-speed cables, as well as CL2P and CMP cables for plenum applications, and slim flexible for confined spaces.

PLUS SERIES TAA-Compliant Certified Premium High Speed HDMI Cable with Ethernet - 4K 60Hz. For high bandwidth, high-resolution applications.

- Approved for use in United States government projects and facilities



Item #	Length	Certification	Signal Type	Connector	Active/Passive	Maximum Bandwidth	Maximum Resolution	Maximum Refresh Rate	Cable Diameter (in)	Minimum Bend Radius (in)	Jacket Rating
C2G50109	3ft (0.9m)	Premium	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	5.8mm	48mm	VW-1
C2G50110	6ft (1.8m)	Premium	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	5.8mm	48mm	VW-1
C2G50111	10ft (3m)	Premium	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	5.8mm	48mm	VW-1

PLUS SERIES Select HDMI Cable with Ethernet - In-Wall CL2-Rated. Standard in-wall passive cables, available in longer lengths.

- For connecting multimedia source devices in desktop or commercial audio video applications



Item #	Length	Certification	Signal Type	Connector	Active/Passive	Maximum Bandwidth	Maximum Resolution	Maximum Refresh Rate	Cable Diameter (in)	Minimum Bend Radius (in)	Jacket Rating
50624	1.5ft (0.46m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	7.3mm	51mm	CL2
50625	3ft (0.9m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	7.3mm	51mm	CL2
50626	5ft (1.5m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	7.3mm	51mm	CL2
50627	6ft (1.8m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	7.3mm	51mm	CL2
50628	10ft (3m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	7.3mm	51mm	CL2
50629	12ft (3.7m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	7.3mm	51mm	CL2
50630	15ft (4.6m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	8.8mm	88mm	CL2
50631	16.5ft (5m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	8.8mm	88mm	CL2
50632	20ft (6.1m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	8.8mm	88mm	CL2
50633	25ft (7.6m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	10mm	70mm	CL2
50634	35ft (10.7m)	No	HDMI 1.4	Standard	Passive	4.95 Gbps	1080p	60Hz	10mm	70mm	CL2
50635	40ft (12.2m)	No	HDMI 1.2	Standard	Passive	4.95 Gbps	1080p	60Hz	10mm	70mm	CL2
50636	50ft (15.2m)	No	HDMI 1.2	Standard	Passive	4.95 Gbps	1080p	60Hz	10mm	70mm	CL2

PLUS SERIES Certified Ultra High Speed HDMI Cable with Ethernet - 8K 60Hz. For high bandwidth, high-resolution applications.

- Ideal for high-resolution applications in video production, broadcasting and other business applications



Item #	Length	Certification	Signal Type	Connector	Active/Passive	Maximum Bandwidth	Maximum Resolution	Maximum Refresh Rate	Cable Diameter (in)	Minimum Bend Radius (in)	Jacket Rating
C2G10410	3ft (0.9m)	Ultra	HDMI 2.1	Standard	Passive	48 Gbps	8K	60Hz	6mm	60mm	CL2
C2G10411	6ft (1.8m)	Ultra	HDMI 2.1	Standard	Passive	48 Gbps	8K	60Hz	6mm	60mm	CL2
C2G10412	10ft (3m)	Ultra	HDMI 2.1	Standard	Passive	48 Gbps	8K	60Hz	6mm	60mm	CL2
C2G10413	12ft (3.7m)	Ultra	HDMI 2.1	Standard	Passive	48 Gbps	8K	60Hz	8mm	80mm	CL2



PLUS SERIES Slim Flexible HDMI Cable with Low Profile Connectors. Super slim and highly flexible for tight spaces.

- Space-saving design: low profile connector and slim cable easily fits behind flat panel displays or equipment racks
- Available in 2-packs (C2G21006 & C2G21007) and 3-packs (C2G21008 & C2G21009)



Item #	Length	Certification	Signal Type	Connector	Active/Passive	Maximum Bandwidth	Maximum Resolution	Maximum Refresh Rate	Cable Diameter (in)	Minimum Bend Radius (in)	Jacket Rating
41361	1ft (0.3m)	No	HDMI 2.0	Low Profile	Passive	18 Gbps	4K	60Hz	3.6mm	25.4mm	VW-1
41362	2ft (0.6m)	No	HDMI 2.0	Low Profile	Passive	18 Gbps	4K	60Hz	3.6mm	25.4mm	VW-1
41363	3ft (0.9m)	No	HDMI 2.0	Low Profile	Passive	18 Gbps	4K	60Hz	3.6mm	25.4mm	VW-1
41364	6ft (1.8m)	No	HDMI 2.0	Low Profile	Passive	18 Gbps	4K	60Hz	3.6mm	25.4mm	VW-1
C2G41398	10ft (3m)	No	HDMI 1.4	Low Profile	Passive	10.2 Gbps	1080p	60Hz	3.6mm	25.4mm	VW-1
C2G21006	3ft (0.9m)	No	HDMI 2.0	Low Profile	Passive	18 Gbps	4K	60Hz	3.6mm	25.4mm	VW-1
C2G21008	3ft (0.9m)	No	HDMI 2.0	Low Profile	Passive	18 Gbps	4K	60Hz	3.6mm	25.4mm	VW-1
C2G21009	6ft (1.8m)	No	HDMI 2.0	Low Profile	Passive	18 Gbps	4K	60Hz	3.6mm	25.4mm	VW-1
C2G21007	6ft (1.8m)	No	HDMI 2.0	Low Profile	Passive	18 Gbps	4K	60Hz	3.6mm	25.4mm	VW-1

PLUS SERIES Standard Speed CMP HDMI Cable For plenum applications needing CMP.

- For plenum space above dropped ceilings or under raised floors in schools, hospitals and other commercial buildings



Item #	Length	Certification	Signal Type	Connector	Active/Passive	Maximum Bandwidth	Maximum Resolution	Maximum Refresh Rate	Cable Diameter (in)	Minimum Bend Radius (in)	Jacket Rating
41190	15ft (4.6m)	No	HDMI 1.2	Standard	Passive	4.95 Gbps	1080p	60Hz	8.4mm	125.73mm	CMP
41191	25ft (7.6m)	No	HDMI 1.2	Standard	Passive	4.95 Gbps	1080p	60Hz	8.4mm	125.73mm	CMP
41192	35ft (10.7m)	No	HDMI 1.2	Standard	Passive	4.95 Gbps	1080p	60Hz	8.4mm	125.73mm	CMP
41193	50ft (15.2m)	No	HDMI 1.2	Standard	Passive	4.95 Gbps	1080p	60Hz	8.4mm	125.73mm	CMP

PLUS SERIES Standard Speed CL2P HDMI Cable With Gripping Connectors. For CL2P plenum installations.

- For plenum space above dropped ceilings or under raised floors in schools, hospitals and other commercial buildings




Item #	Length	Certification	Signal Type	Connector	Active/Passive	Maximum Bandwidth	Maximum Resolution	Maximum Refresh Rate	Cable Diameter (in)	Minimum Bend Radius (in)	Jacket Rating
42528	15ft (4.6m)	No	HDMI 1.4	Gripping	Passive	4.95 Gbps	1080p	60Hz	9mm	135mm	CL2P
42529	25ft (7.6m)	No	HDMI 1.4	Gripping	Passive	4.95 Gbps	1080p	60Hz	9mm	135mm	CL2P
42530	35ft (10.7m)	No	HDMI 1.4	Gripping	Passive	4.95 Gbps	1080p	60Hz	9mm	135mm	CL2P
42531	40ft (12.2m)	No	HDMI 1.4	Gripping	Passive	4.95 Gbps	1080p	60Hz	9mm	135mm	CL2P
42532	50ft (15.2m)	No	HDMI 1.4	Gripping	Passive	4.95 Gbps	1080p	60Hz	9mm	135mm	CL2P

PLUS SERIES Active High Speed HDMI Cable - In-Wall CL3 Rated. For resolutions up to 4K.

- Choose active HDMI cable for distances of 15 feet or more to ensure outstanding picture and sound quality



Item #	Length	Certification	Signal Type	Connector	Active/Passive	Maximum Bandwidth	Maximum Resolution	Maximum Refresh Rate	Cable Diameter (in)	Minimum Bend Radius (in)	Jacket Rating
41412	15ft (4.6m)	No	HDMI 2.0	Standard	Active	18 Gbps	4K	60Hz	5.1mm	51mm	CL3
41413	25ft (7.6m)	No	HDMI 2.0	Standard	Active	18 Gbps	4K	60Hz	6.0mm	60mm	CL3
41414	35ft (10.7m)	No	HDMI 2.0	Standard	Active	18 Gbps	4K	60Hz	8.5mm	85mm	CL3
41415	50ft (15.2m)	No	HDMI 2.0	Standard	Active	18 Gbps	4K	60Hz	8.5mm	85mm	CL3
41368	75ft (22.8m)	No	HDMI 1.4	Standard	Active	10.2 Gbps	4K	30Hz	8.5mm	85mm	CL3
41369	100ft (30.5m)	No	HDMI 1.4	Standard	Active	10.2 Gbps	4K	30Hz	8.5mm	85mm	CL3



CORE SERIES

Everyday Basics.

Your go-to for basic 4K HDMI™ cable. C2G's Core Series provides you with reliable cables for office or commercial use.

- Standard jacket rating, standard connector
- Gold-plated connectors for increased electrical conductivity and enhanced durability
- Good flexibility
- Available in one, two and three-packs in 3 ft, 6 ft and 10 ft lengths (0.9m, 1.8m, 3m)
- Backed by a lifetime warranty for peace of mind

CORE SERIES High Speed HDMI Cables. For reliable connectivity at the most affordable price.

- For connecting computers, projectors and other HDMI devices to monitors and displays
- Available in 2-packs (C2G21000, C2G21001, C2G21002) and 3-packs (C2G21003, C2G21004, C2G21005)



Item #	Length	Certification	Signal Type	Connector	Active/Passive	Maximum Bandwidth	Maximum Resolution	Maximum Refresh Rate	Cable Diameter (in)	Minimum Bend Radius (in)	Jacket Rating
56781	1ft (0.3m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	6mm	42mm	VW-1
50606	1.5ft (0.5m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	6mm	42mm	VW-1
50607	2ft (0.6m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	6mm	42mm	VW-1
56782	3ft (0.9m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	6mm	42mm	VW-1
50608	4ft (1.2m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	6mm	42mm	VW-1
50609	5ft (1.5m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	6mm	42mm	VW-1
56783	6ft (1.8m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	6mm	42mm	VW-1
50610	8ft (2.4m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	6mm	42mm	VW-1
56784	10ft (3m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	6mm	42mm	VW-1
50611	12ft (3.7m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	7.3mm	51mm	VW-1
50612	15ft (4.6m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	7.3mm	51mm	VW-1
C2G21000	3ft (0.9m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	6mm	42mm	VW-1
C2G21001	6ft (1.8m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	6mm	42mm	VW-1
C2G21002	10ft (3m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	6mm	42mm	VW-1
C2G21003	3ft (0.9m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	6mm	42mm	VW-1
C2G21004	6ft (1.8m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	6mm	42mm	VW-1
C2G21005	10ft (3m)	No	HDMI 2.0	Standard	Passive	18 Gbps	4K	60Hz	6mm	42mm	VW-1

