



DATA SHEET

Flexible High Speed HDMI[®] Cable with Low Profile Connectors - 4K 60Hz

Connect an HDMI device to a display and support the latest HDMI audio and video features including 4K Ultra HD

OVERVIEW

The Flexible High Speed HDMI Cable with Low Profile Connectors - 4K 60Hz is perfect for connecting a wide variety of devices from computers to projectors and monitors, home entertainment systems to HDTVs and gaming systems, or any audio video applications requiring high speed HDMI features and video resolutions up to 4k (4096 x 2160) at 60Hz.

This Flexible High Speed HDMI Cable was designed for installations in tight spaces and offers many features like 3D video, deep color, Dolby[R] True HD, DTS-HD Master Audio, and up to 32 audio channels for a multi-dimensional immersive audio experience. Simultaneously deliver dual video streams to multiple users on the same screen, while also delivering multi-stream audio up to four users, giving a dynamic synchronization of video and audio streams. All these features will catch the attention of the audience, providing a more realistic video experience.

This Flexible High Speed HDMI Cable supports the updated library of Consumer Electronic Control (CEC) commands, allowing communication between devices connected through the HDMI ports. The Ethernet capabilities of the cable allow for Ethernet-enabled HDMI devices to access interactive online content or update device firmware. The gold plated connectors on the cable allow for better shielding, increased electrical conductivity, and durability. Lastly, this fully-functional, high bandwidth cable has been tested to perform at industry standards and is backed by a lifetime warranty.

FEATURES

- Supports all HDMI 2.0 features including resolutions up to 4K (4096 x 2160) at 60hz, which means higher quality video for viewing your screen content
- Flexible cable construction and low profile connectors, designed for installations in tight spaces
- Supports 3D video for a more appealing and realistic video experience
- Supports 32 audio channels for an immersive audio experience
- Supports CEC extensions for control of consumer electronics devices through a single control point
- Gold plated connectors for increased electrical conductivity and enhanced durability
- Backed by a Lifetime Warranty for peace of mind

ITEM

DESCRIPTION

CG41361	1ft (0.3m) Ultra Flexible High Speed HDMI [®] Cable with Low Profile Connectors - 4K 60Hz
CG41362	2ft (0.6m) Ultra Flexible High Speed HDMI [®] Cable with Low Profile Connectors - 4K 60Hz
CG41363	3ft (0.9m) Ultra Flexible High Speed HDMI [®] Cable with Low Profile Connectors - 4K 60Hz
CG41364	6ft (1.8m) Ultra Flexible High Speed HDMI [®] Cable with Low Profile Connectors - 4K 60Hz
C2G21006	3ft (0.9m) Ultra Flexible High Speed HDMI [®] Cable with Low Profile Connectors - 4K 60Hz (2 Pack)
C2G21007	6ft (1.8m) Ultra Flexible High Speed HDMI [®] Cable with Low Profile Connectors - 4K 60Hz (2 Pack)
C2G21008	3ft (0.9m) Ultra Flexible High Speed HDMI [®] Cable with Low Profile Connectors - 4K 60Hz (3 Pack)
C2G21009	6ft (1.8m) Ultra Flexible High Speed HDMI [®] Cable with Low Profile Connectors - 4K 60Hz (3 Pack)

SIGNAL SPECIFICATIONS

- Supports HDMI Resolutions up to 4K 60Hz, 4:4:4, 18Gbps
- Supports Full HD Blu-ray Disc and HD DVD Video
- Supports 3D Video
- 2 Video Streams (Dual View)
- Perceptual Quantizer (PQ HDR OETF (SMPTE ST 2084)
- Hybrid Log-Gamma (HLG) HDR OETF
- Static HDR Metadata (SMPTE ST 2086)
- DVD Audio, Super Audio CD (DSD)
- Dolby® True HD, DTS-HD Master Audio Bitstream Capable
- 4 Audio Streams
- Audio Return Channel (ARC)
- Ethernet Channel: 100 Mbit/s
- Consumer Electronic Control (CEC), with updated list of CEC Commands

ELECTRICAL SPECIFICATIONS


- Voltage Rating: 30V
- Temp Rating: 80°C
- Conductor Resistance: at 20°C Max 36AWG:1598 OHM/km
- Insulation Resistance: 10M[OHM]/km Min at 20°C DC 500V
- Spark Test: AC1500V/In the Air
- Dielectric Strength: AC500V/1 Minute No Breakdown
- Impedance: Pairs (Differential Mode) 100±10 OHM

PHYSICAL SPECIFICATIONS:

- Operating Temperature: -20°C to 80°C
- Storage Temperature: -20°C to 80°C

PHYSICAL CHARACTERISTICS:

- Tensile Strength: Unaged: 1500PSI min; Aged: 70% min
- Elongation: Unaged: 100% min; Aged: 65% min
- Deformation Test: Max 50%
- Cable Jacket Ratings: VW-1
- Shield Type: AL Foil Wrap, Braid: 16*5/0.06mm
- Minimum Bend Radius: R25.4MM
- Connector: P1 & P2: HDMI 19 Pin Male: Solder Type, Contacts: Brass, Gold Flash, Housing: LCP, Black, Shell: Gold Plating
- All Hood: Molded Black (Pantone/#Black 6C) PVC
- Product is CE Marked and Conforms to 2011/65/EU ROHS 2



LEGRAND | AV COMMERCIAL BRANDS
C2G | Chief | Da-Lite | Luxul | Middle Atlantic | Vaddio | Wiremom

SIMPLIFIED CONNECTIVITY

USA 800.506.9607 | c2g.com | legrandav.com | customer-service@c2g.com

EMEA +31 495 580 840 | c2g.com/uk | legrandav.com | c2g.emea@av.legrand.com

©2023 Legrand AV Inc. 230136 Rev A 3/23 C2G is a registered trademark of Legrand AV Inc. All other brand names or marks are used for identification purposes and are trademarks of their respective owners. All patents are protected under existing designations. Other patents pending.