

# Lenovo 13w Yoga Gen 2

With a 360° any-position hinge, this versatile device is everything you need for your busy on-the-go lifestyle. It's compact, elegant and packs a 13.3" OGM multi-touch screen display to present wider range of colors and improved contrast in visuals. The AMD Ryzen processors and AMD Radeon Graphics offer faster and more responsive computing performance, and lets you multitask on graphics-intensive tasks such as video editing or gaming. Supporting Rapid Charge, it lasts up to 14.8 hours a day.



With optimized Dolby Audio stereo speakers and HD Realtek audio chip, seamlessly collaborate with friends and family. The device onboards a FHD 1080p front camera with a privacy shutter and a 5.0MP rear camera with autofocus to capture the best side of you.

The Realtek Wi-Fi 6 feature provides access to ultrafast internet connectivity at all times. The dual USB-C 3.2 Gen 1 ports enable data transfer, power delivery and connectivity to surrounding devices and peripherals.


Minimal preloaded applications mean maximum battery life and responsiveness for users, and faster deployment for IT admins.

## Lenovo devices that are a class apart

Lenovo Tab Series is designed for mobile and frontline workers who need a lightweight tablet for basic productivity tasks.

## Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



### Return To Depot Repair Warranty

No-hassle repair process at a Lenovo service center  
 Lenovo pays for all shipping between the customer and service facility

Avoid unplanned operational expense with a simple annual fee

## Accessories

### Lenovo Eco Pro 15.6" Backpack

Eco-friendly design – contains over 83% recycled material  
 The equivalent of 34 plastic water bottles are turned into soft polyester to make each backpack  
 Convenient large storage area and quick access accessory pockets



PN: 4X40Z32891

### Lenovo Go Wireless Vertical Mouse

6-button mouse including 2 programmable side buttons and an IR sensor  
 True Ergonomic vertical design with a 45-degree vertical grip made from treated cork material  
 800, 1600, 2400 adjustable DPI and 2.4 GHz wireless dongle connection



PN: 4Y51C33792

# Lenovo 13w Yoga Gen 2

## Key Specifications

### Processor

AMD Ryzen 3 / 5 / 7

### Operating System

Windows 11 Pro, Windows 11 Home, Windows 11 DG Windows 10 Pro 64

### Display

13.3" WUXGA (1920x1200) IPS Glossy 16:10  
- 300nits, 45% NTSC, Corning Gorilla Glass, anti-fingerprint, touch

### Touchscreen

13.3" WUXGA (1920x1200) IPS Glossy 16:10- 300nits, 45% NTSC, Corning Gorilla Glass, anti-fingerprint, touch

### Graphics

AMD Radeon Graphics (integrated)

### Memory

Up to 12GB or 16GB DDR4-3200 offering  
1x Soldered + 1x SO-DIMM

### Storage

- Up to 1x 512GB M.2 2242 PCIe NVMe SSD

### Audio

High Definition (HD) Audio  
Stereo speakers, 2W x2, Dolby Audio  
Dual-microphone array or  
Dual-microphone array + single microphone

### Battery†

51Wh (up to 14.8 hr) battery Rapid Charge

### Power Adapter

*One of the following*

65W USB-C (2-pin)

65W USB-C (3-pin)

### Camera

*One of the following*

Front FHD 1080p + IR Hybrid with Privacy Shutter

Front FHD 1080p + IR Hybrid with Privacy Shutter + Rear 5.0MP

Front FHD 1080p with Privacy Shutter

Front FHD 1080p with Privacy Shutter + Rear 5.0MP

### Keyboard

6-row, spill-resistant, multimedia Fn keys

Optional backlight

Mylar surface touchpad

60.5 x 104 mm (2.38 x 4.09 inches)

### Dimensions

305 x 216.8 x 17.6 mm

(12 x 8.54 x 0.69 inches)

### Weight

Around 1.517 kg (3.34 lbs)

## Green Certifications

ENERGY STAR 9.0, ErP Lot 6, EPEAT Gold, TCO Certified 9.0, RoHS compliant

## Connectivity

### I/O Ports

1x USB 3.2 Gen 1, 1x USB 3.2 Gen 1 (Always On), 2x USB-C 3.2 Gen 1 (data, PD 3.0, DP 1.4), 1x HDMI 2.0, 1x Card reader, 1x Headphone / microphone combo jack (3.5mm), 1x Nano-SIM card slot (WWAN support models)\*

### WLAN + Bluetooth

Realtek Wi-Fi 6 RTL8852BE, 11ax 2x2 + BT5.1

### WWAN

Optional

## Security & Privacy

Fingerprint Reader

IR Camera with Windows Hello

- Discrete TPM 2.0, TCG certified
- Kensington Nano Security Slot
- Touch style fingerprint reader on power button
- Camera privacy shutter