

ThinkStation P3 Ultra

Business professionals can level up their work experience and performance with this 3.9-liter mini-tower powered by up to 13th Gen Intel Core i9 Processor. Enhance productivity with optional Wi-Fi 6E that enables faster connection speeds even in densely congested areas while with dual Thunderbolt 4 port, connect displays and share files at high speed. A slew of security features includes a discrete TPM 2.0 chipset, Kensington security slot, and BIOS security that keeps data well-protected.



Configured with up to 4TB of high-speed storage via 2x M.2 SSD modules and up to 128GB DDR5 memory, this device offers extreme portable power and enables users to multitask on compute-intensive workflows.

To view and compare detailed spreadsheets, professionals can connect to up to eight independent displays via an onboard Display Port, Thunderbolt, and discrete graphics.

EPEAT Gold, ENERGY STAR 8.0, TCO Certified 9.0, and ROHS compliant certification makes it an energy-efficient device.

Professional machines for advanced users

ThinkStation P3 Series workstations provide affordable power-computing with a choice of processor technologies, expansion bays and support for multiple storage drives.

Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



On-site Service

If a problem can't be fixed remotely, we will visit your location
Normally next business day service
Agreed appointment times

Accessories

Lenovo Go Wireless Numeric Keypad

21-key numeric keypad with industry-leading scissor switch keys
Minimalist design with ultra slim profile at 13 mm with dedicated productivity keys (Calculator, Tab, Equal, Esc keys)
Rechargeable , up to 3 months use in single charge (may vary based on usage)



PN: 4Y41C33791, GY41C33979

Lenovo Essential Wireless Keyboard & Mouse Combo

Simple design that is comfortable for all day use and tough enough to handle spills
Convenient and easy to use wireless connection
Quality typing experience with quiet key strokes and a full-size number pad



PN: 4X30M39458 - US English

ThinkStation P3 Ultra

Key Specifications

Processor Up to one 13th Gen Intel Core i3 / i5 / i7 / i9
Operating System Windows 11 Pro, Windows 11 HomeWindows 11 Home Single Language, Windows 11 DG Windows 10 Pro 64, Ubuntu Linux, Red Hat Enterprise Linux (certified only)
Max Graphics Supports up to one NVIDIA RTX A5500 Laptop GPU
Memory Up to 128GB, 4 DDR5 SO-DIMM slots
Max Storage Drives Up to 1x 2.5" HDD + 2x M.2 SSD · 2.5" HDD up to 1TB · M.2 SSD up to 4TB each
Storage Types Supported Up to 1x 2.5" HDD + 2x M.2 SSD · 2.5" HDD up to 1TB · M.2 SSD up to 4TB each
Storage Controllers Integrated SATA controller Integrated NVMe controller
Power Supply <i>One of the following</i> 170W 90% Adapter 230W 90% Adapter 300W 90% Adapter
Dimensions 87 x 223 x 202 mm (3.43 x 8.78 x 7.95 inches)
Weight 3.6 kg (7.94 lbs, maximum configuration)

Green Certifications

EPEAT Gold, ENERGY STAR 8.0, TCO Certified 9.0, RoHS compliant

Connectivity

Front I/O 1x USB 3.2 Gen 2, 2x Thunderbolt 4, 1x headphone / microphone combo jack (3.5mm)
Rear I/O 1x Ethernet (GbE RJ-45), 1x Ethernet (2.5GbE RJ-45), 4x USB 3.2 Gen 2, 3x DisplayPort 1.2
Optional Rear Ports <i>One of the following</i> 1x USB-C 3.2 Gen 2x2 2x USB 3.2 Gen 1
WLAN + Bluetooth Intel Wi-Fi 6E AX211, 11ax 2x2 + BT5.1, vPro

Security & Privacy

Chassis Intrusion Switch
Discrete TPM 2.0, TCG certified
Kensington Security Slot, 3 x 7 mm
Chassis intrusion switch

Manageability

Intel vPro Enterprise with Intel AMT 16
Non-vPro