



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States

Power Cord for Select Eaton Universal PDUs - 8600VA 208V Wye 3-Phase, L21-30P Input, 30A, 10 ft. (3.05 m)

MODEL NUMBER: CBL351-10

PDU power cord with 8-pin universal plug connects your EVMAGU23X-3 G3 universal input PDU (UPDU) to a compatible AC outlet.

Features

Detachable Power Cord Supports Universal Input PDU

This detachable 8.6kVA power cord is designed for North American 208V Wye 3-phase use. Its 8-pin universal connector mates with the EVMAGU23X-3 G3 universal input PDU (UPDU) to meet your diverse rack-power needs. The 10-foot (3.05-meter) length allows you convenient flexibility in placing the UPDU with respect to the AC outlet.

Locking Connector Helps Prevent Accidental Disconnection and Expensive Downtime

Having a cable come loose accidentally can mean the loss of power and costly downtime. The L21-30P connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure.

Highlights

- Delivers 8.6kVA 3-phase power to Eaton's EVMAGU23X-3 G3 UPDU
- 10 ft. length allows flexibility in placing PDU in relationship to AC outlet
- Locking L21-30P input maintains secure link to avoid loss of power and costly downtime

System Requirements

Pairs with Eaton's EVMAGU23X-3 G3 universal input PDU (UPDU)

Package Includes

CBL351-10 Power Cord, 8600VA 208V Wye 3-Phase, 10 ft. (3.05 m)

Specifications

OVERVIEW	
UPC Code	786689783839
Device Compatibility	PDU
Country/Region	North America
INPUT	
Input Phase	3-Phase
Maximum Input Amps	30.0
Voltage Compatibility (VAC)	208V 3-Phase Wye
PHYSICAL	
Color	Black
Plug Color	Black
Cable Jacket Color	Black
Connector Color	Black
Power Cord Jacket Type	SJ; SOOW
Cable Outer Diameter (OD)	18mm
Number of Conductors	4
Wire Gauge (AWG)	10



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States

Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (in.)	120
Shipping Dimensions (hwd / in.)	5.00 x 17.00 x 17.00
Shipping Dimensions (hwd / cm)	12.70 x 43.18 x 43.18
Shipping Weight (lbs.)	14.00
Shipping Weight (kg)	6.35
ENVIRONMENTAL	
Operating Temperature Range	32° to 140°F (0° to 60°C)
Storage Temperature Range	32° to 194°F (0° to 90°C)
Operating Temperature	32° to 140°F (0° to 60°C)
Operating Humidity Range	10% TO 90% RH, NON-CONDENSING
Storage Humidity Range	10% TO 90% RH, NON-CONDENSING
CONNECTIONS	
Side A - Connector 1	(1) 8-Pin Souriau UTG; HARDWIRE
Side B - Connector 1	(1) NEMA L21-30P
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	Yes
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	UL Listed; cTUVus; cUL Listed
Product Compliance	CE (Europe); FCC (USA); RoHS; UKCA; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States



Powering Business Worldwide

© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.