

OVERVIEW



1. Kensington Security Slot	5. Ethernet (RJ-45)
2. USB-C 3.2 Gen 1	6. 2x USB-A 3.2 Gen 1
3. DP 1.2	7. Power connector
4. DP 1.2 out	8. USB-C 3.2 Gen 1

PERFORMANCE

Processor

Processor Family

Qualcomm® Snapdragon™ Processor

Processor

Processor Name	Cores	Threads	Max Frequency	Cache	Memory Support	Processor Graphics
Qualcomm QCS8250	Qualcomm Kryo 585 Octa-core: 4x Kryo Gold + 4x Kryo Silver	8	Kryo Gold@2.85GHz / Kryo Silver@1.8GHz	4MB	LPDDR5	Qualcomm Adreno™ 650

Operating System

Operating System

Android™ 10

Graphics

Graphics

Graphics	Type	Memory	Connector	Max Resolution	Key Features
Qualcomm Adreno 650 GPU	Integrated	Shared	DP	3840x2160@30Hz	DirectX® 12

Monitor Support

Monitor Support

Supports up to 2 independent displays via native display and 1 external monitor (ThinkSmart™ View Plus needs to connect another computer via DP / USB-C®, and external monitor does not work under Teams APP)

Chipset

Chipset

Qualcomm SoC (System on Chip) platform

Memory

Max Memory

8GB soldered LPDDR5

Memory Slots

Memory soldered to systemboard, no slots

Memory Type

LPDDR5

Storage

Storage Support

128GB UFS 3.1 on systemboard

Storage Type

Disk Type	Interface	Offering
Flash Memory	UFS 3.1	128GB

Multi-Media

Audio Chip

High Definition (HD) Audio, ALC4050H codes and ALC 5520 DSP

Speakers

5W x 2 Stereo speakers, detachable Soundbar (magnetic)

Microphone

Quad-microphone array

Camera

4k Camera, LED Indicator, USB Detachable with privacy shutter
Image Resolution: 8M
Active Array Size: 3840 x 2160

Sensor

Sensors

- Ambient light sensor (ALS)
- Proximity (P) sensor

Power Supply

Power Supply

Power	Type	Efficiency	Key Features
135W	Adapter	89%	Autosensing

DESIGN

Display

Display^[1]

Size	Resolution	Touch	Type	Surface	Aspect Ratio	Contrast Ratio	Key Features
27"	FHD (1920x1080)	Multi-touch	IPS	Anti-glare	16:9	1000:1	anti-fingerprint

Touchscreen

Supports 10-point touch

Notes:

[1] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Input Device

Keyboard

No keyboard

Mouse

No mouse

Mechanical

LED indicators

Status (mute/in meeting/off) LED on camera

Buttons

- Main body: Power Button, Mode Switch, Recovery Button
- Speaker bar: Vol Up, Vol Down, Speaker Mute, Mic Mute

Dimensions (WxDxH)^[1]

615.3 x 273 x 600 .6 mm (24.22 x 10.75 x 23.65 inches)

Weight^[2]

Around 12.6 kg (27.78 lbs)

Case Color

Black

Stand

Adjustable monitor stand, supports -5° to +35° tilt, left & right 45° swivel, up to 110mm lift, with Cell Phone Stand

Others

Supports VESA mount 200 x 200 mm. (For supporting VESA mount, additional mount kits are needed. The kits are sold separately)

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of

component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Network

Ethernet

Gigabit Ethernet, 1x RJ-45

WLAN + Bluetooth®

Qualcomm Wi-Fi® 6 QCA6391, 802.11ax Dual Band 2x2 Wi-Fi + Bluetooth 5.1^[1]

Notes:

[1] Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitations.

Ports^[1]

Top Ports

1x USB-C 3.2 Gen 1 and camera pin hole (for camera only)

Bottom Ports

- 1x DisplayPort™ 1.2 in
- 1x DisplayPort 1.2 out (works only when there is DisplayPort input from a computer)
- 1x Ethernet (RJ-45)
- 1x Power connector
- 1x USB-C 3.2 Gen 1 (support data transfer, Power Delivery 2.0 and DisplayPort 1.2)
- 2x USB-A 3.2 Gen 1

Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

SECURITY & PRIVACY

Security

Physical Locks

Kensington® Security Slot™

Other Security

- Camera privacy shutter
- Facial recognition
- Meeting status light

SERVICE

Warranty^[1]

Base Warranty

- 3-year courier or carry-in service
- 3-year limited onsite service

Notes:

[1] The warranty upgrades may be bundled with some models, please check the "Included upgrade" column in the specific model's configurations. For more service extensions, please go to <https://smartfind.lenovo.com/>. To learn more details of

warranty policy, please access <https://pcsupport.lenovo.com/warranty>.

ACCESSORIES

Bundled Accessories

Bundled Accessories

Viewplus Stylus Pen, passive

SOFTWARE

Preinstalled Software

Preinstalled Software

Microsoft® Teams Display APP

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

RoHS compliant

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

Other Certifications

Other Certifications

TÜV Rheinland® Low Blue Light

- This is a telepresence technology product.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

