



Poly Trio 8300 IP Conference Phone and PoE-enabled No Radio GSA/TAA (84C20AA)

Overview

Smart collaboration starts here



Small meeting room? No problem. Transform your small conference room into a smart collaboration hub with Poly Trio 8300, smart conference phone. Get more done in less space with quality audio clarity, a classic interface and future-proof flexibility.

Hear and be heard

Tune out distractions and keep everyone focused with noise-blocking technology. Pro-level audio quality ensures there's no time lost repeating or misunderstanding ideas.

One-touch-join

A simple interface launches meetings in seconds. The Poly Trio 8300 conference phone provides Wi-Fi, USB, Bluetooth®, and IP connectivity.

Additional specifications

Aspect ratio	16:9
Audio	Poly Acoustic Clarity technology provides full duplex conversations, acoustic echo cancellation, and background noise suppression; Comfort noise generation; DTMF tone generation (RFC 2833 and in-band); Low delay audio packet transmission; Adaptive jitter buffers
Audio codecs	G.711 (A-law and μ -law); G.722; G.722.1; G.722.1C; G.729AB; G.719; SILK; Polycom® Siren™ 7; Siren™ 14; iLBC; OPUS
Certifications and compliances	Argentina CNC; AS/NZ4268; AS/NZS 4268; AS/NZS 60950-1; AS/NZS 62368.1; Australia RCM; Australia/NZ RCM; Brazil ANATEL; CE Mark; CISPR22 Class B; CSA C22.2 No. 60950-1-07; CSA C22.2 No. 62368-1-14; EEA; EN 60950-1 & EN 62368-1; EN55024; EN61000-3-2, EN61000-3-3; EN55032 Class B; ETSI EN 300 328 v1.9.1; ETSI EN 301 489-1; ETSI EN 301 489-17; ETSI EN 301 489-3; FCC Part 15 (CFR 47) Class B; FCC Part 15C; FCC Part 15E; IEC 60950-1 & IEC 62368-1; ICES-003 Class B; Israel MOC; Japan MIC/VCCI; Malaysia SIRIM; NZ Telepermit; ROHS compliant; Saudi Arabia CITC; Singapore IMDA; So. Africa ICASA; So. Korea KC; Taiwan NCC/BSMI; UAE TRA; UL 60950-1 and UL 62368-1
Color	Black
Display size (diagonal)	8.9 cm (3.5")
Display size (diagonal)	3.5"
Energy star certified	ENERGY STAR® certified
Management Software	Poly Zero Touch Provisioning; RealPresence Resource Manager (v. 10.1 or above) based provisioning; Polycom Device Management Service for Enterprise (PDMS-E); Polycom Device Management Service for Service Providers (PDMS-SP) Cloud Management
Manufacturer Warranty	Poly standard one-year limited warranty
Microphone type	Three cardioid microphones
Minimum dimensions (W x D x H)	33.9 x 29.4 x 6 cm
Minimum dimensions (W x D x H)	13.3 x 11.5 x 2.4 in
Network protocols, supported	DHCP VLAN discovery; LLDP-MED for VLAN discovery; FTP/TFTP/HTTP/HTTPS server-based central provisioning; Manual or dynamic host configuration protocol (DHCP) network setup; QoS Support — IEEE 802.1p/Q tagging (VLAN), Layer 3 TOS, and DHCP; Time and date synchronization using SNTP; Provisioning and call server redundancy support
Operating humidity range	5 to 95%
Operating temperature range	0 to 40°C
Operating temperature range	32 to 104°F
Package weight	1760 g
Package weight	2.2 lb
Panel technology	Monochrome LCD
Ports	1 RJ-45 (10/100/1000 Mbps)

Power	Built-in auto sensing IEEE 802.3af Power over Ethernet (Class 0)
Security management	802.1X Authentication and EAPOL Media encryption via SRTP; Digest authentication; Encrypted configuration files; HTTPS secure provisioning; Password login; Support for signed software executables; Support for URL syntax with password; Transport Layer Security (TLS); Wi-Fi encryption: WEP, WPA-Personal, WPA2-Personal, WPA2-Enterprise with 802.1X (EAP-TLS, PEAP-MSCHAPv2); FIPS 140-2 compliant cryptographic module
Sensitivity (speaker)	90 dB
Special features	Adjustable base height; Unicode UTF-8 character support; Privacy shutter
Storage temperature range	-20 to 70 °C
Storage temperature range	-4 to 158 °C
Telephony and call handling features	Bundled with Polycom UC Software: Corporate Directory Access using LDAP; Call timer and call waiting; Call transfer, hold, divert (forward), park, pickup; Called, calling, connected party information; Distinctive incoming call treatment/call waiting; Do not disturb function; Local three-way audio conferencing; Local configurable digit map/dial plan; Shared call/bridged line appearance; Visual Conference Management; Up to 3 lines (maximum one Skype for Business and Microsoft Teams); Daisy-chain up to four; One-touch speed dial, redial and meeting join
UNSPSC code	43191511
UPC number	197497515695
VoIP features	IETF SIP (RFC 3261 and companion RFCs)
Weight	1.62 lb
Weight	735 g
What's in the box	Console; Network (LAN) cable-CAT-5E; Setup sheet
Wireless range	Up to 3.7 m
Wireless range (imperial)	Up to 12 ft

Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.