

Poly Blackwire 3210 Monaural USB-C Headset (Bulk Qty.50)

Freedom to work your way

The Blackwire 3200 Series provides a quality audio experience in a headset that’s built for enterprise needs. With a sleek design and flexible microphone boom for a customizable fit, what’s not to love?



*Product image may differ from actual product

Poly signature audio quality

Experience the high-quality audio you expect from Poly with a headset that offers PC wideband, a noise-canceling mic, and hi-fi stereo sound options. Dynamic EQ optimizes call quality and automatically adjusts the settings for listening to multimedia.

Advanced connectivity

Ideal for managing calls on your PC, mobile phone, or tablet combined with the comfort and durability of a corded headset for greater flexibility.

Long-lasting comfort and portability

Relax while you talk knowing your headset is secure- lightweight metal headband offers durability plus a custom fit. Leatherette ear cushions fold flat for easy portability.

Poly Blackwire 3210 Monaural USB-C Headset (Bulk Qty.50)

Specifications



Compatible with

Compatible operating systems: Windows 11; Windows 10; macOS

Connectivity and communications

Connection type: Wired USB Type-C®
Ear cushions: Artificial leather (surface material)
Headphone type: On-ear (monaural)

User interface features

Button user controls: Call answer/ignore/end/hold; Redial; Mute; Volume +/-

Audio

Audio features:
Dynamic EQ optimized
Digital signal processing (DSP)
Noise cancellation (NC)
Microphone type: Omnidirectional
Microphone bandwidth: 100 Hz to 10 kHz
Speaker bandwidth: 200 Hz to 6.8 kHz (speech mode); 20 Hz to 20 kHz (media mode)
Speaker size: 28 mm
Signal-to-noise ratio: >118 dB
Frequency response (microphone): 100 Hz to 10 kHz
Sensitivity (microphone): -38 dBV/Pa
Sensitivity (speaker): 90 dB

Battery

Impedance: 32 ohms

Certifications

Certified collaboration software: Skype for Business; Cisco Jabber; Avaya
Special features: Adjustable headband; Voice alerts

Environmental

Acoustic protection technology: SoundGuard¹

Applications supported

Management software:
HP Headset Control Center

Weight and dimensions

Product Primary Color: Black
Weight (Imperial): 0.19 lb (with cable); 0.14 lb (without cable)
Weight (metric): 87 g (with cable); 64 g (without cable)
Product dimensions (Imperial): 6.1 x 1.25 x 7.1 in
Product Dimensions (metric): 155 x 32 x 178 mm
Package dimensions (Imperial): 7.28 x 2.2 x 8.14 in
Package dimensions (metric): 185 x 56 x 207 mm
Package weight (Imperial): 0.55 lb
Package Weight (metric): 250 g
Cable length (Imperial): 2.59 ft (inline module to headset); 2.95 ft (USB to inline module); 5.28 ft (total USB to headset)
Cable length (metric): 79 cm (inline module to headset); 90 cm (USB to inline module); 161 cm (total USB to headset)
Product number: 80S09A6

Warranty

Poly standard two-year limited warranty

What is in the box

Headset
USB Type-C® cable

Technical Specifications Footnotes

¹ Protects against Acoustic Shock by limiting sounds to below 118 dBA.