



Poly Studio X70 All-In-One Video Bar with TC8 Controller Kit (83Z52AA)

Overview

Enable meeting equality



The Poly Studio X70, all-in-one video bar, offers quality audio and video performance in large meeting spaces. Enjoy pinpoint-accurate automatic framing and tracking modes, distraction-free audio technology, and lifelike 4K UltraHD video.

Crystal clear video

Ready for your close-up? This all-in-one video bar transitions seamlessly between wide and narrow-angle cameras, showing everyone in your large meeting spaces in sharp detail.

Production-quality performance

Keep your eye on the action with Poly DirectorAI intelligent camera framing and NoiseBlockAI technology — all powered by machine learning. Get advanced vocal pickup from our next gen microphones. Easily share content over wired or wireless connections.

Features

Smart camera tech

Give everyone in hybrid meetings an equal seat at the virtual table using a choice of framing modes with Poly DirectorAI smart camera technology.

4K cameras

No one looks their best with pixilated video. Enjoy richer, more lifelike meeting experiences with 4K UltraHD video.

Noise blocking innovations

Outside noise and side conversations can quickly derail a hybrid meeting. Keep background noise in check with Poly NoiseBlockAI and Acoustic Fence technologies.

Beamforming microphone

Make communicating effortless for everyone on the call, with a next-generation beamforming microphone array that clearly picks up all voices in a room.

Easy management via Poly Lens

Take control of your deployment from anywhere via remote management with Poly Lens cloud-based device management software.

Intuitive touch interface

The TC8 touch interface lets you launch, join, and share in an instant, while keeping your focus on the task at hand. Its sleek design features an 8-inch high-resolution touch display to make control options clear and accessible.

Additional specifications

| | |
|---|--|
| Audio | Poly NoiseBlockAI technology; Poly Acoustic Fence technology |
| Audio standards | 22 kHz with Polycom Siren 22 technology; 20 kHz with G.719 (M- Mode) and Polycom Siren 22 technology; 14 kHz with Polycom Siren 14 technology, G.722.1 Annex C; 7 kHz with G.722, G.722.1; 3.4 kHz with G.711, G.728, G.729A |
| Camera resolution | 2160p, 4K UHD (3840 x 2160) |
| Camera type | Dual-lens |
| Certified collaboration software | Zoom; Microsoft Teams; Google Meet |
| Content video resolution (input) | UHD (3840 x 2160); HD (1920 x 1080); WSXGA+ (1680 x 1050); UXGA (1600 x 1200); SXGA (1280 x 1024); WXGA (1280 x 768); HD (1280 x 720); XGA (1024 x 768); SVGA (800 x 600) |
| Content video resolution (output) | UHD (3840 x 2160); WUXGA (1920 x 1200); HD (1920 x 1080); WSXGA+ (1680 x 1050); SXGA+ (1400 x 1050); SXGA (1280 x 1024); HD (1280 x 720); XGA (1024 x 768) |
| Diagonal field of view (dFoV) | 140° (wide); 78° (narrow) |
| Digital signage | Appspace; Raydiant |
| Horizontal field of view (hFoV) | 120° (wide); 70° (narrow) |
| Interoperability | Zoom Certified; Microsoft Teams Certified; All cloud service providers through Poly Video App mode; USB Device mode; Support for native 3rd party applications including Zoom, Microsoft Teams, BlueJeans, Dialpad, GoToRoom, RingCentral and StarLeaf |
| Lens cover capabilities | Integrated |
| Management Software | Poly Lens |
| Manufacturer Warranty | Poly standard one-year limited warranty |
| Microphone pickup range (imperial) | Up to 25 ft |
| Microphone pickup range (metric) | Up to 7.62 m |
| Microphone type | Two MEMS microphones; Two second-order microphones |
| Network capabilities | IPv4; IPv6; 1x 10/100/1G Ethernet; Auto-MDIX; H.323 and/or SIP up to 6 Mbps in Poly App video mode; Polycom Lost Packet Recovery (LPR) technology; Dynamic bandwidth allocation; Reconfigurable MTU size; Web proxy support: basic, digest, and NTLM |
| Non-Operating Humidity Range | 5 to 95% |
| Non-operating temperature - Celsius | -40 to 70 °C |
| Non-operating temperature - fahrenheit | 40 to 158 °F |
| Operating altitude | 4,877 m |
| Operating altitude | 16,000 ft |
| Operating humidity range | 15 to 80% |

| | |
|---|--|
| Operating temperature range | 0 to 40 °C |
| Operating temperature range | 32 to 104 °F |
| People video resolution | 4K, 30 fps (TX and RX) from 2048 Kbps; 1080p, 30 fps from 1024 Kbps; 720p, 30 fps from 512 Kbps |
| Physical security | Standard Kensington lock slot |
| Ports | 1 USB Type-C® 5Gbps signaling rate; 2 USB Type-A 5Gbps signaling rate; 2 RJ-45; 1 audio-in; 1 audio-out; 2 HDMI-out 1.4 (video); 1 HDMI-in 1.4 (audio) |
| Power | 65 BTU h |
| SMART camera technology | Poly DirectorAI with speaker framing; People framing; Group framing; Presenter tracking; DirectorAI perimeter |
| Sensitivity (speaker) | 83 dB (mid speakers); 89 dB (tweeter speakers) |
| Speaker output power | 2 x 20 W (RMS for mid speakers); 2 x 30 W (maximum for mid speakers); 2 x 15 W (RMS for tweeter speakers); 2 x 20 W (maximum for tweeter speakers) |
| Speaker type | Two-way stereo speakers |
| Special features | Auto sensing power supply |
| Total camera resolution (megapixels) | 2 x 20 MP |
| UNSPSC code | 45111902 |
| UPC number | (AB0) 197497449297; (AB1) 197497449303; (AB2) 197497449310; (ABA) 197497449327; (ABB) 197497449334; (ABG) 197497449341; (ABJ) 197497453614; (ABM) 197497449358; (ABT) 197497449365; (ABU) 197497449372; (AC4) 197497449389; (ACJ) 197497449396; (UUF) 197961922943; (UUZ) 197497449402 |
| Video frame rate | 5–30 fps (up to 4K resolution at 15 fps in call) |
| Video standards | H.264 AVC; H.264 High Profile; H.265 |
| What's in the box | Poly Studio X70; Wall mount kit; AC power adapter; HDMI cable; Power cable; CAT 5E LAN cable; Poly TC8 touch controller |
| Wireless technologies | Bluetooth® 5.0; Wi-Fi 802.11a/b/g/n/ac (MIMO) Multi-channel Concurrency ^[1] |
| Zoom capability | 7.3x digital |

[1] TAA, JITC and no radio versions available.

Services

Poly Services

★ : Recommended

Poly Support Services

| | |
|--|--------------------|
| 3 Year Poly+ Studio X70 TC8 Dual Camera for Wireless Presentation System | P87300312 ★ |
| 1 Year One time ext HW Replacement for Studio X70 TC8 with NBD advanced replacement Poly DaaS | D87300DS1 |
| 1 Year Partner Poly+ Studio X70 TC8 Dual Camera for Wireless Presentation System | P87300160 |
| 1 Year Poly Elite Custom Studio X70 with TC8 For Citi use only | E87300650 |
| 1 Year Poly Elite Onsite Studio X70 TC8 Dual-Camera 4K+ Video Sys for Conf/Collab/Wireless Pres Sys | E87300114 |
| 1 Year Poly Elite Studio X70 TC8 Dual-Camera 4K+ Video System for Conf/Collab/Wireless Pres Sys | E87300112 |
| 1 Year Poly+ Onsite Studio X70 TC8 Dual Camera for Wireless Presentation System | P87300114 |
| 1 Year Poly+ Studio X70 & TC8 Dual-Camera 4K+ Video Sys Conf/Collab/Wireless Pres Sys | P87300112 |
| 1 year Partner Poly+ Studio X70 TC8 Dual Camera for Wireless Presentation System | P87300158 |
| 3 Year Partner Poly+ Onsite Studio X70 TC8 Dual Camera for Wireless Presentation System | P87300358 |
| 3 Year Partner Poly+ Studio X70 and TC8 Dual-Cam 4K+ Video Sys Conf/Collab/Wireless Pres Sys | P87300362 |
| 3 Year Poly Elite Studio X70 TC8 Dual-Camera 4K+ Video System for Conf/Collab/Wireless Pres Sys | E87300312 |
| 3 Year Poly+ Onsite Studio X70 TC8 Dual Camera for Wireless Presentation System | P87300314 |
| 5 Year HW Replacement for Studio X70 and TC8 with NBD advanced part replacement Poly DaaS | D87300DS5 |
| Service reactivation fee Studio X70 with TC8 for product less than one year out of support coverage | R87300801 |
| Service reactivation fee Studio X70 with TC8 for product one year or more out of support coverage | R87300802 |
| Upgrade embedded 1yr Poly+ to 3yr Partner Poly+ OnsiteStudio X70 & TC8 Dual-Camera 4K+ Video System | P87300788 |
| Upgrade embedded 3yr Partner Poly+ to 3yr Poly+ Onsite Studio X70 & TC8 Dual-Camera 4K+ Video System | P87300444 |
| Upgrade from embedded 1y Poly+ to 1y Poly Elite Studio X70 TC8 Dual-Camera 4K+ Video System | E87300902 |
| Upgrade from embedded 1yr Poly+ to 1yr Poly Pus Onsite Studio X70 with TC8 Dual-Camera 4K+ Video Sys | P87300102 |

| | |
|--|-----------|
| Upgrade from embedded 1yr Poly+ to 3yr Partner Poly+Studio X70 and TC8 Dual-Camera 4K+ Video System | P87300351 |
| Upgrade from embedded 1yr Poly+ to 3yr Poly+ Onsite Studio X70 with TC8 Dual-Camera 4K+ Video System | P87300309 |
| Upgrade from embedded 1yr Poly+ to 3yr Poly+Studio X70 with TC8 Dual-Camera 4K+ Video System | P87300103 |
| Upgrade from embedded 3yr Partner Poly+ to 3yr Poly+Studio X70 with TC8 Dual-Camera 4K+ Video System | P87300333 |

Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Dec 11, 2023 9:39 AM UTC+0000