

Poly Voyager 4310-M Microsoft Teams Certified USB-C Headset with charge stand

Cut wires. Cut Costs.

Free your workers from their desks with the perfect entry-level Bluetooth® wireless headset. Meet the Voyager 4300 UC Series. It's everything your teams need to stay productive and connect to all their devices whether at home or in the office. Keep your teams productive with all-day comfort and dual-mic Acoustic Fence technology that eliminates background noise. Phenomenal flexibility, connectivity, and freedom? Yes please!



*Product image may differ from actual product

Up to 50 meters/164 feet of Bluetooth® wireless range

Walk-and-talk with ease with up to 50 meters/164 feet of Bluetooth® wireless range.¹

UC versions connect with PC/Mac and mobile phones

One headset, choose your device—PC/Mac and mobile phone connection options with UC versions.

Office base connects with desk phones, PC/Mac and mobile phones

Multiple device connections—desk phone, PC/Mac and mobile phone connection options with Office base.²

Up to 24 hours of wireless talk time

Stay productive with up to a full 24 hours of wireless talk time.

Designed for portability: use at home and in the office

Designed for comfort with an adjustable, enhanced padded headband and improved memory foam ear cushions.

Stress free mute

Stress free mute with an easy-to-use pinch-to-mute button on microphone boom with dynamic mute alert.

DATASHEET

Poly Voyager 4310-M Microsoft Teams Certified USB-C Headset with charge stand

Specifications



Compatible with

Compatible operating systems: Windows 10; macOS

Connectivity

Wireless range: Up to 50 m; Up to 91 m (with Voyager Office base)

Wireless range (Imperial): Up to 164 ft; Up to 300 ft (with Voyager Office base)

Paired devices: Up to 8

Bluetooth version: 5.1

Supported bluetooth profiles: A2DP; AVRCP; HFP; HSP

Connection type: Bluetooth® (smartphone); USB Type-C® (PC)

Ear cushions: Artificial leather (surface material)

Headphone type: On-ear (binaural)

Battery

Battery life: Up to 24 hours (talk time, online indicator off); Up to 18 hours (talk time, online indicator on); Up to 47 hours (music time); Up to 50 days (standby time)⁴

Battery description: Rechargeable Li-ion

Battery capacity: 350 mAh

User Interface Features

Button user controls: Power on/off; Call answer/end; Mute; Volume +/-; Pairing

Audio

Audio features: Dynamic EQ optimized

Microphone type: 2 analog ECM; 2 digital MEMS

Microphone bandwidth: 100 Hz to 6.8 kHz

Speaker bandwidth: 20 Hz to 20 kHz

Speaker size: 32 mm

Charge time: <1.6 hours

Certifications

Certified collaboration software: Microsoft Teams; Zoom

Special features: Multi-connect; Adjustable headband; Passive noise cancellation (PNC); Two LED indicators on speaker in call status; Easy access to mute button; Fast Charge (up to 10 hours listening time after 15 mins of charge)

Environmental

Acoustic protection technology: SoundGuard Digital¹²

Applications Supported

Management software: Poly Lens

Weight and Dimensions

Product Primary Color: Black

Weight (Imperial): 0.35 lb

Weight (metric): 0.162 kg

Product dimensions (Imperial): 6.1 x 2.6 x 7.2 in

Product Dimensions (metric): 15.5 x 6.7 x 18.2 cm

Package dimensions (Imperial): 7.32 x 8.26 x 2.16 in

Package dimensions (metric): 18.6 x 21 x 5.5 cm

Package weight (Imperial): 0.714 lb

Package Weight (metric): 0.324 kg

Cable length (Imperial): 59.05 in

Cable length (metric): 1.5 m

UPC number: 17229174238

Product number: 77Y97AA

Minimum system requirements

USB Type-A port

Warranty

Poly standard two-year limited warranty

What is in the box

USB Type-C® charging cable

Quick start guide

Travel pouch

USB Type-A adaptor

Charging stand

Wireless headset

Key Selling Points Footnotes

¹ With included BT700 USB adapter.

² Sold separately.

Feature Messaging Footnotes

³ Some solutions are sold separately.

Technical Specifications Footnotes

¹ SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).

² Requires Poly Lens Desktop App to enable SoundGuard Digital features.

³ Voyager Office base available as an accessory, sold separately.

⁴ Requires setting change via Poly Lens or Plantronics Hub.