

OVERVIEW



1. Kensington Security Slot	4. DP 1.2
2. Power-in	5. USB-B 3.2 Gen 1
3. HDMI 1.4	6. USB 3.2 Gen 1

PERFORMANCE

Panel

Panel

In-Plane Switching (IPS)

Backlight

WLED

Display Size

23.8 inches

Max View Area

WxH: 527.0 x 296.4 mm (20.75 x 11.67 inches)

Resolution

1920 x 1080

Aspect Ratio

16:9

Pixel Pitch

0.275 x 0.275 mm

Dot / Pixel Per Inch

93 dpi

Brightness

250 nits

Contrast Ratio

- Contrast Ratio: 1000:1
- Dynamic Contrast Ratio: 3M:1

View Angle (H / V)

Horizontal: 178°, Vertical: 178°

Response Time

- Extreme Mode: 4 ms
- Normal Mode: 6 ms

Refresh Rate

60Hz

Color Gamut

99% sRGB

Color Support

16.7 Million

Color Depth

8-bit (6-bit+FRC)

Screen Surface Treatment

Anti-glare

Curvature

Flat Panel

Operating System

Operating System

- Windows® 10 Support
- Windows 11 Support

Multi-Media

Camera

FHD 1080p

Microphone

Integrated microphone

Speakers

Stereo speakers, 3W x2

Power Supply

Power Consumption

- Typical / Max: 14W / 34W
- Switch-off Mode: <0.3W
- Sleep / Off mode: <0.5W
- External Power Supply
- Energy Star TEC: 37.9kWh
- Energy Star Power On: 11.9W

Voltage Required

AC 100 to 240 V (50-60Hz)

Special Features

Special Features

- KVM Switch
- Natural Low Blue Light
- Lenovo® ThinkColour (Lenovo Display Control Center) Support
ThinkColour can only be used with Windows 10 and Windows 11

DESIGN

Display

Touchscreen

- Capacitive-type multi-touch, supports 10-point touch (for MT 12NB only)
- Non-touch

Mechanical

ThinkCentre® M Series Support

ThinkCentre Tiny, ThinkStation® Tiny from 4th Generation

Bezel Width

- Side: 2mm
- Top / Bottom: 2mm / 46mm

Case Color

Raven black

Dimensions (WxDxH)^[1]

Models	Dimensions
Lowest Position	539.8 x 207.6 x 384.6 mm (21.25 x 8.17 x 15.14 inches)
Highest Position	539.8 x 207.6 x 539.6 mm (21.25 x 8.17 x 21.24 inches)
Head Only	539.8 x 72.8 x 367.6 mm (21.25 x 2.87 x 14.47 inches)

Packaging Dimensions (WxDxH)

620 x 187 x 420 mm (24.41 x 7.36 x 16.54 inches)

Weight^[2]

Models	Weight
Monitor Head Only	3.7 kg (8.2 lbs)
Monitor With Stand	6.0 kg (13.2 lbs)

Packaging Weight

9.5 kg (20.9 lbs)

Mounting

Supports VESA mount 100mm

Stand

ThinkCentre Tiny-In-One 24 Gen 5

Supports -5° to +23.5° tilt, left & right 45 swivel, -5° to +90° pivot, up to 155mm lift

In the Box

- Monitor with Stand
- Power Adapter (90W)
- Power cable (1.0 m)
- Quick Setup Guide

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Ports^[1]

Rear Ports

- 1x USB 3.2 Gen 1
- 1x USB-B 3.2 Gen 1, USB upstream
- 1x HDMI® 1.4
- 1x DisplayPort™ 1.2

Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

SECURITY & PRIVACY

Security

Physical Locks

Kensington® Security Slot™, 3 x 7 mm and 2.5 x 6 mm

SERVICE

Warranty

Base Warranty

3-year limited warranty

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

- EU Energy Label (D-class)
- ENERGY STAR® Certified
- EPEAT™ Gold Registered
- TCO Certified 9.0
- TCO edge 2.0
- Volatile Organic Compound Certification
- RoHS compliant

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

Other Certifications

Other Certifications

- Eyesafe® Certified 2.0
- TÜV Rheinland® Eye Comfort Certification
- TÜV Rheinland Low Blue Light (Hardware Solution)

- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

