

You are browsing the product catalog for

Pakistan



DESKTOP PRINTERS

PC45T

The PC45T thermal transfer printer brings powerful performance, flexible configuration, reliable connectivity, and easy integration in a compact design to tackle rapidly changing everyday work environments.

Overview



Feedback

Versatile and Durable Design

The PC45T 4-inch direct thermal printer is built for performance, featuring a large touchscreen and enterprise-level ruggedness. With optimized low-label and low-ribbon warning workflows, it minimizes downtime and enhances productivity. Its flexibility allows for seamless switching between thermal transfer and direct thermal media, adapting to various business needs.

Reliable Connectivity

Stay connected with Wi-Fi 5 and Bluetooth® 5.1 LE, ensuring continuous productivity. The PC45T's WLAN connectivity supports rapid data capture, facilitating quick and efficient deployments within your organization.

Smart Customization with Smart Parse

Leverage Smart Parse technology to easily resize objects, barcodes, or font types without access to the backend system. The PC45T is compatible with numerous network protocols and supports multiple print languages, whether connected to a local server or operating in the cloud.

Streamlined Printer Network Control

The Honeywell Printer Edge™ platform offers a centralized management solution for your printer network. Gain real-time visibility, automated software updates, and robust security features—perfect for businesses that can't afford downtime.

Cost-Effective Workflow Solutions

Printer Edge simplifies operations and allows you to manage costs efficiently. By enhancing control over your printing environment, it empowers you to focus on optimizing workflow and delivering quality service.

Specifications

FEATURES

Features

- Bluetooth
- Cutter Module
- Media Low Sensor
- RFID
- Self Strip Module
- Wifi

Application

- Packaging Label
- Receipt
- Wristband

Compatible Software

- Honeywell Printer Edge

Compatible Drivers

- CUPS driver for Linux
- Honeywell Device Types for SAP
- Honeywell label design and print package
- InterDriver Windows printer driver

DIMENSIONS

Overall Dimensions

- 179.6 mm L x 212.9 mm W x 285.5 mm H
(7.1 in L x 8.4 in W x 11.1 in H)

PRINTING SPECIFICATIONS

2D Barcodes

- QR

Resolutions

- 203 dpi
- 300 dpi

Print Speeds

- 8 ips

Feedback

Print Method

- Thermal Transfer

Character Sets

- Asian Fonts
- Latin

MEDIA

Printer Media Type

- Thermal Transfer

NETWORK

Wireless Communication

- Bluetooth
- Wifi

Network Specifications

- TCP/IP suite (TCP, UDP, M, IGMP), LPR/LPD, Telnet/SSH, FTP/SFTP, BOOTP, DHCP, HTTP/HTTPS, SNMPv1/2c/3, SNMP-MIBII supported – over UDP/IP (private enterprise MIB included), SMTP Supports IPv4 and IPv6

SOFTWARE & FIRMWARE

Printer Command Language

- Fingerprint (FP), Direct Protocol (DP), Intermec Printer Language (IPL), ZSim2 (ZPL-II), DPL, XML-enabled for SAP All and Oracle WMS, PDF, C#

HARDWARE

Printer Connection Interface

- Bluetooth
- Ethernet
- USB
- Wifi

ELECTRICAL

Operating Voltage

- 100-240V AC

ENVIRONMENTAL

Operating Temperature

- 0°C to 45°C (32°F to 113°F)

SERVICE TERMS

Warranty Duration

- 2 years

OTHERS

Print Width

- 4 inch

Print Resolution

- 203 dpi
- 300 dpi

Print Volume

- Up to 2,000

Industry

- Aerospace
- Government & Public Sector
- Healthcare
- Logistics & Warehouses
- Manufacturing
- Retail

Print Technology

- Thermal Transfer

Connectivity

- Ethernet
- Wi-Fi

Feedback



Please sign in to view part numbers available for purchase based on your account

[Sign In](#)

Showing 1 to 7 of 7 parts



Search

PART NUMBER	DESCRIPTION	ORDER ONLINE
PC45T000000200	SKU, LCD, ETH, 203DPI, NO PC, PC45T	SIGN IN
PC45T000000201	SKU, LCD, ETH, 203DPI, US PC, PC45T	SIGN IN
PC45T000000300	SKU, LCD, ETH, 300DPI, NO PC, PC45T	SIGN IN
PC45T000000301	SKU, LCD, ETH, 300DPI, US PC, PC45T	SIGN IN
PC45T010000201	SKU, LCD, E+BT+WL, 203DPI, US PC, PC45T	SIGN IN
PC45T01NA01201	SKU, LCD, E+BT+WL, RFID, MLS, 203DPI, US PC	SIGN IN
PC45T020000200	SKU, LCD, E+BT+W, 203DPI, NO PC, PC45T	SIGN IN

Rows

[Previous](#) [1](#) [Next](#)

Product Number

Please sign in to view part numbers available for purchase based on your account
[Sign In](#)


PART NUMBER	DESCRIPTION
PC45T000000200	SKU,LCD,ETH,203DPI, NO PC,PC45T
PC45T000000200	SKU,LCD,ETH,203DPI, NO PC,PC45T
PC45T000000201	SKU,LCD,ETH,203DPI, US PC,PC45T
PC45T000000201	SKU,LCD,ETH,203DPI, US PC,PC45T
PC45T000000300	SKU,LCD,ETH,300DPI, NO PC,PC45T
PC45T000000300	SKU,LCD,ETH,300DPI, NO PC,PC45T
PC45T000000301	SKU,LCD,ETH,300DPI, US PC,PC45T
PC45T000000301	SKU,LCD,ETH,300DPI, US PC,PC45T
PC45T010000201	SKU,LCD,E+BT+WL,203DPI, US PC,PC45T
PC45T010000201	SKU,LCD,E+BT+WL,203DPI, US PC,PC45T
PC45T01NA01201	SKU,LCD,E+BT+WL,RFID,MLS,203DPI, US PC
PC45T01NA01201	SKU,LCD,E+BT+WL,RFID,MLS,203DPI, US PC
PC45T020000200	SKU,LCD,E+BT+W,203DPI,NO PC,PC45T
PC45T020000200	SKU,LCD,E+BT+W,203DPI,NO PC,PC45T

Feedback



Discover the Powerfully Reliable PC45T Printer


Complete Your Solution



Honeywell Operational Intelligence

Intelligence data insights, asset management and automation for specific pain points to improve functionality and increase ROI.

[→ LEARN MORE](#)



Honeywell Support Services

Maximize the value of your printers with complete support throughout the full lifecycle.

[→ LEARN MORE](#)

Feedback

Honeywell
Industrial Automation
855 S Mint St
Charlotte, NC 28202
800-582-4263

Product name
© Current year Honeywell International Inc.
All rights reserved.

[Safety and Productivity Solutions homepage](#)



This document was generated on (YYYY-MM-DD, HH:mm:ss). Subject to change without notice.

Feedback