

OVERVIEW



1. Kensington Security Slot	4. VGA
2. Power connector	5. Audio line-out (3.5mm)
3. HDMI 1.4	

PERFORMANCE

Panel

Panel

In-Plane Switching (IPS)

Backlight

WLED

Display Size

23.8 inches

Max View Area

WxH: 527 x 296.5 mm

Resolution

1920 x 1080

Aspect Ratio

16:9

Pixel Pitch

0.275 x 0.275 mm

Dot / Pixel Per Inch

93 dpi

Brightness

Typical: 250 cd/m²

Contrast Ratio

Contrast Ratio: 1300:1

View Angle (H / V)

Horizontal: 178°, Vertical: 178°

Response Time

- Extreme Mode: 4 ms
- Normal Mode: 6 ms

Refresh Rate

100Hz

Color Gamut

99% sRGB

Color Support

16.7 Million

Color Depth

8-bit (6-bit+FRC)

Screen Surface Treatment

Anti-glare

Curvature

Flat Panel

Operating System

Operating System

- Windows® 10 Support
- Windows 11 Support

Power Supply

Power Consumption

- Typical / Max: 13.5W / 20.5W
- Switch-off Mode: <0.3W
- Sleep / Off mode: <0.5W
- Internal Power Supply

- Energy Star TEC: 40.5kWh
- Energy Star Power On: 12.9W

Voltage Required

AC 100 to 240 V (50-60Hz)

Special Features

Special Features

Natural Low Blue Light

DESIGN

Mechanical

ThinkCentre® M Series Support

ThinkCentre M Series Tiny, ThinkCentre M Series Nano
For supporting Tiny devices, additional mount kits are needed (sold separately).
For supporting Nano devices, additional mount kits are needed (sold separately).

Bezel Width

- Side: 2mm
- Top / Bottom: 2mm / 22mm

Cable Management

Support

Case Color

Raven black

Dimensions (WxDxH)^[1]

Models	Dimensions
Lowest Position	539.4 x 183.0 x 434.0 mm (21.24 x 7.20 x 17.09 inches)
Highest Position	539.4 x 183.0 x 434.0 mm (21.24 x 7.20 x 17.09 inches)
Width of Head (Slimmest Part)	6.9 mm (0.27 inches)
Head Only	539.4 x 43.0 x 326.2 mm (21.24 x 1.69 x 12.84 inches)

Packaging Dimensions (WxDxH)

592 x 110 x 415 mm (23.31 x 4.33 x 16.34 inches)

Weight^[2]

Models	Weight
Monitor Head Only	3.0 kg (6.6 lbs)
Monitor With Stand	3.8 kg (8.4 lbs)

Packaging Weight

5.7 kg (12.6 lbs)

Mounting

Supports VESA mount 100 x 100 mm

Stand

supports -5° to +22° tilt

In the Box

- 1x HDMI® cable (1.8m)
- 1x Power cable (1.8m)
- Monitor with Stand
- Quick Setup Guide

Notes:

[1] The system dimensions may vary depending on configurations.
[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Ports^[1]

Rear Ports

- 1x HDMI 1.4
- 1x VGA
- 1x audio-out (3.5mm)

Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

SECURITY & PRIVACY

Security

Physical Locks

Kensington® Security Slot™

SERVICE

Warranty

Base Warranty

3-year limited warranty

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

- EU Energy Label (E-class)
- ENERGY STAR® Certified
- EPEAT™ Gold Registered
- TCO Certified 9.0
- TCO edge 2.0
- Volatile Organic Compound Certification
- RoHS (2011/65/EU)

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

Other Certifications

Other Certifications

- Eyesafe® Certified 2.0
- TÜV Rheinland® Eye Comfort Certification
- TÜV Rheinland Low Blue Light (Hardware Solution)

• Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not

WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.

- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

