ProductSheet

Poly Trio C60 IP Conference Phone Full Radio and PoE-enabled GSA/TAA (849B3AA)

One device. Many possibilities.

Bring people together. Launch big ideas. And make sure everyone at the table can be heard, near or far with Poly signature audio. The Trio C60 plays nicely with everyone, delivering native experiences on your favorite collaboration platforms.



Poly signature audio
Get more out of your conference calls. Poly reduces distracting background noise to ensure every inflection is heard. Hear every reaction with up to 22 kHz of rich, full sound.

One-touch join
All it takes is a fingertip to get started. Join your calls in a second with a single touch of a button thanks to the truly intuitive user experience.

Featuring

Flexible connectivity
Maximize flexibility and investments with connectivity to multiple SIP and UC-cloud services simultaneously.

Audio clarity
Experience the power of full-duplex audio for natural conversations. Count on audio clarity in any size space with echo and reverb cancellation.

Poly portfolio compatible
Complement your Poly Studio X50, Poly Studio X30, or G7500 video solution with fast, simple control from Trio C60.

Scalable
Cater to any size meeting with optional expansion microphones or by daisy-chaining multiple systems together.

Wi-Fi calling
Get started faster and more easily with Wi-Fi audio calling (2.4–5 GHz), with no need to re-cable.

Specifications

Display size (diagonal)	12.7 cm (5")
Display size (diagonal)	5"
Panel technology	Color LCD
Audio	Poly Acoustic Clarity technology provides full duplex conversations, acoustic echo cancellation, and background noise suppression; Comfort noise generation; DTMF tone generation (RFC 2833 and in-band); Low delay audio packet transmission; Adaptive jitter buffers
Minimum dimensions (W x D x H)	38.3 x 7.5 x 33.2 cm
Minimum dimensions (W x D x H)	15.1 x 2.9 x 13.1 in
Weight	950 g
Weight	2.1 lb
Ports	1 USB 2.0 Type-A (for USB battery charging); 1 USB 2.0 Micro-B (for USB audio device); 2 RJ-45 (10/100/1000BASE-TX Mbps)
Package dimensions (W x D x H)	48.3 x 11.5 x 39.4 cm
Package weight	300 g
Energy star certified	ENERGY STAR® certified
Special features	Unicode UTF-8 character support
Security management	802.1X Authentication and EAPOL Media encryption via SRTP; Digest authentication; Encrypted configuration files; HTTPS secure provisioning; Password login; Support for signed software executables; Support for URL syntax with password; Transport Layer Security (TLS); Wi-Fi encryption: WEP, WPA-Personal, WPA2-Personal, WPA2-Enterprise with 802.1X (EAP-TLS, PEAP-MSCHAPv2); FIPS 140-2 compliant cryptographic module
UPC number	197497506440
Manufacturer Warranty	Poly standard one-year limited warranty
What's in the box	Console; Network (LAN) cable-CAT-5E; USB Type-A cable; Cable wrap; Tactile overlay for improved accessibility; Setup sheet

Top Recommended Displays, Accessories and Services

Poly Support Services

3 Year Poly+ Trio C60	P86240312

Messaging Footnotes

No Messaging Footnotes

Technical Specifications Footnotes

No Technical Specifications Footnotes

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.