

NOTE:

1.CABLE:DP UL20276 30AWG#5PR+30AWG#4C+AEB 50% COLOR:BLACK  
 OD:6.0MM MARKING:BLACK BOX CORPORATION(←25.4mm→)DisplayPort Cable  
 E223178 兄 AWM STYLE 20276 80℃ 30V VW-1 C

BBOX P/N	LENGTH
VCB-DP2-0010-MM-R2	10FT

2.CONNECTOR:DP MALE AUTOMATIC WELDING NICKEL PLATING IRON SHELL  
 BLACK RUBBER CORE

3.PVC MOLDED COLOR:BLACK

4.Dust cap

5.SHELL MATERIAL: ABS

6.LABEL:BLACK BOX P/N LABEL


7.Resolution Supported: 4K\*2K 60Hz YCbCr4:4:4 8bit

ELECTRONIC TEST:

- A. OPEN/SHORT/INTERMITTENCE:100%.
- B. INSULATION RESISTANCE 3 ohm Min.
- C. HI-POT TEST:DC 300V/10ms.

ALL MATERIALS COMPLY WITH ROHS2(2015/863)

PIN Assignment



**BLACK BOX**

Tolerance:	APPROVED BY:	
X. ±	CHECK BY:	VCB-DP2-0010-MM-R2
.X ±	DRAWN BY:	Description:
.XX ±	Dong.MI	DisplayPort Port M TO M CABLE
.XXX ±	DATE:	DWG. NO:
Angel:	2023.08.29	
X ±	Scale:	Unit mm
.X ±		SHEET: 1 OF 1

REV	DESCRIPTION	APPD.	DATE
-----	-------------	-------	------



REV:01