



# Poly Rove Single/Dual Cell DECT 1893-1906 MHz B2 Base Station (8G0D9AA)

## Overview

### End-to-end security

Secure your conversations with the Poly Rove B2 base station DECT™ end-to-end encryption. Built for enterprise deployments and compatible with any of the Poly Rove handsets and the Rove R8 repeater, the Rove B2 base station keeps teams going.

### Expand with confidence

Poly Rove B2 base station is compatible with all Poly Rove products and has the flexibility to scale as you grow. So, you don't have to worry about outgrowing your communication solution.

### Seamless and secure calling

Communicate confidently with the Poly Rove B2 base station secure solution. Enjoy seamless conversations with end-to-end encryption, thanks to DECT™ technology, ensuring privacy from your handset to the base station.

## Features

### Scale effortlessly

The mid-level DECT™ base station for small deployments needing up to 5,000 sq ft of coverage on a single cell deployment, and up to 15,000 sq ft with the dual cell base station for medium sized deployments.

### Extended range

Employees can move around effortlessly with an indoor range of up to 50 m/164 ft and up to 300 m/984 ft outdoors. Extend your reach significantly, depending on the environment, as a Rove R8 repeater is added.<sup>[1]</sup>

### Safeguard your calls

Conversations are safe and secure with DECT™ wireless security. And it doesn't stop there - maintain DECT™ encryption even when you add a base or repeater to your solution.

---

*[1] The Rove B2 base stations are compatible with up to 6 Poly Rove R8 repeaters per base station. Range increases by up to 50 m/164 ft (indoor) or up to 300 m/984 ft (outdoor), depending on environment, as a repeater is added.*

## Additional specifications

<b>Audio</b>	DTMF tone generation (RFC 2833 and in-band)
<b>Audio codecs</b>	G.165, 168 echo cancellation
<b>Battery life</b>	Up to 18 hours (talk time); Up to 300 hours (standby time)
<b>Battery type</b>	Rechargeable Li-ion
<b>Certifications and compliances</b>	UL 62368-1
<b>Certified collaboration software</b>	Zoom
<b>Color</b>	Black
<b>Country of origin</b>	Product of China
<b>DECT frequency</b>	1880 to 1900 MHz
<b>Display features</b>	Adjustable font size selection (regular, medium, large)
<b>Display size (diagonal)</b>	6.1 cm (2.4")
<b>Display size (diagonal)</b>	2.4"
<b>Energy star certified</b>	ENERGY STAR® certified
<b>Headset and handset compatibility</b>	Compliant with ADA Section 508 Subpart B 1194.23 (all)
<b>Headset ports</b>	1 3.5 mm headset jack
<b>Management Software</b>	Polycom Device Management Service for Service Providers (PDMS-SP) Cloud Management
<b>Manufacturer Warranty</b>	Poly standard one-year limited warranty
<b>Minimum dimensions (W x D x H)</b>	56.9 x 146.3 x 36.8 mm
<b>Minimum dimensions (W x D x H)</b>	2.2 x 5.8 x 1.5 in
<b>Native resolution</b>	240 x 320
<b>Network protocols, supported</b>	Manual or dynamic host configuration protocol (DHCP) network setup; IPv4
<b>Onscreen controls</b>	Three multi-colored mute indicators; Three sets of capacitive touch volume and mute buttons
<b>Operating humidity range</b>	5 to 95%
<b>Operating temperature range</b>	-10 to 55°C
<b>Operating temperature range</b>	14 to 131°F
<b>Package dimensions (W x D x H)</b>	239 x 141 x 44 mm
<b>Package dimensions (W x D x H)</b>	9.4 x 5.6 x 1.7 in
<b>Package weight</b>	395 g
<b>Package weight</b>	0.87 lb
<b>Panel technology</b>	Color TFT LCD
<b>Power</b>	External universal AC adapter: 5V 1A DC

<b>Security management</b>	DECT™ security certified
<b>Special features</b>	Unicode UTF-8 character support; Push-to-talk
<b>Storage temperature range</b>	-40 to 158°F
<b>Storage temperature range</b>	-40 to 70°C
<b>Telephony and call handling features</b>	Up to 10 simultaneous calls (single cell)
<b>UNSPSC code</b>	43191511
<b>UPC number</b>	197497776980
<b>VoIP features</b>	Up to Twenty (20) service subscription profile assignments (SP 1 – 20)
<b>Weight</b>	0.37 lb
<b>Weight</b>	168 g
<b>What's in the box</b>	Safety information sheet; Handset; Quick start guide; AC power adapter; Charging cradle; Spare battery; Base station; Ethernet cable; Belt clip
<b>Wireless range</b>	Up to 50 m indoor
<b>Wireless range (imperial)</b>	Up to 165 ft indoor

---

# Services

## Poly Services

★ : Recommended

### Poly Support Services

3 Year Poly+ Rove B2 Single/Dual Cell DECT Base Station	P86820312 ★
1 Year Partner Poly+ Rove B2 Single and Dual Cell DECT Base Station	P86820160
1 Year Poly Elite Rove B2 Single/Dual Cell DECT Base Station	E86820112
1 Year Poly+ Rove B2 Single/Dual Cell DECT Base Station	P86820112
3 Year Partner Poly+ Rove B2 Single and Dual Cell DECT Base Station	P86820362
7 Year HWR Rove B2 Single/Dual Cell DECT Base Station NBD with Poly DaaS Svc	D7YLLT031

---

## Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.