



Poly Rove R8 DECT Repeater (84H79AA)



Overview

Expand securely

Enhance your Poly Rove DECT™ footprint with the Poly Rove R8 repeater. Built to extend the range of the Poly Rove base station to offer scalability without sacrificing security. Guard your most critical conversations with end-to-end encryption.

Wider reach, safer calls

Communicate confidently with the Poly Rove R8 repeater secure solution. Enjoy seamless conversations with end-to-end encryption, thanks to DECT™ technology, ensuring privacy from your handset to the base station to the repeater.

We grow with you

Poly Rove R8 is compatible with all Poly Rove products and has the flexibility to scale as you grow.

Features

Effortless expansion

Experience enhanced scalability through auto configuration on both single and dual cell base stations reducing IT setup time.

Get more range

Extend your reach significantly from up to 50 m/164 ft to 300 m/984 ft, depending on the environment, as a Rove R8 repeater is added.^[1]

[1] The Poly Rove B1 and Poly Rove B4 base stations are compatible with up to 3 Poly Rove R8 repeaters per base station. The Poly Rove B2 base stations are compatible with up to 6 Poly Rove R8 repeaters per base station.

Additional specifications

Certifications and compliances	UL 62368-1
Certified collaboration software	Zoom
Color	Black
Country of origin	Product of China
DECT frequency	1880 to 1900 MHz
Energy star certified	ENERGY STAR® certified
Management Software	Polycom Device Management Service for Service Providers (PDMS-SP) Cloud Management
Manufacturer Warranty	Poly standard one-year limited warranty
Operating humidity range	5 to 95%
Operating temperature range	-10 to 55°C
Operating temperature range	14 to 131°F
Package dimensions (W x D x H)	239 x 141 x 44 mm
Package dimensions (W x D x H)	9.4 x 5.6 x 1.7 in
Package weight	354 g
Package weight	0.78 lb
Ports	1 RJ-45 (10/100/1000BASE-TX Mbps)
Power	External universal AC adapter: 5V 2A DC; Power over Ethernet (PoE)
Security management	DECT™ security certified; Encrypted Daisy Chained
Special features	Extends DECT™ coverage
Storage temperature range	-40 to 70°C
Storage temperature range	-40 to 158°F
UNSPSC code	43191515
UPC number	(ABA) 197497527605; (ABB) 197497527612; (ABG) 197497527636; (ABJ) 197497775358; (ABU) 197497527643; (UUF) 196548117000
Weight	0.37 lb
Weight	166 g
What's in the box	Desk stand; Safety information sheet; Quick start guide; Base station; Ethernet cable
Wireless range	Up to 50 m indoor
Wireless range (imperial)	Up to 165 ft indoor

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Nov 17, 2023 4:47 PM UTC+0000