



FLEXIBILITY YOU NEED— AT A PRICE YOU CAN AFFORD.

BENEFITS

- Leatherette ear cushions fold flat for easy storage (C3215/C3225).
- Call answer/end, mute, volume +/-.
- Variants include universal USB or USB-C type connectivity.
- 3.5 mm connectivity lets you work on a variety of mobile devices (C3215/C3225).

BLACKWIRE 3200 SERIES

The Blackwire 3200 Series corded UC headsets are durable, lightweight, easy to deploy and come in a variety of connectivity and wearing options. Add insights from Plantronics Manager Pro, an additional service, and you've got a future proof solution. The Blackwire 3200 series with Poly's signature audio provides top notch features at a price you can afford.

- Available in monaural (C3210/C3215) or hi-fi stereo with passive noise reduction (C3220/C3225).
- Variants include universal USB or USB-C.
- Connectivity to smartphone and tablet via 3.5 mm (C3215/C3225).
- Intuitive inline controls to answer/end calls, control volume, and mute.
- PC wideband audio with noise-canceling microphones for high-quality PC telephony.
- Plantronics Manager Pro, an additional purchase, enables your IT team to gain insight into every compatible Plantronics headset being used company-wide.

BLACKWIRE 3200 SERIES



C3210



C3215



C3220



C3225

SPECIFICATIONS

CONNECTS TO

- PC via USB/USB-C, connects to mobile devices and tablets via 3.5 mm and devices that support USB-C

COMPATIBLE WITH

- Windows® or Mac OS

IDEAL FOR

- Users transitioning to PC telephony for webinars, conference calls, music, and other multimedia applications

PC AUDIO PERFORMANCE

- Dynamic EQ, microphone frequency response 100 Hz–10 kHz optimal for PC wideband voice telephony (up to 6,800 Hz), hi-fi stereo (C3220/C3225). Receive output from 20 Hz–20 kHz, enhanced digital signal processing (DSP), noise-canceling microphone, adjustable audio alerts with Plantronics Hub software (mute/volume)*

HEARING PROTECTION

- SoundGuard: Acoustic limiting for protection against sounds above 118 dBA

REMOTE CALL CONTROL

- Call answer/ignore/end/hold, redial, mute, volume +/-

SPEAKER SIZE

- 28 mm/ 0.09 ft

INPUT IMPEDANCE

- 32 ohms

SPEAKER SENSITIVITY

- 90dB*

SPEAKER BANDWIDTH (SPEECH MODE)

- 200-6800Hz

SPEAKER BANDWIDTH (MEDIA MODE)

- 20-20000Hz

MAXIMUM ACOUSTIC OUTPUT

- 118dB SPL

MICROPHONE SENSITIVITY

- -38dBV/Pa

MICROPHONE BOOM LENGTH

- 130 mm / 0.43 ft

MICROPHONE BANDWIDTH

- 100-10000Hz

WEIGHT (WITH CABLE)

- 87 g/ 0.19 lbs (C3210)
- 96 g/ 0.21 lbs (C3215)
- 118 g/ 0.26 lbs (C3220)
- 121 g/ 0.27 lbs (C3225)

WEIGHT (WITHOUT CABLE)

- 64 g/ 0.14 lbs (C3210, 3215)
- 92 g/ 0.20 lbs (C3220, 3225)

CABLE LENGTH (INLINE MODULE TO HEADSET)

- 790 mm/ 2.59 ft (C3210, 3220)
- 1295 mm/ 4.25 ft (C3215, 3225)

CABLE LENGTH (USB TO INLINE MODULE)

- 900 mm/ 2.95 ft

CABLE LENGTH (TOTAL USB TO HEADSET)

- 1610 mm/ 5.28 ft (C3210, 3220)
- 2270 mm/ 7.45 ft (C3215, 3225)

HEADBAND ADJUSTMENT

- 35 mm/ 0.11 ft (C3210, 3215)
- 70 mm/ 0.23 ft (C3220, 3225)

BOOM ROTATION

- 270° (C3210, 3215, 3220, 3225)

MODELS

- **C3210 USB** (Monaural); **C3210 USB-C** (Monaural); **C3215 USB** (Monaural with 3.5 mm); **C3215 USB-C** (Monaural with 3.5 mm); **C3220 USB** (Stereo); **C3220 USB-C** (Stereo); **C3225 USB** (Stereo with 3.5 mm); **C3225 USB-C** (Stereo with 3.5 mm): Built for UC applications and softphones from Avaya®, Cisco®, Microsoft® and more*. Certified for Skype for Business

* 1mW/1kHz 0.01m open field

LEARN MORE

For more information on Blackwire 3200 Series visit
www.poly.com/blackwire-3200