

OVERVIEW



1. Headphone / microphone combo jack (3.5mm)	4. ThinkSmart One Cable
2. Power button	5. Kensington Security Slot
3. Power connector	

PERFORMANCE

Processor

Processor Family

8th Generation Intel® Core™ i5 Processor

Processor***

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Memory Support	Processor Graphics
Core i5-8365U	4	8	1.6GHz	4.1GHz	6MB	DDR4-2400	Intel UHD Graphics
Core i5-8365UE	4	8	1.6GHz	4.1GHz	6MB	DDR4-2400	Intel UHD Graphics 620

Operating System

Operating System**

- Windows® 10 IoT Enterprise
- Windows 11 IoT Enterprise GAC 64
- Windows 11 IoT Enterprise SAC 64

Graphics

Graphics

Graphics	Type	Memory	Connector	Max Resolution	Key Features
Intel HD graphics	Integrated	Shared	2x HDMI®	4096x2304@60Hz(HDMI)	DirectX® 12

Monitor Support

Monitor Support

Supports up to 3 independent displays via native display and 2 external monitors; supports external monitors via 2x HDMI (on ThinkSmart™ One Cable)

Chipset

Chipset

Intel SoC (System on Chip) platform

Memory

Max Memory

Up to 16GB DDR4-2400

Memory Slots

Memory soldered to systemboard, no slots, dual-channel

Memory Type

DDR4-2400

Storage

Storage Support

One drive, up to 256GB SSD

Storage Type**

Disk Type	Interface
M.2 2242 SSD	PCIe® NVMe®, PCIe 3.0 x4
M.2 2280 SSD	PCIe NVMe, PCIe 3.0 x4

Removable Storage

Card Reader

No card reader

Multi-Media

Audio Chip

High Definition (HD) Audio

Speakers

4 premium tuned speakers, 3W x4

Microphone

Four omnidirectional microphones for 360° audio capture

Camera

No camera

Sensor**Sensors**

IR-based proximity sensor, automatically dim / brighten display (detection angle: +/- 45% (from display); detection distance: 3 meters at maximum)

Power Supply**Power Supply**

Power	Type	Efficiency	Key Features
90W	Adapter	88%	Autosensing

DESIGN**Display****Display**

Size	Resolution	Touch	Brightness	Surface	Aspect Ratio	Contrast Ratio	Refresh Rate	Key Features
10.1"	FHD (1920x1200)	Multi-touch	320 nits	Anti-glare	16:10	1000:1	60Hz	Smudge resistant, 360° rotation support

Touchscreen

TDDI technology, supports 10-point touch

Input Device**Keyboard**

No keyboard

Mouse

No mouse

Mechanical**LED indicators**

360 degree LED ring on hinge neck and LED on top, indicates status for all users in the room

Buttons

Power button

Dimensions (WxDxH)^[1]

240 x 200 x 185.3 mm (9.45 x 7.87 x 7.30 inches)

Packaging Dimensions (WxDxH)

297x 332 x 262 mm (11.7 x 13.07 x 10.31 inches)

Weight^[2]

Around 2.45 kg (5.4 lbs)

Packaging Weight

Around 4.62 kg (10.19 lbs)

Case Color

Raven black and red bottom

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Network

Ethernet

Gigabit Ethernet, Intel Ethernet Connection I219-LM, 1x RJ-45, supports Wake-on-LAN

WLAN + Bluetooth^[1]

Intel Wireless-AC 9560, 802.11ac Dual Band 2x2 Wi-Fi® + Bluetooth 5.0, Intel vPro® technology support, M.2 card

Notes:

[1] Bluetooth 5.1 is hardware ready but may run at a lower version due to OS limitations.

Ports^[1]

Front Ports

1x headphone / microphone combo jack (3.5mm)

Rear Ports

None

Left Ports^[2]

- 1x USB-C® 3.2 Gen 2
- 2x USB 3.2 Gen 2
- 1x HDMI-in
- 1x DisplayPort™ Out
- 1x Ethernet (RJ-45)
- 1x power connector

Right Ports

None

One Cable

Ports on ThinkSmart One Cable: 3x USB 3.2 Gen 1, 1x USB-C 3.2 Gen 1 (Data transfer only), 2x HDMI out, 1x Ethernet (RJ-45), 1x power connector

Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

[2] ThinkSmart One Cable occupies the ports on base (2x USB, 1x USB-C, 1x DP, 1x Ethernet, 1x Power DC-IN).

SECURITY & PRIVACY

Security

Security Chip

Discrete TPM 2.0, TCG certified

Physical Locks

- Cable lock box and secure cable management door to secure the cable connections
- Kensington® Security Slot™, 3 x 7 mm

BIOS Security

- Supervisor password

- System management password

MANAGEABILITY

System Management

System Management

Intel vPro with Intel AMT 12

SERVICE

Warranty^[1]

Base Warranty**

- 3-year limited onsite service
- 3-year limited onsite service with Premier Support

Notes:

[1] The warranty upgrades may be bundled with some models, please check the "Included upgrade" column in the specific model's configurations. For more service extensions, please go to <https://smartfind.lenovo.com/>. To learn more details of warranty policy, please access <https://pcsupport.lenovo.com/warranty>.

SOFTWARE

Preinstalled Software

Preinstalled Software

- Microsoft® Teams Rooms (for MT 11H0 / 11H1)
- Zoom Rooms (for MT 11H2 / 11H3)

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

RoHS compliant

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

Other Certifications

Other Certifications

TÜV Rheinland® Ultra Low Noise

- This is a telepresence technology product.
- Feature with ** means that only one offering listed under the feature is configured on selected models.
- Feature with *** means that one or more offerings listed under the feature could be configured on selected models.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. **LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow**

you.

- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

