

A group of four business professionals are gathered around a large wooden conference table in a bright, modern office. A woman with curly hair is pointing at a laptop screen, while a man in a suit looks on with a smile. Another man in a blue shirt is holding a document, and a fourth man is partially visible on the left. The table is cluttered with various items: a laptop, a smartphone, a blue mug, a pair of glasses, a red folder with a bar chart, a green marker, and some sticky notes. Large windows in the background let in natural light, creating a warm and collaborative atmosphere.

#CONNECTBETTER

Table of Contents

| | | | |
|------------|-----------------------------|------------|--------------------------|
| About AVer | Why AVer | Room Types | Video Conference Cameras |
| 03 | 04 | 06 | 08 |
| Videobars | Video Collaboration Systems | Software | Specifications |
| 18 | 22 | 30 | 32 |

About AVer

AVer is an award-winning provider of visual collaboration solutions that improve productivity and enrich lives. To increase the competitive advantage for your business, AVer solutions leverage the power of visual communications to help people connect better.

Our business product portfolio includes PTZ Cameras, HD Video Conferencing solutions, and videobars. We strive to provide industry leading service and support that exceeds our customer's expectations. Additionally, our products meet the highest certification or collaboration standards with Microsoft Teams, Zoom or Google Meet.





Why AVer

We take pride in creating high-quality products. That's why we are recognized by so many as a key partner.

AVer's award-winning USB conference cameras help your team connect and collaborate like never before. With years of manufacturing experience, we provide professional, high-quality products and services.

With our Advanced Replacement Program*, if your system is not performing during the first year, a replacement unit will be sent to you within 72 hours.

Combined with the industry's only 3 Year Warranty this ensures total protection and peace of mind at no additional cost.

Phone: 1.877.528.7824 Email: support.usa@aver.com

*North America only. Visit averusa.com/support for more details.

Our Try & Buy Program is a full 30-day evaluation of any AVer product with ZERO risks. This allows you to experience the superior performance of AVer products.

We ship out a brand new unit for you to try, if the product fits your needs then we will work with a partner to help you purchase our product. If not, we provide return shipping at no cost.

Room Types



Home Office

A home office is a private workspace in a residence used for remote work, hybrid schedules, or self-employment. It can also serve as a study or project/hobby space.

A30, CAM130, VB130



Huddle Room

A huddle room is a small and private meeting area seating **1-4 people**. Depending on its size and needs, an organization may have several huddle rooms.

A30, CAM130, VB130, VB342 Pro2, FONE540



Small Conference

Small sized collaboration spaces are larger than huddle spaces and can accommodate **4-7 people**. These are corner offices, study spaces, meeting rooms or larger home offices.

CAM130, VB130, VB342 Pro, FONE540



Medium Conference

Medium sized conference rooms are your standard conference room size built to accommodate **7-12 people**. This is your typical executive conference room.

CAM520 Pro2, CAM520 Pro3, CAM550, CAM570, VC520 Pro2, VC550, VB342 Pro, VB350, FONE540



Large Conference

Large conference rooms are equipped with teleconferencing and collaboration technologies. They can accommodate **12-20 people**. Most offices only have one of these spaces. This is the space where meetings including all employees happen.

CAM520 Pro2, CAM520 Pro3, CAM550, CAM570, VB350, VC520 Pro2, VC550, FONE540





VIDEO CONFERENCE CAMERAS


Connect anywhere, anytime with AVer's Plug and Play devices.
Collaborate with your team face-to-face.

A30

All-In-One Video Conference Camera

| |
|--|
| 1080p @30fps HD in a Video Call |
| 23x digital zoom |
| AI Image Rotation |
| Superior AI Audio Technology |
| Built-in Microphone & Speaker |
| Webcam & Doc Cam |
| Auxiliary Microphone & USB Camera Inputs |
| HDMI & USB |

| | | |
|---|---|--|
| 4K | Lighting | Built-in Microphone & Speaker |
| 4K |  |  |
| Plug-N-Play | 5 Year Warranty | |
|  |  | |



Aver SKU: COMCAM130

CAM130

Compact 4K Camera Perfect for Remote Work

| |
|---|
| Crystal-clear ultra HD 4K |
| 4X digital zoom |
| Dual FOV: 90° or 120° |
| SmartFrame technology |
| Adjustable 11 level intelligent fill lighting |
| Built-in microphone |
| Manual privacy shutter |

| | | |
|--|--|---|
| 4K | Lighting | Dual FOV |
| 4K |  |  |
| SmartFrame | 3 Year Warranty | |
|  |  | |



CAM130

4K Content Camera Bundle for Whiteboards

- 4K Whiteboard Camera
- Dual FOV: 90° or 120°
- Keystone Correction to flatten the view of a whiteboard
- Adjustable whiteboard mount with multiple installation options to fit all sizes of whiteboards or IFP's DMI display link, power 12v DC, expansion mic port, RS232, 3.5mm phone-in
- Innovative technology allows participants to see "through" the presenter for an unobstructed view of the whiteboard

4K

Plug-N-Play

Lighting

3 Year Warranty

Dual FOV

zoom

Certified

ClickShare

BARCO

Certified for

Microsoft Teams



AVer SKU: COMCN130B



AVer SKU: COM520PR2

CAM520 Pro2

Enterprise-Grade Camera with Improved SmartFrame

- 1080p @30fps HD in a Video Call
- 12X optical zoom (18X total zoom)
- 84.5° FOV
- 100 camera presets
- RS232, VISCA integration
- Improved SmartFrame technology with face and body detection
- PoE+ enabled Ethernet port
- IP video streaming

1080P

HD

Plug-N-Play

SmartFrame

3 Year Warranty

POE+

zoom

Certified

ClickShare

BARCO

Certified for

Microsoft Teams

CERTIFIED FOR

RingCentral

CAM520 Pro3

Enterprise Grade Conferencing Camera

| |
|--|
| 1080p @60fps Full HD in a Video Call |
| 12X optical zoom (36X total zoom) |
| 80.5° FOV |
| Sony WDR Sensor |
| Advanced AI: SmartComposition, Upgraded SmartFrame, Preset Framing |
| HDMI / USB 3.1 / RTSP/RTMP / RS232, VISCA Integration |
| PoE+ enabled Ethernet port |
| IP video streaming |


1080P
HD


Plug-N-Play

SmartComposition

3 Year Warranty

PoE+







AVer SKU: COM520PR3

CAM550

Enterprise-Grade 4K Dual Lens Camera with AI Technology

| |
|---|
| 1080p @30fps HD in a Video Call |
| 4K Optical Lens / 84.5° FOV w/ 4K Sony Exmor Sensor |
| Secondary 90° Wide-Angle viewfinder lens strictly for people counting |
| 12X optical zoom (18X total zoom) |
| Advanced AI : SmartFrame, People Counting, Gesture Control |
| USB model: LAN, USB type B to PC, power 12v DC, RS232, HDMI-Out |
| Network port for power, virtual USB, and management |



AVer SKU: COMCN130B


4K
4K


Plug-N-Play


12X Zoom


3 Year Warranty


Dual Lens











CAM570

4K Dual Lens Audio Tracking Camera
for Medium and Large Rooms

- 1080p @30fps HD in a Video Call
- 4k Optical Lens / 90° FOV w/ 4K Sony Exmor Sensor
- Secondary Wide-Angle Viewfinder Lens strictly for people counting
- 12X optical zoom (36X total zoom)
- Built in MIC array for Voice-Tracking capabilities
- Advanced AI: SmartFrame, People Counting, Voice-Tracking, Voice-Framing, Gesture Control
- USB model: LAN, USB type B to PC, power 12v DC, RS232, HDMI-Out
- Network port for power, virtual USB, and management

4K Ultra HD

4K

Plug-N-Play

Voice-Tracking

3 Year Warranty

USB 3.1



AVer SKU: COMCAM570



VIDEOBARS

High-quality camera, microphone and speaker in an all-in-one videobar for huddle and small rooms.



VB130

4K Videobar with Built-in Lighting

- 4K video & 4X digital zoom
- Dual FOV: 90° or 120°
- Advanced AI with SmartFrame & SmartSpeaker technology
- Adjustable 5 level intelligent fill lighting
- 5-microphone array with acoustics
- Adjustable audio fence
- Powerful speaker for acoustic clarity
- Built-in TV mount

4K

SmartFrame

Lighting

3 Year Warranty

Dual FOV

zoom

Certified

ClickShare

BARCO

Certified for

Microsoft Teams

CERTIFIED FOR

RingCentral

TNT

AWARDSHOW

Communication

SOLUTIONS

2021

TMC LABS

Innovation

TECH&LEARNING

AVer SKU: COMMVB130



AVer SKU: COMVB342P



VB342 Pro

Enterprise-Grade PTZ Video Bar

- 1080p 60fps High-Definition video
- 4K Optical Lens / 90° FOV w/ 4K Sony Exmor Sensor
- Up to 12X (3X optical) zoom lens w/ mechanical pan and tilt
- Beam forming mic array w/ powerful 6w speakers
- Advanced AI : SmartFrame, SmartSpeaker, People Counting
- USB Model: LAN, USB 3.0 type B to PC, USB 2.0 for BT dongle, USB HUB, HDMI display link, power 12v DC, expansion mic port, RS232, 3.5mm phone-in
- TV & wall mount, credenza stand

4K

4K

Plug-N-Play

12X Zoom

3 Year Warranty

USB 3.1

zoom

Certified

ClickShare

BARCO





Certified for

Microsoft Teams

VB350

Enterprise-Grade PTZ Video Bar

| |
|--|
| 1080p 60fps High-Definition video |
| 18X Hybrid Zoom |
| 4K Dual Lens |
| 113° FOV |
| Sony 4K Sensor |
| Advanced AI : SmartFrame, SmartSpeaker, Conversation View, Presentation Mode, Audio Tracking |
| 14 Beamforming Mic Array with Audio Fencing |
| HDMI / LAN / USB 3.1 / RS232 / Visca Over IP / RTSP/RTMP |

| | | |
|---|---|--|
| 4K 4K Plug-N-Play | SmartFrame  3 Year Warranty | HDMI  |
|  |  | |

| | |
|---|---|
|  |  |
|---|---|



AVer SKU: COMMVB350



VIDEO COLLABORATION SYSTEMS

Affordable, high-quality, professional USB video collaboration systems for mid to large conference rooms.

VC520 Pro2

Next Level of Audio and Video Conferencing System

| |
|---|
| 1080p @30fps HD in a Video Call |
| 84.5° FOV |
| 100 camera presets |
| Improved SmartFrame technology with face and body detection |
| Full-duplex speakerphone with touch controls |
| 15 ft audio pickup for each speakerphone with noise suppression and AGC |
| Expansion speakerphone and microphone accessories |

1080P
HD

Plug-N-Play

12X Zoom

3 Year Warranty

Daisy Chain

zoom
Certified

certified by
ClickShare
Customer
BRIDGE

CERTIFIED FOR
RingCentral

2021
GOLDEN BRIDGE
AWARDS



AVer SKU: COMVCPRO2

VC520 Pro2

Microsoft Teams Edition

| |
|---|
| 1080p @30fps HD in a Video Call |
| 24X total zoom (12X optical zoom)* |
| 84.5° FOV |
| 100 camera presets |
| Improved SmartFrame technology with face and body detection |
| Full-duplex microphone array with echo cancellation |
| Touch controls for volume down/up, mute, call, hang-up, and Teams button* |
| Dual omni-directional microphone array |

*with PTZ2 app

1080P
HD

Plug-N-Play

12X Zoom

3 Year Warranty

Daisy Chain

zoom
Certified

certified by
ClickShare
Customer
BRIDGE

CERTIFIED FOR
RingCentral

2021
GOLDEN BRIDGE
AWARDS

Certified for
Microsoft Teams







AVer SKU: COMVCMST

VC550

4K Dual Lens PTZ Conference Camera with AI Technology & Speakerphone

| |
|--|
| 1080p @30fps HD in a Video Call |
| 24*X Zoom: 12X optical 2X digital zoom |
| Secondary 90 Wide-Angle viewfinder lens strictly for people counting |
| Advanced AI: SmartFrame, People Counting, Gesture Control |
| Simultaneous 3-way output: USB, HDMI and IP connections |
| Two omni-directional microphones support 360° pickup |
| Full duplex microphone array speakerphone |

| | |
|---|---|
| 3.5 mm Line-in Jack | Daisy-Chain Additional Microphones |
|  |  |
| Plug-N-Play | 1 Year Warranty |
|  |  |







AVer SKU: COMMVC550

FONE540

Advanced Audio that Adapts to Any Meeting Space

| |
|---|
| Full-duplex microphone array speakerphone |
| Two omnidirectional microphones support 360° pickup |
| Advanced noise suppression silences background noises |
| Smart LED indicators to show call status |
| Touch controls for volume down/up, mute, phone input, call, and hang up |
| LAN for IP remote access |

| | |
|--|--|
| 3.5 mm Line-in Jack | Daisy-Chain Additional Microphones |
|  |  |
| Plug-N-Play | 1 Year Warranty |
|  |  |




AVer SKU: COMFON540




EZ Manager Software

Easy to Use and Efficient Central Management Tool

| |
|--|
| Remotely manage firmware and software upgrades |
| Backup and restore camera configurations |
| Intuitive, responsive user interface |
| Manage multiple devices and locations |
| View camera connection status |
| Scalable for 1 to 10,000 cameras |



Software

| EZ Manager Software | PTZApp 2 | OBS Plugin |
|--|---|--|
| <div><ul style="list-style-type: none">— Free download for Windows & Mac— Available for Firefox and Chrome— Remotely manage firmware and software upgrades— Backup and restore camera configurations— Intuitive and responsive user interface— Manage multiple devices and locations</div> | <div><ul style="list-style-type: none">— Free download for Windows and Mac— Firmware field upgrade— Advanced device settings and diagnostics— Upgraded interface for full control of AVer USB camera functions— Enable virtual streaming when applicable</div> | <div><ul style="list-style-type: none">— Free download for Windows— Host a professional and efficient livestream— Full PTZ & SmartFrame controls— Switch between 10 camera presets</div> |



Specifications



| | A30 | CAM130 | CAM520 Pro2 | CAM520 Pro3 |
|----------------------|--------------------------|--------------------------|-------------------------|------------------------------|
| Part Number | VISIONA30 | COMCAM130 | COM520PR2 | COM520PR3 |
| Room Type | Home Office/Huddle/Small | Home Office/Huddle/Small | Medium/Large | Medium/Large |
| Document Camera | ✓ | ✗ | ✗ | ✗ |
| Zoom | 23X Digital | 4X Digital | 18X Total (12X Optical) | 18X Total (12X Optical) |
| FOV | 110° | 120° Wide or 90° Depth | 84.5° | 80.5° |
| Pan | ePTZ | ePTZ | ±170° | ±170° |
| Tilt | ePTZ | ePTZ | 90° (up) / 30° (down) | 90° (up) / 30° (down) |
| Display Resolution | 4K | 4K | 1080p | 1080p |
| SmartFrame | ✗ | ✓ | ✓ | ✓ |
| SmartComposition | ✗ | ✗ | ✗ | ✓ |
| SmartSpeaker | ✗ | ✗ | ✗ | ✗ |
| Preset Framing | ✗ | ✓ | ✓ | ✓ |
| Presets | ✗ | 10 | 10 | 10 on remote (128 vis RS232) |
| Microphone | ✓ | 2 | ✗ | ✗ |
| Speaker | ✓ | ✗ | ✗ | ✗ |
| Audio Fencing | ✗ | ✗ | ✗ | ✗ |
| WDR | ✗ | ✓ | ✓ | ✓ |
| HDMI | ✓ | ✗ | ✗ | ✓ |
| Bluetooth | ✗ | ✗ | ✗ | ✗ |
| Ethernet | ✗ | ✗ | ✓ | ✓ |
| PoE+ | ✗ | ✗ | ✓ | ✓ |
| RS232 | ✗ | ✗ | ✓ | ✓ |
| IP Streaming | ✗ | ✗ | ✓ | ✓ |
| Gesture Control | ✗ | ✗ | ✗ | ✗ |
| Fill Light | ✓ | ✓ | ✗ | ✗ |
| Remote | ✓ | ✗ | ✓ | ✓ |
| Privacy Shutter | ✓ | ✓ | ✗ | ✗ |
| Warranty | 5 Year | 3 year | 3 year | 3 year |
| Advanced Replacement | 1 year | 1 year | 1 year | 1 year |



| CAM550 | CAM570 | VB130 | VB342 Pro | VB350 |
|-------------------------------------|-------------------------------------|--------------------------|------------------------------------|-----------------|
| COMCAM550 | COMCAM570 | COMMB130 | COMVB342P | COMMB350 |
| Medium/Large | Medium/Large | Home Office/Huddle/Small | Huddle/Medium | Medium/Large |
| ✗ | ✗ | ✗ | ✗ | ✗ |
| 24X Total (12X Optical, 2X Digital) | 36X Total (12X Optical, 3X Digital) | 4X Digital | 15X Total (3X Optical, 5X Digital) | 18X Hybrid Zoom |
| 85°(Optical lens); 95°(AI lens) | 90°(Optical lens); 95°(AI lens) | 120° Wide or 90° Depth | 92° | 113° |
| ±170° | ±170° | ePTZ | Mechanical Pan 180° | 165° |
| 120° | 120° | ePTZ | Mechanical Tilt 105° | 101° |
| 4K | 4K | 4K | 4K | 4K |
| ✓ (Auto Framing, Preset Tracking) | ✓ (Auto Framing, Preset Tracking) | ✓ | ✓ | ✓ |
| ✗ | ✗ | ✗ | ✗ | ✗ |
| ✗ | ✓ | ✓ | ✓ | ✓ |
| ✓ | ✓ | ✓ | ✓ | ✓ |
| 10 on remote (128 via RS232) | 10 on remote (128 via RS232) | 10 | 10 | ✓ |
| ✗ | ✗ | 5 | 10pcs | 14 |
| ✗ | ✗ | ✓ | ✓ | ✓ |
| ✗ | ✗ | ✓ | ✓ | ✓ |
| ✓ | ✓ | ✓ | ✓ | ✓ |
| HDMI Out (1080p/60) | HDMI Out (1080p/60) | ✗ | ✓ | ✓ |
| ✗ | ✗ | ✓ (optional dongle) | ✓(optional dongle) | ✗ |
| ✓ | ✓ | ✓ | ✓ | ✓ |
| ✓ | ✓ | ✗ | ✗ | ✗ |
| ✓ | ✓ | ✗ | ✓ | ✓ |
| ✓ | ✓ | ✗ | ✗ | ✓ |
| ✓ | ✓ | ✓ | ✓ | ✓ |
| ✗ | ✗ | ✓ | ✗ | ✗ |
| 3 year | 3 year | 3 year | 3 year | 3 year |
| 1 year | 1 year | 1 year | 1 year | 1 year |



| | VC520 Pro2 | VC550 |
|----------------------|-------------------------|-------------------------------------|
| Part Number | COMVCPRO2 | COMMVC550 |
| Room Type | Medium/Large | Medium/Large |
| Document Camera | ✗ | ✗ |
| Zoom | 18X Total (12X Optical) | 24X Total (12X Optical, 2X Digital) |
| FOV | 84.5° | 85°(Optical lens); 95°(AI lens) |
| Pan | ±170° | ±170° |
| Tilt | 90° (up) / 30° (down) | 120° |
| Display Resolution | 1080p | 4K |
| SmartFrame | ✓ | ✓ (Auto Framing, Preset Tracking) |
| SmartComposition | ✗ | ✗ |
| SmartSpeaker | ✗ | ✗ |
| Preset Framing | ✓ | ✓ |
| Presets | 10 | 10 on remote (128 via RS232) |
| Microphone | 2 | 2 |
| Speaker | ✓ | ✓ |
| Audio Fencing | ✗ | ✗ |
| WDR | ✓ | ✓ |
| HDMI | ✗ | HDMI 1.3 (1080p/30/60) |
| Bluetooth | ✗ | ✓ |
| Ethernet | ✓ | ✓ |
| PoE+ | ✗ | ✓ |
| RS232 | ✓ | ✓ |
| IP Streaming | ✓ | ✓ |
| Gesture Control | ✗ | ✓ |
| Fill Light | ✗ | ✗ |
| Remote | ✓ | ✓ |
| Privacy Shutter | ✗ | ✗ |
| Warranty | 3 year | 3 year |
| Advanced Replacement | 1 year | 1 year |

| | FONE540 |
|----------------------|-------------------------------|
| Part Number | COMFON540 |
| Room Type | All Sizes |
| Microphone | 2 Omnidirectional Microphones |
| Pickup Distance | 5m |
| Speakerphone | ✓ |
| Bluetooth | ✗ |
| Warranty | 2 year |
| Advanced Replacement | 1 year |



To learn more, visit averusa.com/business

AVer Information Inc. Americas averusa.com 668 Mission Court Fremont, CA 94539 Toll Free 1.877.528.7824

©2023 by AVer Information Inc. All rights reserved. All products and features are subject to change. All brand names and logos are trademarks of their respective companies.



Facebook: AVerVideoConference
Twitter: @AVerVC
LinkedIn: AVerUSA
Youtube: AVer USA