

Product Line
FORTIRACK

Type
RM-FR-T20

Supported Models **FORTIGATE 90G**
FORTIGATE 91G

DIMENSIONS 1U

COLOR RAL 9003 White

PRODUCT DIMENSIONS **44 x 482 x 217 mm**

(height x width x depth) **1.73 x 18.98 x 8.54 in**



MOUNTING INSTRUCTIONS

1. Remove the 4 rubber feet from the bottom of the FortiGate.
2. Place up to two appliance backwards on the rack & fix the appliance with the 2 bolts from the bottom and tighten it lightly.
3. Place up to 4 power supplies on the extension rack.
4. To install the power supplies, put the zip ties through the designated holes, place the power supplies on the rack between the zip ties and tighten firmly.
5. Tie the excess length of the power cable down with the 3rd zip tie.
6. Slide the extension part into the rack as shown on the picture and fix the two parts with two washers and M3x6mm bolts.
7. Place your FortiRack in your 19 inch rack.

Please ensure proper ventilation according to the network appliance manufacturer guidelines.

PACKAGE CONTENTS

Qty	Description
1	FortiRack
1	FortiRack extension part
12	Zip ties
6	Bolts M3x6mm
2	Nut



**Consider the environment,
recycle where applicable.**

Rackmount.IT rack mount kits are RoHS compliant, developed & manufactured in the Netherlands and made of first quality parts.

In case of problems please contact your reseller or sales@rackmount.it.

Revision 1 - 27-10-2023