



Poly Sync 10 Microsoft Teams Certified Speakerphone (77P34AA)

Overview

Instant conference room

Turn your home office into a conference room. The all-in-one Poly Sync 10 USB speakerphone delivers high-quality audio that's great for voice and music. Its two-microphone array reduces surrounding noise for better conference calls.



Simple to use

User-friendly, worry-free operation for the confidence of knowing your calls will go smoothly. Easy-to-use touch-sensitive controls, clear LED indicators, and clear, bright call status light bar.

Works the way you do

Durable and space saving, this IP64 dust- and water-resistant speakerphone fits your workstyle. Use your favorite collaboration apps without hassle and free up table space with its slim, dynamic design.

Hear and be heard

Dynamic audio that makes conference calls seamless and clear. A two-microphone array keeps surrounding noise out of your call. And full-duplex audio enables simultaneous conversations so everyone on the call can be heard.

Features

Two-microphone array

Experience conference calls with outside noise and distractions tuned out. A two-microphone array focuses on your voice — not the surrounding noise.

Hi-fi audio and power amplifier

Expect high-quality performance for calls and while listening to podcasts or music thanks to the reliable, enterprise-grade hi-fi audio and power amplifier.

Full-duplex audio

Collaboration gets tough when one voice dominates the conversation. Full-duplex audio makes simultaneous conversations a breeze.

Touch-sensitive controls

It's easy to spot and control your call status directly on the device. Stay in control with easy-to-use, touch-sensitive controls and a clear LED indicator.

Dust-and-water resistant

Accidents happen — especially on the go. That's why durability is top of mind. Protect your investment from real-life hazards with a device that's IP64 dust and water-resistant.

Certified for Microsoft Teams

Full Microsoft Teams certification takes your Microsoft Teams experience to the next level with a button for instant access to the app and more.

Additional specifications

Audio	Full duplex audio; Noise and echo reduction; Up to 5 ft / 1.5 m microphone pickup range; Ideal for up to 3 m x 3 m room sizes; Bass reflect with dual passive radiators
Cable length	71.5 cm
Cable length (imperial)	28 in
Cartons per layer	10
Cartons per pallet	160
Certifications and compliances	CE; FCC; Rohs; IP64
Color	Silver
Compatibility	Compatible with PCs via USB-A cable and USB-C® adapter
Compatible Operating Systems	Windows 10; macOS
Connection type	USB Type-C®; USB Type-A
Country of origin	Made in China
ECCN	EAR99
HTS code	8518302000
Indicator light	On call
Management Software	Poly Lens; Plantronics Manager Pro suites (Asset Management and Adoption); Plantronics Hub (desktop)
Manufacturer Warranty	Poly standard two-year limited warranty
Master carton upc code	10017229191041
Microphone bandwidth	100 Hz to 7.8 kHz
Microphone type	Two-microphone steerable array
Minimum System Requirements	USB Type-A port; USB Type-C® port
Minimum dimensions (W x D x H)	7.2 x 3.5 x 1.3 in
Minimum dimensions (W x D x H)	18.2 x 8.9 x 3.3 cm
Multiple order quantity	10
Number of microphones	2
Package dimensions (W x D x H)	93 x 198 x 40 mm
Package dimensions (W x D x H)	1.77 x 3.74 x 6.22 in
Package weight	348 g
Package weight	0.76 lb
Pallet (layers)	16
Pallet dimensions	40 x 48 x 70.39 in
Pallet dimensions (W x D x H)	101.6 x 121.9 x 178.8 cm

Pallet weight	617.36 kg
Pallet weight	1361.04 lb
Products per pallet	1600
Products per pallet layer	160
Speaker size	40 mm
Special features	UC certified; Highly visible status light bar for 360 degree call status indication
Touch user controls	Call/answer end; Mute; Volume +/-; Microsoft Teams
UNSPSC code	43191515
UPC number	017229175884
Weight	0.617 lb
Weight	0.28 kg
What's in the box	Poly Sync 10-M; User guide; USB Type-A cable; USB-C® adapter

Services

Poly Services

★ : Recommended

Poly Support Services

3 year Poly+ Sync 10 Service	PSYNC10312 ★
1 year Poly Elite Sync 10 Service	ESYNC10112
3 year Next Business Day Hardware Advance Replacement Sync 10 Poly DaaS Service	DSYNC10DS3
3 year Partner Poly+ Sync 10 Service	PSYNC10362

Audio

★ : Recommended

Audio Accessories

Poly Sync 20 Case	85R77AA
Poly Sync 40 Charging Stand with Power Supply	85T35AA
Poly Sync 40 Charging Stand with Universal Power Supply	85R78AA
Poly Sync 40 Desk Mount	85R80AA
Poly Sync 60 Universal Power Supply	85R82AA

Disclaimer — Copyright

Bluetooth® is a trademark owned by its proprietor and used by HP Inc. under license.

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.