

OVERVIEW



1. Joystick	7. USB-B 3.2 Gen 1
2. Source Key	8. USB 3.2 Gen 1
3. Power connector	9. Audio-out (3.5mm)
4. HDMI 1.4	10. USB 3.2 Gen 1
5. DP 1.2	11. USB 3.2 Gen 1
6. VGA	12. USB 3.2 Gen 1

PERFORMANCE

Panel

Panel

3-side NearEdgeless, In-Plane Switching

Backlight

WLED

Display Size

27 inches

Max View Area

WxH: 597.9 x 336.3 mm

Resolution

1920 x 1080

Aspect Ratio

16:9

Pixel Pitch

0.3114 x 0.3114 mm

Dot / Pixel Per Inch

82 dpi

Brightness

300 cd/m²

Contrast Ratio

- Contrast Ratio: 1000:1
- Dynamic Contrast Ratio: 3M:1

View Angle (H / V)

Horizontal: 178°, Vertical: 178°

Response Time

- Extreme Mode: 4 ms
- Normal Mode: 6 ms
- Off Mode: 14 ms

Refresh Rate

60Hz

Color Gamut

99% sRGB

Color Support

16.7 Million

Color Depth

8-bit (6-bit+FRC)

Screen Surface Treatment

Anti-glare

Operating System

Operating System

- Windows® 10 Support
- Windows 11 Support

Multi-Media

Camera

- No bundled webcam (Support ThinkVision® MC 60 Monitor Webcam, sold separately)
- ThinkVision MC 60 monitor webcam (Some models only)

Speakers

Optional Modular Soundbar support (MS30 Monitor Soundbar)

Power Supply

Power Consumption

- Typical / Max: 24W / 65W
- Sleep / Off mode: <0.5W
- Switch-off Mode: <0.3W
- Energy Star Power On: 15W
- Energy Star TEC: 50kWh
- Internal Power Supply

Voltage Required

AC 100 to 240 V (50-60Hz)

Special Features

Special Features

- Natural Low Blue Light
- Lenovo® ThinkColour (Lenovo Display Accessories and Display Manager) Support
Lenovo ThinkColour supports Windows 10 & 11, Mac OS, and Windows On Arm (functions vary across systems).
Lenovo Display Accessories and Display Manager is formerly Lenovo Display Control Center.

DESIGN

Mechanical

ThinkCentre® M Series Support

ThinkCentre M Series Tiny Support

For supporting Tiny devices, additional Tiny Clamp Bracket Mounting Kit III (PN: 4XF1K72399) are needed (sold separately).

Bezel Width

- Side: 2mm
- Top / Bottom: 2mm / 17.6mm

Cable Management

Support

Case Color

Raven black

Dimensions (WxDxH)^[1]

Models	Dimensions
Lowest Position	611.9 x 204.5 x 389.3 mm (24.09 x 8.05 x 15.33 inches)
Highest Position	611.9 x 204.5 x 544.3 mm (24.09 x 8.05 x 21.43 inches)
Head Only	611.9 x 50.0 x 362.5 mm (24.08 x 1.97 x 14.27 inches)

Packaging Dimensions (WxDxH)

690 x 148 x 525 mm (21.17 x 5.83 x 20.67 inches)

Weight^[2]

Models	Weight
Monitor Head Only	4.9 kg (10.8 lbs)
Monitor With Stand	6.9 kg (15.2 lbs)

Packaging Weight

10.1 kg (22.27 lbs)

Mounting

Supports VESA mount 100mm

Stand

Supports -5° to +23.5° tilt, left & right 45 swivel, 90° pivot, up to 155mm lift

In the Box

- Monitor with Stand

- 1x DP Cable (1.8m) (No for Brazil)
- 1x HDMI® Cable (1.8m) (Brazil only)
- 1x USB-A to USB-B Cable (1.8m)
- 1x Power cable (1.8m)
- Quick Setup Guide

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Ports^[1]

Rear Ports

- 1x USB-B 3.2 Gen 1, USB upstream
- 4x USB 3.2 Gen 1 (1x BC 1.2), USB downstream
- 1x HDMI 1.4
- 1x DisplayPort™ 1.2
- 1x VGA
- 1x Power Connector
- 1x audio-out (3.5mm)

Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

SECURITY & PRIVACY

Security

Physical Locks

Kensington® Security Slot™

SERVICE

Warranty

Base Warranty

3-year limited warranty

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

- ENERGY STAR® Certified
- EPEAT™ Gold Registered^[2]
- RoHS compliant
- TCO Certified
- TCO edge

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

[2] EPEAT is registered where applicable, please see <https://www.epeat.net> for registration status by country.

Other Certifications

Other Certifications

- Eyesafe® Certified
- TÜV Rheinland® Eye Comfort Certification
- TÜV Rheinland Low Blue Light (Hardware Solution)

- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

