

Minuteman Value for Non-Critical Equipment

Minuteman Power Technologies' line of MMS Series Surge Protectors offer the value and features customers demand, and provide the opportunity to build a complete protection system with a single trusted name.

Your ultimate defense against power surges and voltage fluctuations! Minuteman's state-of-the-art surge protector products are designed to safeguard your valuable electronic devices, providing them with the utmost protection during unexpected power disturbances.

Designed to Protect:

- **Computers**
Desktops, Printers, Laptops, Scanners, Routers
- **Home Audio/Video**
TVs, DVRs & VCRs, Stereo Systems, Broadband, Satellite Boxes
- **Communications**
Phones, Voicemail, VoIP systems
- **Home Appliances**
Home automation devices, Charging stations, Lamps & Lighting, Kitchen appliances
- **Security and Access Control**
CCTV cameras, Access control devices, Recorders

Key Features

- **Superior Surge Protection:** Shield your devices from lightning, grid fluctuations, and malfunctions.
- **Multiple Outlets:** Accommodate computers, laptops, printers, chargers, and more
- **Overload Protection:** Prevent excessive currents, avoiding hazards and damage.
- **Sleek and Space-Saving Design:** Fits behind furniture, keeps workspace tidy
- **LED Indicators:** At-a-glance grounding and surge protection status.
- **Durable Construction:** High-quality materials for lasting protection.
- **EMI/RFI Noise Filtration:** EMinimize interference for uninterrupted performance.

NEW MMS Series Surge Protectors

MMS Model Number	MMS-DSK6U3	MMS-POD4U4	MMS-STP8U3	MMS-WAL6U3
Electrical Rating	15A, 120V, 1800 W	15A, 120V, 1800 W	15A, 120V, 1800 Wa	15A, 120V, 1800 W
Joule Rating	1080J	1080J	2160J	1080J
Outlet Quantity	6	4	8	6
Rotating Outlets	-	4	-	-
Switch/Circuit Breaker	2 position on/off switch/ 15A AC circuit breaker			-
Dimensions (L x W x H) inches	5.3 x 2.7 x 5.2	7.83 x 7.17 x 2.36	11.22 x 3.54 x 1.44	5.43 x 3.86 x 2.23
Surge Protection Mode	L-N, L-G, N-G			
UL Clamping Voltage	500V	500V, 500V, 600V	400V, 500V, 500V	TBD
Maximum Peak Current	72,000A	72,000A	144,000A	72,000A
Max Spike Voltage	6KV	6KV	6KV	6KV
	EMI/RFI Noise Filter			
Frequency	150KHz-100MHz	150KHz-100MHz	150KHz-100MHz	150KHz-100MHz
Attenuation	Up to 40dB	Up to 40dB	Up to 40dB	Up to 40dB
	USB Charging			
Format / Qty.	2 - Type A / 1 - Type C	3 - Type A / 1 - Type C / 1 - MicroUSB	2 - Type A / 1 - Type C	2 - Type A / 1 - Type C
Charge Capacity (Combined)	24W Max	36W Max	30W Max	20W Max
Power Cord Length	6 ft.	6 ft.	6 ft.	-
Right-angle Input Plug	Yes	Yes	Yes	Yes
Surge Protected Indicator	Yes	Yes	Yes	Yes
Ground OK Indicator	-	-	-	-
Surge Circuit Shutdown	Yes	Yes	Yes	Yes
Power Safety Shutdown (L-N)	Yes	Yes	Yes	Yes
Cord Management	-	-	-	-
Accessories	-	-	-	-
Certifications	UL1449, UL1363, cUL, FCC Class B, RoHS			
Warranty	Limited Lifetime			

MMS Series Surge Protector Specifications

MMS Model Number	MMS110	MMS362P	MMS370	MMS780R	MMS7100RT	MMS660S
Electrical Rating	15A, 120V, 1800 W	15A, 120V, 1800 W	15A, 120V, 1800 W	15A, 120V, 1800 W	15A, 120V, 1800 W	15A, 120V, 1800 W
Joule Rating	540J	241J	1080J	2160J	2880J	540J
Outlet Quantity	1	6	7	8	10	6
Rotating Outlets	-	-	-	6	5	-
Switch/Circuit Breaker	-	2 position on/off switch/ 15A AC circuit breaker				-
Dimensions (L x W x H) inches	2.13 x 2 x 2.38	10.79 x 3.27 x 3.15	12.76 x 4.25 x 1.77	14.02 x 3.54 x 2.28	12.52 x 4.41 x 1.89	9.14 x 5.95 x 1.07
Receptacle Covers	-	-	Yes	-	-	-
Surge Protection Mode	L-N, L-G, N-G	L-N	L-N, L-G, N-G	L-N, L-G, N-G	L-N, L-G, N-G	L-N, L-G, N-G
UL Clamping Voltage	500V	800V	400V	330V, 400V, 400V	330V, 400V, 400V	500V
Maximum Peak Current	36,000A	12,000A	72,000A/96,000A	144,000A	180,000A	36,000A
Max Spike Voltage	6KV	6KV	6KV	6KV	6KV	6KV
	EMI/RFI Noise Filter					
Frequency	150KHz-100MHz	-	150KHz-100MHz	150KHz-100MHz	150KHz-100MHz	150KHz-100MHz
Attenuation	Up to 40dB	-	Up to 40dB	Up to 40dB	Up to 58dB	Up to 40dB
	Telephone / Fax / Modem					
Jack Type	-	-	-	-	RJ11/6P2C (1 in/1 out)	-
Energy	-	-	-	-	160J	-
Line Protection	-	-	-	-	1 Line	-
Power Cord Length	-	3 ft.	6 ft.	7 ft.	7 ft.	-
Right-angle Input Plug	-	Yes	Yes	No	No	-
Surge Protected Indicator	Yes	-	Yes	Yes	Yes	Yes
Ground OK Indicator	Yes	-	Yes	Yes	Yes	Yes
Surge Circuit Shutdown	Yes	-	Yes	Yes	Yes	Yes
Power Safety Shutdown (L-N)	Yes	-	Yes	Yes	Yes	Yes
Cord Management	-	-	-	Yes	Yes	-
Accessories	-	-	-	-	Tel Cable x 1	-
Certifications	UL1449, UL1363, cUL, FCC Class B, RoHS					
Warranty	Limited Lifetime	2 Years	Limited Lifetime	Limited Lifetime	Limited Lifetime	Limited Lifetime