


OVERVIEW



1. Headphone / microphone combo jack (3.5mm)	5. Microphone
2. Speaker	6. Card slot
3. USB-C 2.0 (support data transfer and charging)	7. Power button
4. Volume buttons	

Notes:

- Card slot is for microSD card (WLAN model) or nano-SIM + microSD card (WWAN model)

PERFORMANCE

Processor

Processor

Processor Name	Cores	Max Frequency	Memory Support	Processor Graphics
MediaTek Helio G88	Octa-core 2x A75 + 6x A55	A75@2.0GHz / A55@1.8GHz	LPDDR4x	Arm Mali-G52 MC2 GPU

Operating System

Operating System^[1]

Android™ 13 or later

Notes:

[1] Expect OS upgrades until Android™ 15 and security patches until January 2028. For latest software upgrade plan, please visit <https://support.lenovo.com/solutions/ht501098>.

Graphics

Graphics

Arm Mali-G52 MC2 GPU

Memory

Max Memory

- 4GB soldered memory, not upgradable
- 8GB soldered memory, not upgradable

Memory Type

LPDDR4x

Storage

Storage Support

- 64GB eMMC 5.1 on systemboard
- 128GB eMMC 5.1 on systemboard
- microSD card, supports up to 1TB (exFAT)

Storage Type

Disk Type	Interface	Offering
Flash Memory	eMMC 5.1	64GB / 128GB

Removable Storage

Card Reader**

- Nano-SIM + microSD card slot (WWAN models)
- microSD card slot (WLAN models)

Multi-Media

Speakers

4 speakers, 1W x4, optimized with Dolby Atmos®

Microphone

Single microphone

Camera**

- Front 8.0MP, f/2.0, 78° FoV (field of view) fixed focus, face unlock, video recording 1080P@30fps
- Rear 13.0MP, f/2.2, 80° FoV, video recording 1080p@30fps, autofocus
- Front 8.0MP, f/2.0, 78° FoV (field of view) fixed focus, face unlock, video recording 1080P@30fps
- Rear 8.0MP, f/2.0, 77° FoV, video recording 1080p@30fps, autofocus

VoiceCall

- Voice call^[1]
- No support

Notes:

[1] Use of Voice call requires cellular data plan. Voice call functionality details may vary based on local operator network, data and messaging services. Please contact your carriers for details.

Sensor

Vibration Motor

No support

Sensors

- Accelerometer (G) sensor
- Ambient light sensor (ALS)
- Gyroscope sensor
- Hall sensor

Battery

Battery

Integrated Li-Polymer 7040mAh (typical) battery

Max Battery Life^[1]

Video playback: 10 hr

Web browsing: 10 hr

Music playback: 50 hr

Notes:

[1] All battery life claims are approximate and based on internal testing under optimal laboratory and network conditions. Actual battery performance will vary depending on numerous factors including product configuration and usage, software, operating conditions, wireless functionality, power management settings, screen brightness and other factors. The maximum capacity of the battery will naturally decrease with time and usage.

Power Adapter

Power Adapter

- 5V/2A (10W) AC adapter, 100-240V, 50-60Hz
- No power adapter^[1]

Notes:

[1] In compliance with EU regulations, our product no longer includes an in-box charging adapter. We encourage you to re-use your existing USB Power Delivery (PD) compatible charger.

For optimal performance, ensure your compatible charger delivers between a minimum of 10 Watts required by the product, and a maximum of 15 Watts to achieve the fastest charging speed.

The Lenovo® 68W USB-C® Wall Charger is recommended for this product. However, other compatible USB PD chargers can also be used.

For a detailed list of compatible chargers, please visit www.Lenovo.com/support.

DESIGN

Display

Display^[1]

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Refresh Rate	Viewing Angle (L/R/U/D)
11" ^[2]	WUXGA (1920x1200)	Multi-touch	IPS	400nits	Anti-fingerprint	16:10	1500:1	72% NTSC	90Hz	80° / 80° / 80° / 80°

Touchscreen

In-cell multi-touch, supports 10-point touch

Notes:

[1] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

[2] Measured diagonally, Lenovo® Tab K11's screen size is 11" in the full rectangle without accounting for the rounded corners. Actual viewable area is less due to the rounded corners.

Input Device

Pen

- Lenovo® Tab Pen, 4096 levels of pressure sensitivity, tilt detection, palm rejection
- No pen (purchase separately)^[1]

Notes:

[1] For details upon pen compatibility, please check the file "Lenovo® Android™ Tablet - Option Compatibility Matrix" from <https://support.lenovo.com/solutions/accs-guide>. Pen availability may vary by country / region.

Mechanical

Dimensions (WxDxH)^[1]

255.26 x 166.31 x 7.15 mm (10.05 x 6.55 x 0.28 inches)

Weight^[2]

Around 465 g (1.03 lbs)

Case Color**

- Luna grey
- Seafoam green

Case Material

Metal

Buttons

- Power button
- Volume buttons

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Network

WLAN + Bluetooth®

Wi-Fi® 5, 802.11ac 1x1 Wi-Fi® + Bluetooth® 5.1

WWAN

- 4G LTE
- No support

Cellular Bands^[1]

GSM: B2/B3/B5/B8

WCDMA: B1/B2/B4(for NA)/B5(B6/B19)/B8

FDD LTE: B1/B2/B3(expanded Band3)/B4/B5(B19)/B7/B8/B12/B13/B14(for NA)/B17(for NA)/B25/B20/B26/B28(a+b)/B66/B29(for NA)/B30(for NA)/B71(for NA)

TDD LTE: B38/B40/B41 Full Band

Wi-Fi® Direct

Support

Wi-Fi® Display

Support

Location Services**

Models	Location
WLAN models	GPS + GLONASS + Galileo
WWAN models	GPS + GLONASS + Galileo + A-GPS

Notes:

[1] For WWAN models

Ports^[1]

Standard Ports

- 1x USB-C® 2.0 (support data transfer and charging)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Card slot

Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4® 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

SERVICE

Warranty

Base Warranty^{**[1]}

- 1-year carry-in service
- 1-year mail-in service
- 1-year courier service
- 2-year (1-yr battery) carry-in service
- 2-year (2-yr battery) carry-in service
- 2-year (1-yr battery) courier service
- 2-year (2-yr battery) courier or carry-in service

Notes:

[1] For warranty upgrade service, please go to <https://smartfind.lenovo.com/services>. To learn more details of warranty policy, please access <https://support.lenovo.com/warrantylookup/warrantypolicy>.

ACCESSORIES

Bundled Accessories

Bundled Accessories^{***[1]}

- Film
- Folio case
- Glass screen protector
- Lenovo® Tab Pen
- None

Notes:

[1] For more compatible accessories, please check the file "Lenovo® Android™ Tablet - Option Compatibility Matrix" from <https://support.lenovo.com/solutions/accs-guide>.

OPERATING REQUIREMENTS

Operating Environment

Temperature

Operating: 0°C (32°F) to 40°C (104°F)

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

- ENERGY STAR® 8.0 (only available for TB330FU)
- ErP Lot 6
- ErP Lot 26
- RoHS compliant

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit <https://compliance.lenovo.com>.

Other Certifications

Dust and Water Resistant

IP52

Other Certifications

- TÜV Rheinland® Low Blue Light (Hardware Solution)
- android enterprise recommended

SOFTWARE

Preinstalled Software

Preinstalled Software^[1]

- Calculator
- Calendar
- Camera
- Chrome
- Clock
- Contacts
- Entertainment Space
- Files by Google
- Find my device
- Gboard
- Gmail
- Google
- Google Assistant
- Google Drive
- Google Maps
- Google Meet
- Google One
- Google Play Books
- Google Play Games
- Google Podcasts
- Google TV
- Kids Space^[2]
- Lenovo® Freestyle
- Lenovo® Vantage
- Messages
- MyScript® Calculator
- Nebo®
- News
- Notepad
- Pay (Wallet)
- Photos
- Recorder
- Safety
- WPS
- Weather
- YouTube
- YouTube Kids
- YouTube Music

Notes:

[1] Actual application availability varies by country/region.

[2] Books and video content not available in all regions. Video content subject to availability of YouTube Kids app. Books content requires the Play Books app. Availability of apps, books, and video content may change without notice. Google Assistant not available in Google Kids Space. Google Kids Space requires a Google Account for your child. Parental controls require the Family Link app on a supported Android™, Chromebook, or iOS device.

Additional Software

Additional Software^[1]

- Access to device management features via SDK
- Additional security patch extensions
- Android™ zero-touch enrollment
- Cloud-based customization & configuration
- Commercial grade SW with limited monetization content^[2]
- Customization management of firmware updates

Notes:

[1] To acquire additional software service, please contact Lenovo® local sales or business partners for the steps of deployment. License/activation fees may be applicable.

[2] Google Mobile Services (GMS) contents are allowed; manufacturer related monetization and push contents are limited.

- Feature with ** means that only one offering listed under the feature is configured on selected models.
- Feature with *** means that one or more offerings listed under the feature could be configured on selected models.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

