

Poly Savi 7210 Office DECT 1920-1930 MHz Single Ear Headset



*Product image may differ from actual product

Move freely, get more done

Help office workers be more productive – it's easier than you think. The Savi 7200 office series of DECT™ wireless headsets for desk phones are crowd pleasers that let workers roam far. Compatible with 800+ desk phones, they're cost effective, too.

Hands-free productivity

Everyone in the office could use more flexibility. They can roam confidently 400 ft / 120 m from the headset base with up to 12 hours of talk time. And collaboration is simple, since teams can conference up to four headsets on a single base.

Easy integration

Savi 7200 wireless headsets offer instant integration with over 800 analog and IP desk phones from industry leading makers – including a wide range of phones that Poly offers.

DECT™ Adaptive Power

Optimize range, save power, and maximize office space with the DECT™ adaptive power system. It automatically adjusts wireless signal strength based on distance from the headset base.

Featuring Roam farther

Give workers more flexibility and hands-free productivity with a roaming range of up to 120 m / 400 ft from the headset base.

12 hours talk time

Build more confidence into every call with up to 12 hours of talk time with each charge.

Training made easy

Collaboration is easier with conferencing of up to 4 headsets on one base.

Charge indicator

Provide the peace of mind that comes from knowing headsets are always fully charged with the headset docking charge indicator.

Keep conversations private

Help make every conversation clearer, with a flexible noise-canceling microphone boom that's easy to adjust for optimal placement on every call.

Desk phone compatibility

Take advantage of one-stop shopping, since these headsets are compatible with the wide range of phones that Poly offers.

Poly Savi 7210 Office DECT 1920-1930 MHz Single Ear Headset



*Product image may differ from actual product

Specifications

Connectivity and communications

Wireless range: Up to 400 ft from base

Paired devices: Up to 4

Connection type: Wireless: DECT™; Wired: RJ-11

Ear cushions: Artificial leather (surface material)

Headphone type: On-ear (monaural)

User interface features

Button user controls: Call answer/end; Mute; Volume +/-;
Power on/off

Audio

Acoustic protection technology: SoundGuard¹

Microphone type: Noise cancelling

Microphone bandwidth: 100 Hz to 6.8 kHz

Speaker bandwidth: 300 Hz to 3.3 kHz (narrowband mode);
100 Hz to 6.8 kHz (wideband mode)

Charge time: <3 hours

Power supply

Battery life: Up to 12 hours (talk time)

Battery description: Rechargeable Li-ion polymer

Battery capacity: 250 mAh

Charging type:

Poly Savi 7210 Office DECT 1920-1930 MHz Single Ear Headset

Specifications

Management

Management software:

Poly Lens

Poly Lens app (desktop)

Weight and dimensions

Product Primary Color: Black

Weight: 0.23 lb

Product dimensions: 6.1 x 6.53 x 2.63 in

Package weight: 0.66 lb

Package dimensions: 7.48 x 8.26 x 2.16 in

Master carton quantity: 5

Master carton dimension: 10.39 x 13.26 x 8.89 in

Master carton weight: 7.8 lb

Cartons per layer: 10

Pallet (layers): 6

Cartons per pallet: 60

Products per layer: 50

Products per pallet: 300

Pallet weight: 628.62 lb

Pallet dimensions: 40 x 48 x 58.66 in

UPC number: 197497169119

Product number: 7W6D4AA

Product name: Poly Savi 7210 Office DECT 1920-1930 MHz
Single Ear Headset

Warranty

Poly standard two-year limited warranty

Country of origin

Country of origin: Made in Mexico

What is in the box

Wireless headset

Office base

AC power adapter

AC interchangeable plugs

Telephone cable

Safety guide

Warranty card

Quick start guide

Poly Savi 7210 Office DECT 1920-1930 MHz Single Ear Headset

Footnotes

Messaging Footnotes

² HL10, sold separately. ¹ Sold separately.

Technical Specifications Footnotes

¹ Protects against Acoustic Shock by limiting sounds to below 118 dBA.