



**C2G**  
**10ft (3m) C2G Plus Series TAA-Compliant High Speed HDMI® Cable with Ethernet - 4K 60Hz (Available for Preorder)**  
 Part No. AVD\_CG\_C2G50111

This HDMI® cable meets stringent TAA compliant requirements and is approved for use in United States government projects and facilities. C2G Plus Series High Speed HDMI Cable with Ethernet - 4K 60Hz is perfect for connecting a wide variety of devices from computers to projectors and monitors, or any audio video applications requiring high speed HDMI features and video resolutions up to 4K (4096 x 2160) at 60Hz.



This cable series offers features like 3D video, deep color, Dolby® True HD, DTS-HD Master Audio, and up to 32 audio channels for a multi-dimensional immersive audio experience. Simultaneously deliver dual video streams to multiple users on the same screen while delivering multi-stream audio to up to four users, giving a dynamic synchronization of video and audio streams. All these features will catch the audience’s attention, providing a more realistic video experience.

These cables support the updated Consumer Electronic Control (CEC) commands library, allowing communication between devices connected through the HDMI ports. The cable’s Ethernet capabilities allow Ethernet-enabled HDMI devices to access interactive online content or update device firmware. The gold- plated connectors on the cable allow for better shielding, increased electrical conductivity, and durability. Lastly, this fully functional, high bandwidth cable has been tested to perform at industry standards and is backed by a lifetime warranty.

## Features & Benefits

### TAA Compliant

Supports all HDMI 2.0 features including resolutions up to 4K (4096 x 2160) at 60hz, which means higher quality video for viewing your screen content.

Supports 32 audio channels for an immersive audio experience

Gold plated connectors for increased electrical conductivity and enhanced durability

### Premium High Speed HDMI® Certification

Supports 3D video for a more appealing and realistic video experience

Supports CEC extensions for control of consumer electronics devices through a single control point

Backed by a Lifetime Warranty for peace of mind

## Specifications

### General Info

Product Line	C2G	Color	Black
UPC Number	757120501114	Country Of Origin	Taiwan, Province Of China
Warranty Type	Lifetime	Type	Cable

### Dimensions

Product Length US	10.0 FT	Cable Length	10 ft
Outside Diameter	5.8 mm		

### Listing Agencies / 3rd Party Agencies

REACH Compliant	Yes
-----------------	-----

### Buy American Act Compliance

TAA Compliant	Yes
---------------	-----

### Additional Information

RoHS Compliant	Yes
----------------	-----

### Technical Information

Jacket Material	PVC	Wire Gauge	30 AWG
Video Resolution	4K 60Hz	Bend Radius	48 mm
Conductor Size	30 AWG	Cable Type	High Speed HDMI
Jacket Rating	VW-1 Rated	Temperature Rating	80°C
Insulation Resistance	10 MOhm	Cable Diameter	5.8 mm
Data Transfer Rate	18 Gbps	Connector 2	HDMI Male
Connector 1	HDMI Male	Video Output Support	HDMI
Operating Temperature	-20°-80°C	Video Input Support	HDMI
Voltage	30.0 V	Storage Temperature	-10° - 55° C