

Lenovo V14 G4 ABP

Whether it's a busy executive, a creative freelancer, or a remote worker, this laptop is packed with features to enhance their work experience wherever they are. Equipped with up to AMD Ryzen 5 processors, it ensures seamless multitasking and great performance. Executives can effortlessly manage data-heavy presentations, while freelancers can smoothly run resource-intensive creative applications. The 14-inch Full HD display offers crisp visuals and wide viewing angles, perfect for content creators and designers who need accurate colors and sharp details even while on the move.



With a variety of ports including USB 3.2, USB-C, and HDMI, consultants can easily connect to projectors, while photographers can transfer files swiftly. Consultants and financial professionals can work confidently with security features like TPM 2.0 and supervisor password, knowing their information is secure.

Frequent travelers and field researchers can trust in its ability to withstand the bumps and drops of a busy lifestyle, thanks to its military-grade durability. They can stay connected wherever they go with Wi-Fi6 technology.

The device comes with up to 45Wh integrated Li-Polymer battery that supports rapid charge, enabling professionals to work from anywhere without worrying about the power plug.

Lenovo devices that are a class apart

The Lenovo V Series provides security, data protection and productivity features in an affordable package.

Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Return To Depot Repair Warranty

No-hassle repair process at a Lenovo service center
 Lenovo pays for all shipping between the customer and service facility
 Avoid unplanned operational expense with a simple annual fee

Accessories

Lenovo Business Casual 17" Backpack

Functional three-compartment backpack with clean and modern design, crafted from water-repellent fabric
 Dedicated and soft padded PC compartment fits up to 17.3" laptops
 Hidden anti-theft pocket on the back to keep valuable items secure; comes with a luggage strap for easy travel



PN: 4X40X54260

Lenovo Professional Wireless Keyboard & Mouse

Wireless keyboard and mouse combo with reliable 2.4 GHz wireless connection
 Slim keyboard with number pad, noise-suppression design, dedicated media controls & adjustable tilt legs
 Contoured design of the mouse suits both left-handed & right-handed users



PN: 4X30H56796

Lenovo V14 G4 ABP

Performance

Processor

AMD Ryzen 3/5

Operating System

Windows 11 Pro
Windows 11 Home
Windows 11 Home Single Language

Graphics

AMD Radeon Graphics (integrated)

Memory ¹

Up to 16GB DDR4-3200 offering, 1x Soldered + 1x SO-DIMM

¹The max memory is based on the test results with current Lenovo memory offerings. The system may support more memory as the technology develops.

Storage ²

Models with 38Wh battery:
up to two drives, 1x 2.5" HDD + 1x M.2 SSD
2.5" HDD up to 1TB
M.2 2242 SSD up to 512GB

Models with 45Wh battery:
up to 1x 512GB M.2 2242 PCIe NVMe SSD

²The storage capacity supported is based on the test results with current Lenovo storage offerings. The system may support larger storage as the technology develops.

Audio

High Definition (HD) Audio
Stereo speakers, 1.5W x2, Dolby Audio
Dual-microphone array with noise-cancelling

Camera

HD 720p, with privacy shutter

Battery ³

38Wh (up to 7.4 hr) or 45Wh (up to 9.5 hr) battery
Rapid Charge

³Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter

65W round tip adapter
65W USB-C adapter, PD 3.0

Design

Display ⁴

14" FHD (1920x1080) TN 16:9 Anti-glare
- 250nit, 45% NTSC, 60Hz

14" FHD (1920x1080) IPS 16:9 Anti-glare
- 300nits, 45% NTSC, 60Hz

⁴IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Keyboard

6-row, spill-resistant

Touchpad

Mylar surface touchpad
62 x 104 mm (2.44 x 4.09 inches)

Dimensions ⁵

324.2 x 215.2 x 19.9 mm (12.76 x 8.47 x 0.78 inches)

⁵The system dimensions may vary depending on configurations.

Weight ⁶

Starting at 1.41 kg (3.1 lbs)

⁶The system weight is approximate and may vary depending on configurations

Color

Business black
Iron grey

Case material

PC + ABS (top)
PC + ABS (bottom)

Connectivity

Ethernet

Gigabit onboard Ethernet

WLAN + Bluetooth ⁷

802.11ac or 802.11ax (Wi-Fi 6)
Bluetooth 5.1

⁷Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitations.

Ports

1x USB 2.0
1x USB 3.2 Gen 1
1x USB-C 3.2 Gen 1 (data, PD 3.0, DP 1.2)
1x HDMI, up to 2.5K/60Hz
1x Ethernet (RJ-45)
1x Headphone / microphone combo jack (3.5mm)
1x Power connector

Docking

Supports USB-C docking

Security & Privacy

Firmware TPM 2.0
Kensington Nano Security Slot
Camera privacy shutter

Certifications

Green Certifications ^{8 9}

EPEAT Silver Registered*
ENERGY STAR 8.0*
ErP Lot 6
ErP Lot 26
TCO Certified*
RoHS compliant

⁸The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁹EPEAT is registered where applicable, please see <https://www.epeat.net> for registration status by country.

Other Certifications

TÜV Rheinland Low Blue Light (Software Solution)
MIL-STD-810H