LIQUID COOLING

MAG CORELIQUID I360 / WHITE

RADIATE YOUR COOLING





SPECIFICATIONS

Radiator Size	360 mm
Radiator Dimensions (WxDxH)	394 x 120 x 27 mm / 15.5 x 4.7 x 1.06 inches
Radiator Material	Aluminum
Water Cooling Tube Material	EPDM
Number of Fans	3
Fan Dimensions (WxDxH)	120 x 120 x 25 mm / 4.7 x 4.7 x 0.98 inches
Fan Air Flow	70.7 CFM
Fan Bearing	Loop Dynamic Bearing(LDB)
Fan Life Expectancy	30,000 hrs@40℃
Fan Rated Current	0.2A (MAX:0.3A)
Fan Power Consumption	2.4W (MAX:3.6W)
PWM Mode	Yes
Cable Length (PWM Cable)	550 / 500 mm; 21.65 / 19.69 inches
Fan Connector	5V ARGB 3-PIN Header
Block Lighting	ARGB Gen2
Fan Lighting	ARGB Gen2
Pump Life Expectancy	50,000 hours in typical use
Pump Noise Level	20 dBA (avg.)
Pump Rated Current	0.32A (Max: 0.5A)
Pump Power Consumption	3.84W (Max: 6W)
Pump Speed	3400 RPM ± 10%
Pump Connector	PWM 4-PIN Header 5V ARGB 3-PIN Header (Female) 5V ARGB 3-PIN Header (male)
Cold Plate Material	Copper
Block Dimensions (WxDxH)	69.1 x 74 x 62.45 mm
Intel Socket Support	LGA 1150/1151/1155/1156/1200/1700/1851
AMD Socket Support	AM5 / AM4
Accessories	Thermal paste x 1

Generated 2024-12-20, check for the latest version www.msi.com/datasheet. The information provided in this document is intended for informational purposes only and is subject to change without notice.

© 2024 Micro-Star Int'l Co.Ltd. MSI is a registered trademark of Micro-Star Int'l Co.Ltd. All rights reserved.