

Poly Studio X70 All-In-One Video Bar with TC10 Controller Kit No Radio GSA/TAA (8L539AA)



Enable meeting equality

The Poly Studio X70, all-in-one video bar, offers quality audio and video performance in large meeting spaces. Enjoy pinpoint-accurate automatic framing and tracking modes, distraction-free audio technology, and lifelike 4K UltraHD video.



Crystal clear video

Ready for your close-up? This all-in-one video bar transitions seamlessly between wide and narrow-angle cameras, showing everyone in your large meeting spaces in sharp detail.

Production-quality performance

Keep your eye on the action with Poly DirectorAI intelligent camera framing and NoiseBlockAI technology — all powered by machine learning. Get advanced vocal pickup from our next gen microphones. Easily share content over wired or wireless connections.

Featuring

Smart camera tech

Give everyone in hybrid meetings an equal seat at the virtual table using a choice of framing modes with Poly DirectorAI smart camera technology.

4K cameras

No one looks their best with pixilated video. Enjoy richer, more lifelike meeting experiences with 4K UltraHD video.

Noise blocking innovations

Outside noise and side conversations can quickly derail a hybrid meeting. Keep background noise in check with Poly NoiseBlockAI and Acoustic Fence technologies.

Beamforming microphone

Make communicating effortless for everyone on the call, with a next-generation beamforming microphone array that clearly picks up all voices in a room.

Easy management via Poly Lens

Take control of your deployment from anywhere via remote management with Poly Lens cloud-based device management software.

Specifications

Audio	Poly NoiseBlockAI technology; Poly Acoustic Fence technology
Dimensions (W x D x H)	840.18 x 135.38 x 117.33 mm
Dimensions (W x D x H)	33.1 x 5.3 x 4.6 in
Weight	3200 g
Weight	7.05 lb
Ports	1 USB Type-C® 5Gbps signaling rate; 2 USB Type-A 5Gbps signaling rate; 2 RJ-45; 1 audio-in; 1 audio-out; 2 HDMI-out 1.4 (video); 1 HDMI-in 1.4 (audio)
Power supply type	External; Auto sensing
Security management	AES 128 bits encryption; AES 256 bits encryption; H.235.6 support; Authenticated access to admin menus, web interface, and APIs; Local account password policy configuration; Security profiles; Local account and login port lockout; Secure defaults; Remote logging with support for TLS; Active directory external authentication; Binary Floor Control Protocol (BFCP)
UPC number	197497837650
Manufacturer Warranty	Poly standard one-year limited warranty
What's in the box	Poly Studio X70; Ethernet cable; Wall mount kit; 2 HDMI cable; AC power adapter

Top Recommended Displays, Accessories and Services

Poly Support Services

3 Year Poly+ Poly Studio X70 and TC10

P88155312

Messaging Footnotes

No Messaging Footnotes

Technical Specifications Footnotes

No Technical Specifications Footnotes

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

