

Technical Specifications

HP Series 5 Pro 27" QHD Monitor - 527pq




1. Power Button

Front
2. Power LED

Technical Specifications

HP Series 5 Pro 27" QHD Monitor - 527pq



Back

1. Joypad OSD button
2. Security Cable Slot
3. Power Connector
4. HDMI 2.0
5. DisplayPort™ 1.2
6. USB-B port
7. 2x SuperSpeed USB Type-A 5Gbps signaling rate
8. SuperSpeed USB Type-A 5Gbps signaling rate
9. SuperSpeed USB Type-A 5Gbps signaling rate (charging)

Technical Specifications


Model: 9D9S0UT

Panel Specifications	Display Size (Diagonal)	68.6 cm (27")	
	Viewable Diagonal Size	68.47 cm (26.96")	
	Panel Technology	IPS	
	Curvature	Flat	
	Max Refresh Rate	100 Hz	
	Native Resolution	QHD (2560 x 1440)	
	Panel Bit Depth	True 8 bit	
	Aspect Ratio	16:9	
	Brightness (Typical)	350 nits	
	Display Contrast Ratio (Static)	1500:1	
	Display Contrast Ratio (Dynamic)	10000000:1 = 10M:1	
	Flicker Free	Yes	
	Pixel Pitch	0.2331 x 0.2331 mm	
	Pixels Per Inch (PPI)	109 PPI	
	Display Colors	Up to 16.7 million colors supported <i>*Number of colors through A-FRC technology.</i>	
		Backlight Lamp Life Minimum (To Half Brightness - In Hours)	30,000 hours
		Backlight Type	Edge-lit, WLED
		Screen Treatment	Anti-glare
		Hardness	3H
		Haze	25%
	Response Time (Typical)	5ms GtG (with overdrive)	
	Horizontal Viewing Angle (Typical Cr>10)	178°	
	Vertical Viewing Angle (Typical Cr>10)	178°	
	Panel Active Area Metric (W X H)	59.67 x 33.57 cm	
	Panel Active Area Imperial (W X H)	23.49 x 13.21 in	
	NOTE: Performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.		
Color	sRGB	100%	
Color Management	Color Space	RGB 4:4:4, YCBCR 4:4:4, YCBCR 4:2:2	
	RGB Channel Adjust	Yes, Gain	
	Default Color Temperature	Neutral (6500K)	
Monitor Specifications	Bezel Type	3-sided borderless	
	Color Of Stand	Black and Silver	
	Color Of Head	Black	
	Tilt	-5 to +20°	
	Swivel	±45°	
	Pivot	±90	
	Height Adjust Range	150 mm	
	Vesa Mounting	100 mm x 100 mm	
	Security Lock	Security lock-ready	

Technical Specifications

Detachable Stand	Yes
Warranty	3/3/0 for AMS, EMEA, APJ (3/3/3 in select APJ countries)
Low Blue Light	Yes, HP Eye Ease (TÜV Low Blue Light Hardware Solution certified)
Zero Bright Dot Guarantee	No* *The HP Pixel Policy allows no bright sub-pixel defects for this display. For complete details, see http://support.hp.com/us-en/document/c00288895 .
Management Software	HP Client Management Script Library*, HP Display Center** *The Client Management Script Library must be downloaded to the connected PC to run CMSL commands. Some limitations may apply to legacy displays. Visit support.hp.com to download **Host PC requires Windows 10 and above. HP Display Center is available on the Microsoft store.
On Screen Display (OSD)	Brightness+, Color, Input, Image, Power, Menu, Management, Information, Exit
Native Resolution	QHD (2560 x 1440)
Maximum Resolution	QHD (2560 x 1440 @ 100 Hz)
Preset Graphic Modes/Supported Resolutions	640 x 480 @ 60Hz 640 x 480 @ 75Hz 720 x 400 @ 70 Hz 720 x 480 @ 60Hz 720 x 576 @ 50Hz 800 x 600 @ 60 Hz 800 x 600 @ 75 Hz 1024 x 768 @ 60 Hz 1024 x 768 @ 75 Hz 1280 x 720 @ 50Hz 1280 x 720 @ 60 Hz 1280 x 720 @ 100 Hz 1280 x 1024 @ 60 Hz 1280 x 1024 @ 75 Hz 1440 x 900 @ 60 Hz 1600 x 900 @ 60 Hz 1600 x 1200 @ 60 Hz 1680 x 1050 @ 60 Hz 1920 x 1080 @ 50Hz 1920 x 1080 @ 60 Hz 1920 x 1080 @ 75 Hz 1920 x 1080 @ 100 Hz 1920 x 1200 @ 60Hz 2560 x 1440 @ 60 Hz 2560 x 1440 @ 75 Hz 2560 x 1440 @ 100 Hz
Minimum Vertical Scan Rate	50 Hz
Maximum Vertical Scan Rate	100 Hz

Technical Specifications

	Minimum Horizontal Scan Rate	30 kHz
	Maximum Horizontal Scan Rate	152 kHz
	Maximum Pixel Clock	420 MHz
	User Programmable Modes	Yes, 21
	User-Assignable Function Buttons	Yes, 4 (6 options)
	Languages	11 (English, Spanish, German, French, Italian, Netherlands, Portuguese, Japanese, T-Chinese, S-Chinese and Russian)
Connector Types	DisplayPort™	1 DisplayPort™ 1.2
	HDMI	1 HDMI 2.0
	HDCP	Yes, DisplayPort™ and HDMI
	USB-Type-A	4 SuperSpeed USB Type-A 5Gbps signaling rate (1 charging)
	USB-B (Hub enablement)	1 USB-B
Special Features	Switch	Monitor Power button Next Active Input / Up button Information / Down button Brightness / Left button Color / Right button Menu / Enter button
	User Presets	21
	User Updateable Firmware	Yes
Power & Operating Specs	Power Supply	Internal
	Power Source	100 – 240 VAC 50/60 Hz
	Power Consumption- Max	72 W
	Energy Saving/Stand By Mode	0.5 W
	Power Consumption - Typical	30 W
Energy Star Data	Operational Mode at 100 VAC	16.5 W
	Operational Mode at 115 VAC	16.5 W
	Operational Mode at 230 VAC	16.5 W
EU Energy Efficiency Class (ErP LOT-5)	On-mode Power Consumption for Standard Dynamic Range (SDR)	21.7 W
	ErP LOT5 Energy Efficiency Class for Standard Dynamic Range (SDR)	
Operating Conditions	Operating Temperature - Celsius	5~35°C
	Operating Temperature - Fahrenheit	41– 95°F
	Non-Operating Temperature - Celsius	-40 – 65°C
	Non-Operating Temperature - Fahrenheit	-40 – 149°F
	Operating Humidity	20 – 80% Relative Humidity (non-condensing)
	Non-Operating Humidity	5~95%RH
	Operating Altitude Metric	0~5,000m
	Non-operating Altitude Metric	0~12,192m

Technical Specifications

	Operating Altitude Imperial	0~16,400ft
	Non-operating Altitude Imperial	0~40,000ft
Certifications and Compliances	Low Halogen	Yes*
		* External power supplies, WWAN modules, power cords, cables and peripherals excluded. Service parts obtained after purchase may not be Low Halogen.
	Agency Approvals and Certifications	WW application CE,CB,KC/KCC/NOM/PSB/PSE/ICES/TUV-S/ISO 9241-307/cTUVus/GS/ISC/CCC/CEL/CECP/SEPA/TCO/TCO Certified Edge/TUV HW LBL/Energy Star/Korea MEPS/EAC/VCCI/FCC/BSMI/BIS/NRCS/UAE/Ukraine/Ukraine EE/WEEE/ Australian or New Zealand DoC/EMF/California CEC/RCM/TGM Windows 11 (x64 only), Windows 10 (x64 only)
	Microsoft WHQL Certification	Yes
	ENERGY STAR® Certified	EPEAT® Gold in United States*
	EPEAT® Registered	EPEAT® registered with Climate+
	Regions need to verify by country	*EPEAT® Gold NOTE: Based on US EPEAT® registration according to IEEE 1680.1-2018 EPEAT®. Status varies by country. Visit www.epeat.net for more information.
	China Energy Label	CEL Grade 2
	TCO Certified Edge	Yes
	TCO Certified	Yes
	SmartWay Transport Partnership - NA only	Yes (NA sku)
Contains Recycled Materials	Recycled Plastics	85% ITE-derived closed loop plastic* Contains Ocean-Bound Plastic** * Recycled plastic content percentage is based on the definition set in the IEEE 1680.1-2018 standard **All plastic parts contain ocean-bound plastic. Percentage of ocean-bound plastic contained in each component varies by product.
	Recycled Metal	At least 35% recycled metal* * Recycled metal is expressed as a percentage of the total weight of the metal according to ISO 14021 definitions for metal parts over 25 grams.
	Recycled Glass	20% recycled glass* * Percentage of recycled glass in the monitor panel varies by product. Recycled glass is expressed as a percentage of the total weight of the glass.
	Recyclable Packaging (Box, packing materials)	Outside Box and corrugated cushions are 100% sustainably sourced and recyclable* & Molded Paper Pulp

Technical Specifications

Cushion inside box is 100% sustainably sourced and recyclable**

*100% outer box packaging and corrugated cushions made from sustainably sourced certified and recycled fibers.

**Molded pulp cushions contains 100% recycled wood fiber and organic materials.

		Metric	Imperial	
Unit Product/Package Specifications	Product Dimensions (Unpacked with stand) (W x D x H)	61.34 x 22.89 x 54.38 cm	24.15 x 9.01 x 21.41 in	
	Product Dimensions (Packed) (W x D x H)	69.9 x 16 x 44.6 cm	27.52 x 6.3 x 17.56 in	
	Display Head Dimensions (Unpacked without stand) (W x D x H)	61.34 x 4.69 x 35.67 cm	24.15 x 1.85 x 14.04 in	
	Base Area Footprint (w x d mm)	255.96 x 206.96 mm	10.08 x 8.15 in	
	Bezel Measurements	Top: NA Sides: NA Bottom: 10.6 mm	Top: NA Sides: NA Bottom: 4.17 in	
	Product Weight (Unpacked with stand)	6.2 kg	13.7 lb	
	Product Weight (Packed)	9.2 kg	20.3 lb	
	Product Weight (Head Only)	4.6 kg	10.1 lbs	
	Pallet Information	Pallet Dimensions (L x W x H mm)	Slip Sheet: 1130 x 709 x 2242 mm (20' ft & 40' ft) Slip Sheet: 1130 x 709 x 2242 mm (40 HQ) Pallet: 1130 x 709 x 1925 mm (20' ft & 40' ft) Pallet: 1130 x 709 x 2371 mm (40 HQ)	Slip Sheet: 44.49 x 27.91 x 88.27 inch (20' ft & 40' ft) Slip Sheet: 44.49 x 27.91 x 88.27 inch (40 HQ) Pallet: 44.49 x 27.91 x 75.79 inch (20' ft & 40' ft) Pallet: 44.49 x 27.91 x 93.35 inch (40 HQ)
		Pallet Total Weight	Slip Sheet: 326.78 kg (20' ft & 40' ft) Slip Sheet: 326.78 kg (40 HQ) Pallet: 273.54 kg (20' ft & 40' ft) Pallet: 338.3 kg (40 HQ)	Slip Sheet: 720.42 lbs (20' ft & 40' ft) Slip Sheet: 720.42 lbs (40 HQ) Pallet: 603.05 lbs (20' ft & 40' ft) Pallet: 745.83 lbs (40 HQ)
Pallet Layers		5 layers per slip sheet 4 layers or 5 layer per pallet		
Pallet Product per Layer		7 per layer (slip sheet) 7 per layer (pallet)		
Total Products per Pallet		35 sets per slip sheet 28 sets or 35 sets per pallet		
Container Load, 20-Foot		560 sets (slip sheet) 448 sets (pallet)		
Container Load, 40-Foot		1120 sets (slip sheet) 896 sets (pallet)		
Container Load, 40-Foot HighQ		1120 sets (slip sheet) 1120 sets (pallet)		

Technical Specifications

What's in the box?
AC power cord (1.83m) 5.9ft
HDMI 2.0 cable (1.8m) 5.9 ft
USB 3.0 B-A cable (1.8m)
DisplayPort™ 1.2 cable (1.8m)
Warranty
Quick Setup Poster

**User Guide and
Warranty Languages**

User Guide Languages

Warranty Languages

Arabic, Bahasa Indonesia, Bulgarian, Chinese-S, Chinese-T, Czech, Danish, Dutch, English, Estonian, Finnish, French, German, Greek, Hebrew, Hungarian, Italian, Japanese, Kazakh, Korean, Latvian, Lithuanian, Norwegian, Polish, Portuguese (Brazilian), Portuguese (Iberian), Romanian, Russian, Serbian, Slovak, Slovenian, Spanish, Swedish, Thai, Turkey, Ukrainian
English US (EN), English AP (EN-AP), English LA (EN-LA), English UK (EN-GB), Arabic (AR) -17x, Bahasa Indonesia (ID), Bosnian (BS), Bulgarian (BG), Chinese-S (CN), Chinese-T (TW), Croatian (HR), Czech (CS), Danish (DA), Dutch (NL), Estonian (ET), Finnish (FI), French Canadian (FC), French European (FR), German (DE), Greek (EL), Hebrew (HE), Hungarian (HU), Italian (IT), Japanese (JA), Kazakh (KK), Korean (KO), Latvian (LV), Lithuanian (LT), Norwegian (NO), Polish (PL), Portuguese, Brazilian (BR), Portuguese, Iberian (PT), Romanian (RO), Russian (RU), Serbian (SR), Slovak (SK), Slovenian (SL), Spanish, Castilian (ES-ES), Spanish, Latin America (ES-MX), Swedish (SV), Thai (TH)
Turkish (TR), Ukrainian (UK), Vietnamese (VI)

Technical Specifications

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Microsoft and Windows are registered trademarks or trademarks of Microsoft Corporation in the U.S. and/or other countries. ENERGY STAR is a registered trademark owned by the U.S. Environmental Protection Agency.

Summary

Change Log			
November 22, 2024	V1 to V2	Updated Added	Management Software Section Certification Section
	V2 to V3		
	V3 to V4		