

NOTE:

1.CABLE:UL20276 30AWG#6PR+30AWG#1PR+30AWG#1PR+30AWG#3C+AEB 50% COLOR BLACK OD:7.3MM MARKING:BLACK BOX CORPORATION(←25.4mm→)E223178 兄 AWM STYLE 20276 80℃ 30V VW-1 DVI CABLE C

2.CONNECTOR:DVI(24+1) MALE AUTOMATIC WIRE WELDING IRON SHELL NICKEL PLATING

3.PVC MOLDED COLOR:BLACK

4.SCREW:#4-40UNC 4*28.5MM

5.LABEL:BLACK BOX P/N LABLE

6.Dust cap

ELECTRONIC TEST:

- A. OPEN/SHORT/INTERMITTENCE:100%.
- B. INSULATION RESISTANCE 10M ohm Min.
- C. HI-POT TEST:DC 300V/10ms.
- D. CONDUCTIVE RESISTANCE: 0<L≤10FT 2 ohm(MAX)
10<L≤15FT 3 ohm(MAX)


ALL MATERIALS COMPLY WITH ROHS2(2015/863)

BBOX P/N	LENGTH
EVNDVI02-0003-R2	3FT
EVNDVI02-0006-R2	6FT
EVNDVI02-0010-R2	10FT
EVNDVI02-0015-R2	15FT

BLACK BOX

Tolerance:	APPROVED BY:	
X ±	CHECK BY:	EVNDVI02-XXXX-R2
.X ±	DRAWN BY:	Description:
.XX ±	Dong MI	DVI (24+1) M TO M CABLE
.XXX ±	DATE:	DWG. NO:
Angel:	2023.08.18	
X ±	Scale:	Unit mm SHEET: 1 OF 2
.X ±		REV:01

REV	ECN NO	DESCRIPTION	APPD.	DATE



3FT/6FT/10FT/15FT


SectionA-A

7.OPERATING TEMP: 0°C TO +45°C;

8.STORAGE TEMP: -10°C TO +80°C;

9.HUMIDITY:10-85%

PIN Assignment



BLACK BOX			
Tolerance:	APPROVED BY:		
X ±	CHECK BY:	EVNDVI02-XXXX-R2	
.X ±	DRAWN BY:	Description:	
.XX ±	Dong.MI	DVI (24+1) M TO M CABLE	
.XXX ±	DATE:	DWG. NO:	☉ ☐
Angel:	2023.09.08		
X ±	Scale:	Unit mm	SHEET: 2 OF 2
.X ±			REV: 01

REV	ECN NO	DESCRIPTION	APPD.	DATE
-----	--------	-------------	-------	------