

OVERVIEW



1. Bring your Own Meeting (BYOM) connector *	6. 2x USB-C (USB 10Gbps)
2. HDMI-in *	7. HDMI-out 2.1 TMDS
3. 3x USB-A (USB 5Gbps), with BYOM	8. Ethernet (RJ-45)
4. USB-A (Hi-Speed USB), with IP Controller	9. HDMI-out 2.1 TMDS
5. Power connector	

Notes:

- Items with * are only available on selected models

PERFORMANCE

Compute Unit

Compute Unit^[1]

Features	Information
Processor (Two Options)	(Optional 1) Intel® Core™ Ultra 5 135H, 14C (4P + 8E + 2LPE) / 18T, Max Turbo up to 4.6GHz, 18MB (Optional 2) Intel® Core™ Ultra 7 165H, 16C (6P + 8E + 2LPE) / 22T, Max Turbo up to 5.0GHz, 24MB
Operating System	Windows® 11 IoT Enterprise for Collaboration GAC 64
Graphics	Integrated Intel® Arc™ Graphics. Max Resolution: 3840x2160@60Hz(HDMI® 2.1 TMDS)
Chipset	Intel® SoC (System on Chip) platform
Memory (Two Options)	(Optional 1) 16GB (2x 8GB) DDR5 5600 SO-DIMM, Dual-Channel (Optional 2) 32GB (2x 16GB) DDR5 5600 SO-DIMM, Dual-Channel
Storage	One drive, 256GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0
Power Supply (Two Options)	(Optional 1) 135W 89% Adapter, autosensing, without BYOM (Optional 2) 170W 89% Adapter, autosensing, with BYOM
Onboard Ethernet	Gigabit Ethernet, Intel® Ethernet Connection I219-LM, 1x RJ45
WLAN + Bluetooth®	Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 Wi-Fi® + Bluetooth® 5.3, Intel® vPro® technology support, M.2 Card
Case Color	Black
Rear Ports	<ul style="list-style-type: none"> • 2x USB-C® (USB 10Gbps / 3.2 Gen 2), with 15W power supply and DisplayPort™ 1.4 • (Optional) 1x USB-C® in (USB 5Gbps / USB 3.2 Gen 1), with BYOM and 45W power supply • 3x USB-A (USB 5Gbps / USB 3.2 Gen 1) • 1x USB-A (Hi-Speed USB / USB 2.0), with IP controller • (Optional) 1x HDMI®-in • 2x HDMI®-out 2.1 TMDS • 1x Ethernet (RJ-45) • 1x Power connector
Dimension (WxDxH)	with cable management with rubber feet: 185 x 220 x 42.8 mm (7.28 x 8.66 x 1.69 inches) with cable management without rubber feet: 185 x 220 x 38 mm (7.28 x 8.66 x 1.5 inches) without cable management: 185 x 140 x 38 mm (7.28 x 5.51 x 1.5 inches)
Weight	with cable management: 1.01 kg (2.23 lbs) without cable management: 0.86 kg (1.90 lbs)
BIOS Security	<ul style="list-style-type: none"> • Supervisor password • Power-on password • Hard disk password
Security Chip	Discrete TPM 2.0, TCG certified
Physical Locks	Kensington® Security Slot™

Notes:

[1] Bring Your Own Meeting(BYOM) mode setting by BIOS setup or by ThinkSmart® Manager Portal

DESIGN

Mechanical

Component Options**

Product	Compute System	Controller	Audio Bar
ThinkSmart® Core Gen 2	1x ThinkSmart® Core Gen 2	-	-
ThinkSmart® Core Gen 2+CTRL	1x ThinkSmart® Core Gen 2	1x ThinkSmart® Controller	-
ThinkSmart® Core Gen 2+IPCTRL	1x ThinkSmart® Core Gen 2	1x Lenovo® IP Controller	-



ThinkSmart® Core Gen 2 FRK	1x ThinkSmart® Core Gen 2	1x ThinkSmart® Controller	1x ThinkSmart® Bar 180
ThinkSmart® Core Gen 2 IPFRK	1x ThinkSmart® Core Gen 2	1x Lenovo® IP Controller	1x ThinkSmart® Bar 180

Controller

ThinkSmart® Controller

Features	Information
Display	<ul style="list-style-type: none"> • 10.1" Display, 1280x800 • 10-point touch • Up to 340 nits brightness • 16:10 aspect ratio • 30° and 60° rotatable • Anti-Fingerprint, Anti-Glare
Ports	<ul style="list-style-type: none"> • 1x USB-C® (connect to compute unit, 10m USB-C® cable included) • 1x 3.5mm headphone / mic combo jack
Security	Kensington® MiniSaver Security Slot
Dimension (WxDxH)	265.5 x 13 x 168.1 mm (10.5 x 0.5 x 6.6 inches)
Weight	753.8 g (1.7 lbs)

Lenovo® IP Controller

Features	Information
Display	<ul style="list-style-type: none"> • 10.1" Display, 1280x800 • 10-point touch • Up to 340 nits brightness • 16:10 aspect ratio • 30° and 60° rotatable • Anti-Fingerprint, Anti-Glare
Ports	<ul style="list-style-type: none"> • 1x Gigabit Ethernet (RJ-45) • 1x HDMI®-in • 1x Power Connector (on Link Box) • 1x Gigabit Ethernet (RJ-45, on Link Box) • 1x HDMI® out (on Link Box) • 1x USB-B (on Link Box)
Security	Kensington® MiniSaver Security Slot
Dimension (WxDxH)	248 x 151 x 100 mm (9.76 x 5.94 x 3.94 inches)
Weight	0.97 kg (2.16 lbs)

Audio Bar

ThinkSmart® Bar 180

Features	Information
Audio	<ul style="list-style-type: none"> • 4x Speaker (2x woofer, 2x tweeter) • Stereo audio out • 80 Hz to 20 KHz frequency range
Microphone	<ul style="list-style-type: none"> • 8x microphone beamforming array • -37dBFS sensitivity • 100 Hz to 8 KHz frequency range
Camera	<ul style="list-style-type: none"> • 3x Camera • Up to 3840 x 1080@30fps • 16:10 • 13 megapixels • Panoramic 4K • 180° Horizontal FoV, 54° Vertical FoV
Ports	<ul style="list-style-type: none"> • 1x USB-C® • 1x USB-A • 1x RJ 45
Dimension (WxDxH)	650 x 80 x 125 mm (25.6 x 3.1 x 4.9 inches)

Weight	2.2 kg (4.85 lbs)
--------	-------------------

MANAGEABILITY

System Management

System Management

Intel® vPro® Enterprise

SERVICE

Warranty^[1]

Base Warranty

3-year limited onsite service

Notes:

[1] The warranty upgrades may be bundled with some models, please check the "Included upgrade" column in the specific model's configurations. For more service extensions, please go to <https://smartfind.lenovo.com/>. To learn more details of warranty policy, please access <https://support.lenovo.com/warrantylookup/warrantypolicy>.

ACCESSORIES

Bundled Accessories

Bundled Accessories***

- (Optional) External adapter cage
- (Optional) Lenovo® BYOM Cable for ThinkSmart® Core Gen 2 - USB-C® to USB-C® 3m
- (Optional) Lenovo® BYOM Cable for ThinkSmart® Core Gen 2 - USB-C® to USB-C® 5m (non-Display)
- (Optional) Removable cable management box
- (Optional) VESA mount bracket

CERTIFICATIONS

Other Certifications

Other Certifications

Microsoft® Teams Certification

SOFTWARE

Preinstalled Software

Preinstalled Software

Microsoft® Teams Rooms

- This is a telepresence technology product.
- Feature with ** means that only one option listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.
- Feature with *** means that one or more options listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. **LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without



notice.

