

Secure KVM/KM Cable Compatibility Chart

Belkin's cable solutions offer the easiest and neatest way to connect all your computers and peripherals to your Secure KVMs/KMs, providing image clarity for high-resolution applications as well as audio and USB connections. Every cable features TAA compliance, high retention gold-plated connectors, Hook and Loop wire identification straps, and a black jacket. Belkin cables add high-performance, high quality and reliability to the TAA SKVM/SKM application.



Secure KVM/KM Part Number(s)	Cable Part Number	Cable Description	Length (ft/m)	Display(s)	Cable Type	Host Connector	SKVM/KM Host Connector	Console/ Display Connector	SKVM/KM Console/ Display Connector
F1DN102KVM-UN-4 F1DN102KVM-UNN4 F1DN104KVM-UN-4 F1DN104KVM-UNN4 F1DN108KVM-UN-4 F1DN116KVM-UN-4	F1D9019b06t	Belkin TAA DP/USB/AUD SKVM CBL, DP M/M; USB A/B, 6'	6' ft / 1.8 m	Single	Combination	DP, USB-A, Audio	DP, USB-B, Audio	N/A	N/A
F1DN102KVM-DC-4 F1DN102KVM-D-4 F1DN104KVM-DC-4 F1DN104KVM-D-4 F1DN108KVM-DC-4 F1DN104KVMDCU-4 F1DN104MKVMDC-4 F1DN108MKVMDC-4 F1DN104MKVMDC4 F1DN108MKVMDC4	F1D9019b10t	Belkin TAA DP/USB/AUD SKVM CBL, DP M/M; USB A/B, 10'	10' ft / 3 m	Single	Combination	DP, USB-A, Audio	DP, USB-B, Audio	N/A	N/A
	F1DN1CCBL-CPN6t	Belkin TAA USB-C to DP/USB/ DEVICE PWR-NET CBL VID M; USB B, 6'	6' ft / 1.8 m	Single	Combination	USB-C	DP, USB-B	N/A	N/A
	F1DN1CCBL-MP10t	Belkin TAA MiniDP/USB/AUD to DP/USB/AUD SKVM CBL, 10'	10' ft / 3 m	Single	Combination	Mini DP, USB-A, Audio	DP, USB-B, Audio	N/A	N/A
	F1DN1CCBL-MP6t	Belkin TAA MiniDP/USB/AUD to DP/USB/AUD SKVM CBL, 6'	6' ft / 1.8 m	Single	Combination	Mini DP, USB-A, Audio	DP, USB-B, Audio	N/A	N/A

Secure KVM/KM Part Number(s)	Cable Part Number	Cable Description	Length (ft/m)	Display(s)	Cable Type	Host Connector	SKVM/KM Host Connector	Console/ Display Connector	SKVM/KM Console/ Display Connector
F1DN102KVM-UN-4 F1DN102KVM-UNN4 F1DN104KVM-UN-4 F1DN104KVM-UNN4 F1DN108KVM-UN-4 F1DN116KVM-UN-4	F1DN1CCBL-DH10t	Belkin TAA DVI-D/USB/AUD to High Retention HDMI/USB/AUD SKVM CBL, 10'	10' ft / 3 m	Single	Combination	DVI-D, USB-A, Audio	HDMI, USB-B, Audio	N/A	N/A
	F1DN1CCBL-DH6t	Belkin TAA DVI-D/USB/AUD to High Retention HDMI/USB/AUD SKVM CBL, 6'	6' ft / 1.8 m	Single	Combination	DVI-D, USB-A, Audio	HDMI, USB-B, Audio	N/A	N/A
	F1DN1CCBL-HH10t	Belkin TAA High Ret HDMI/USB/AUD to High Ret HDMI/USB/AUD SKVM CBL, 10'	10' ft / 3 m	Single	Combination	HDMI, USB-A, Audio	HDMI, USB-B, Audio	N/A	N/A
	F1DN1CCBL-HH6t	Belkin TAA High Ret HDMI/USB/AUD to High Ret HDMI/USB/AUD SKVM CBL, 6'	6' ft / 1.8 m	Single	Combination	HDMI, USB-A, Audio	HDMI, USB-B, Audio	N/A	N/A
	F1DN1CCBL-VH-10	Belkin VGA to HDMI/USB/AUD CBL VGA/HDMI MM, USB A/B, 10'	10' ft / 3 m	Single	Combination	VGA, USB-A, Audio	HDMI, USB-B, Audio	N/A	N/A
	F1D9022b06t	Belkin TAA USB/AUD SKVM CBL, USB A/B, 3.5mm Audio, 6'	6' ft / 1.8 m	Single	Keyboard, Mouse, Audio, Remote	USB-A, Audio	USB-B, Audio	N/A	N/A
	F1D9022b10t	Belkin TAA USB/AUD SKVM CBL, USB A/B, 3.5mm Audio, 10'	10' ft / 3 m	Single	Keyboard, Mouse, Audio, Remote	USB-A, Audio	USB-B, Audio	N/A	N/A
F1DN202KVM-UN-4 F1DN202KVM-UNN4 F1DN204KVM-UN-4 F1DN204KVM-UNN4 F1DN208KVM-UN-4 F1DN202KVM-DC-4 F1DN202KVM-D-4 F1DN204KVM-DC-4 F1DN204KVM-D-4 F1DN104MKVMDC-4 F1DN108MKVMDC-4 F1DN104MVKVMDC4 F1DN108MVKVMDC4	F1DN2CCBL-CPN6t	Belkin TAA USB-C to DUAL DP/USB/DEVICE PWR-NET CBL VID M; USB B, 6'	6' ft / 1.8 m	Dual	Combination	USB-C	2 x DP, USB-B	N/A	N/A
F1DN2CCBL-MP6t	Belkin TAA Dual-Head MiniDP/USB/AUD to DP/USB/AUD SKVM CBL, 6'	6' ft / 1.8 m	Dual	Combination	2 x Mini DP, USB-A, Audio	2 x DP, USB-B, Audio	N/A	N/A	
F1DN2CCBL-MP10t	Belkin TAA Dual-Head MiniDP/USB/AUD to DP/USB/AUD SKVM CBL, 10'	10' ft / 3 m	Dual	Combination	2 x Mini DP, USB-A, Audio	2 x DP, USB-B, Audio	N/A	N/A	

Secure KVM/KM Part Number(s)	Cable Part Number	Cable Description	Length (ft/m)	Display(s)	Cable Type	Host Connector	SKVM/KM Host Connector	Console/ Display Connector	SKVM/KM Console/ Display Connector
FIDN202KVM-UN-4 FIDN202KVM-UNN4 FIDN204KVM-UN-4 FIDN204KVM-UNN4 FIDN208KVM-UN-4	FIDN2CCBL-DH6t	Belkin TAA Dual-Head DVI-D/USB/AUD to High Ret HDMI/USB/AUD SKVM CBL, 6'	6' ft / 1.8 m	Dual	Combination	2 x DVI-D, USB-A, Audio	2 x HDMI, USB-B, Audio	N/A	N/A
	FIDN2CCBL-DH10t	Belkin TAA Dual-Head DVI-D/USB/AUD to High Ret HDMI/USB/AUD SKVM CBL, 10'	10' ft / 3 m	Dual	Combination	2 x DVI-D, USB-A, Audio	2 x HDMI, USB-B, Audio	N/A	N/A
	FIDN2CCBL-HH6t	Belkin TAA Dual-Head High Ret HDMI/USB/AUD to High Ret HDMI/USB/AUD SKVM CBL, 6'	6' ft / 1.8 m	Dual	Combination	2 x HDMI, USB-A, Audio	2 x HDMI, USB-B, Audio	N/A	N/A
	FIDN2CCBL-HH10t	Belkin TAA Dual-Head High Ret HDMI/USB/AUD to High Ret HDMI/USB/AUD SKVM CBL, 10'	10' ft / 3 m	Dual	Combination	2 x HDMI, USB-A, Audio	2 x HDMI, USB-B, Audio	N/A	N/A
	FIDN2CCBL-HH6t	Belkin TAA Dual-Head High Ret HDMI/USB/AUD to High Ret HDMI/USB/AUD SKVM CBL, 6'	6' ft / 1.8 m	Dual	Combination	2 x HDMI, USB-A, Audio	2 x HDMI, USB-B, Audio	N/A	N/A
	FIDN2CC-DHPP10t	Belkin TAA Dual-Head DVI-D/USB/AUD to High Ret HDMI/USB/AUD and DP to DP SKVM CBL, 10'	10' ft / 3 m	Dual	Combination	DP, DVI-D, USB-A, Audio	DP, HDMI, USB-B, Audio	N/A	N/A
	FIDN2CC-DHPP6t	Belkin TAA Dual-Head DVI-D/USB/AUD to High Ret HDMI/USB/AUD and DP to DP SKVM CBL, 6'	6' ft / 1.8 m	Dual	Combination	DP, DVI-D, USB-A, Audio	DP, HDMI, USB-B, Audio	N/A	N/A
	FIDN2CC-HHPP10t	Belkin TAA Dual-Head High Ret HDMI/USB/AUD to High Ret HDMI/USB/AUD and DP to DP SKVM CBL, 10'	10' ft / 3 m	Dual	Combination	DP, HDMI, USB-A, Audio	DP, HDMI, USB-B, Audio	N/A	N/A
	FIDN2CC-HHPP1t	Belkin TAA Dual-Head High Ret HDMI/USB/AUD to High Ret HDMI/USB/AUD and DP to DP SKVM CBL, 1'	1' ft / 0.3 m	Dual	Combination	DP, HDMI, USB-A, Audio	DP, HDMI, USB-B, Audio	N/A	N/A
	FIDN2CC-HHPP6t	Belkin TAA Dual-Head High Ret HDMI/USB/AUD to High Ret HDMI/USB/AUD and DP to DP SKVM CBL, 6'	6' ft / 1.8 m	Dual	Combination	DP, HDMI, USB-A, Audio	DP, HDMI, USB-B, Audio	N/A	N/A

Secure KVM/KM Part Number(s)	Cable Part Number	Cable Description	Length (ft/m)	Display(s)	Cable Type	Host Connector	SKVM/KM Host Connector	Console/ Display Connector	SKVM/KM Console/ Display Connector
F1DN102KVM-UN-4 F1DN102KVM-UNN4 F1DN104KVM-UN-4 F1DN104KVM-UNN4 F1DN108KVM-UN-4 F1DN116KVM-UN-4 F1DN202KVM-UN-4 F1DN202KVM-UNN4 F1DN204KVM-UN-4 F1DN204KVM-UNN4 F1DN208KVM-UN-4	F1DN1VCBL-DH6t	Belkin TAA High Ret HDMI 2.0 to DVI-D Video Cable, 6'	6' ft / 1.8 m	Single/ Dual	Video Only	N/A	N/A	DVI	HDMI
	F1DN1VCBL-DH10t	Belkin TAA High Ret HDMI 2.0 to DVI-D Video Cable, 10'	10' ft / 3 m	Single/ Dual	Video Only	N/A	N/A	DVI	HDMI
	F1DN1VCBL-HH6t	Belkin TAA High Ret HDMI 2.0 to High Ret HDMI 2.0 Video Cable, 6'	6' ft / 1.8 m	Single/ Dual	Video Only	N/A	N/A	HDMI	HDMI
	F1DN1VCBLF-HH6t	Belkin TAA High Ret HDMI 2.0 to High Ret HDMI 2.0 Ferrite Video Cable, 6'	6' ft / 1.8 m	Single/ Dual	Video Only	N/A	N/A	HDMI	HDMI
	F1DN1VCBL-HH10t	Belkin TAA High Ret HDMI 2.0 to High Ret HDMI 2.0 Video Cable, 10'	10' ft / 3 m	Single/ Dual	Video Only	N/A	N/A	HDMI	HDMI
	F1D9026-10	Belkin CABLE, RJ14, 6P6C, 26AWG, UNSHIELDED, DCU CBL, 10'	10' ft / 3 m	Single/ Dual	Keyboard, Mouse, Audio, Remote	N/A	N/A	N/A	N/A
	F1D9026-50	Belkin CABLE, RJ14, 6P6C, 26AWG, UNSHIELDED, DCU CBL, 50'	50' ft / 15.2 m	Single/ Dual	Keyboard, Mouse, Audio, Remote	N/A	N/A	N/A	N/A
	F1D9032-04INCH	Belkin CABLE, USB MINI AB-M/ USB A (F) K/B ADAPTER, 4"	4 in / .01 m	Single/ Dual	Keyboard, Mouse, Audio, Remote	N/A	N/A	N/A	N/A

Secure KVM/KM Part Number(s)	Cable Part Number	Cable Description	Length (ft/m)	Display(s)	Cable Type	Host Connector	SKVM/KM Host Connector	Console/ Display Connector	SKVM/KM Console/ Display Connector
F1DN102KVM-UN-4 F1DN102KVM-UNN4 F1DN104KVM-UN-4 F1DN104KVM-UNN4 F1DN108KVM-UN-4 F1DN116KVM-UN-4 F1DN202KVM-UN-4 F1DN202KVM-UNN4 F1DN204KVM-UN-4 F1DN204KVM-UNN4 F1DN208KVM-UN-4 F1DN102KVM-DC-4 F1DN102KVM-D-4 F1DN202KVM-DC-4 F1DN202KVM-D-4 F1DN104KVM-DC-4 F1DN104KVM-D-4 F1DN204KVM-DC-4 F1DN204KVM-D-4 F1DN108KVM-DC-4 F1DN208KVM-DC-4 F1DN104KVMDCU-4 F1DN204KVMDCU-4 F1DN104MKVMDC-4 F1DN108MKVMDC-4 F1DN104MKVMDC4 F1DN108MKVMDC4	F1D9020b06t	Belkin TAA Dual DP/USB/AUD SKVM CBL, DP M/M; USB A/B, 6'	6' ft / 1.8 m	Single/ Dual	Keyboard, Mouse, Audio, Remote	2 x DP, USB-A, Audio	2 x DP, USB-B, Audio	N/A	N/A
	F1D9020b10t	Belkin TAA Dual DP/USB/AUD SKVM CBL, DP M/M; USB A/B, 10'	10' ft / 3 m	Single/ Dual	Keyboard, Mouse, Audio, Remote	2 x DP, USB-A, Audio	2 x DP, USB-B, Audio	N/A	N/A
	F1DN1VCBLF-PP6t	Belkin TAA DP to DP Ferrite Video Cable, 6'	6' ft / 1.8 m	Single/ Dual	Video Only	N/A	N/A	DP	DP
	F1DN1VCBL-PH6t	Belkin TAA DP to HDMI Video Cable, 6'	6' ft / 1.8 m	Single/ Dual	Video Only	N/A	N/A	HDMI	DP
	F1DN1VCBL-PH10t	Belkin TAA DP to HDMI Video Cable, 10'	10' ft / 3 m	Single/ Dual	Video Only	N/A	N/A	HDMI	DP
	F1DN1VCBL-PP10t	Belkin TAA DP to DP Video Cable, 10'	10' ft / 3 m	Single/ Dual	Host and Video	DP	DP	DP	DP
	F1DN1VCBL-PP6t	Belkin TAA DP to DP Video Cable, 6'	6' ft / 1.8 m	Single/ Dual	Host and Video	DP	DP	DP	DP
	F1DN1USBF-6t	Belkin TAA USB A/B Ferrite Choke Cable, 6'	6' ft / 1.8 m	Single/ Dual	Keyboard, Mouse, Audio, Remote, CAC	USB-A	USB-B	N/A	N/A
	F1D9013b06t	Belkin TAA USB A/B Cable, 6'	6' ft / 1.8 m	Single/ Dual	Keyboard, Mouse, Audio, Remote, CAC	USB-A	USB-B	N/A	N/A
	F1D9013b10t	Belkin TAA USB A/B Cable, 10'	10' ft / 3 m	Single/ Dual	Keyboard, Mouse, Audio, Remote, CAC	USB-A	USB-B	N/A	N/A

Secure KVM/KM Part Number(s)	Cable Part Number	Cable Description	Length (ft/m)	Display(s)	Cable Type	Host Connector	SKVM/KM Host Connector	Console/ Display Connector	SKVM/KM Console/ Display Connector
FIDN104KVMDCU-4 FIDN204KVMDCU-4	FIDN1CCBL-C6t	Belkin TAA USB-C to USB-C Cable, 6'	6' ft / 1.8 m	Single/ Dual	Host and Video	USB-C	USB-C	N/A	N/A
	FIDN1CCBL-C10t	Belkin TAA USB-C to USB-C Cable, 10'	10' ft / 3 m	Single/ Dual	Host and Video	USB-C	USB-C	N/A	N/A
FIDN102MOD-BA-4 FIDN104MOD-BA-4 FIDN108MOD-BA-4 FIDN102MOD-DD-4 FIDN102MOD-HH-4 FIDN102MOD-PP-4 FIDN104MOD-DD-4 FIDN104MOD-HH-4 FIDN104MOD-PP-4	FIDN1MOD-HC-D06	Belkin Modular DVI Single Head Host Cable 6'	6' ft / 1.8 m	Single	Host Only - Modular	DVI, USB-A	Proprietary	N/A	N/A
	FIDN1MOD-HC-H06	Belkin Modular HDMI Single Head Host Cable 6'	6' ft / 1.8 m	Single	Host Only - Modular	HDMI, USB-A	Proprietary	N/A	N/A
	FIDN1MOD-HC-H10	Belkin Modular HDMI Single Head Host Cable 10'	10' ft / 3 m	Single	Host Only - Modular	HDMI, USB-A	Proprietary	N/A	N/A
	FIDN1MOD-HC-M06	Belkin Modular Mini DP Single Head Host Cable 6'	6' ft / 1.8 m	Single	Host Only - Modular	Mini DP, USB-A	Proprietary	N/A	N/A
	FIDN1MOD-HC-P06	Belkin Modular DP Single Head Host Cable 6'	6' ft / 1.8 m	Single	Host Only - Modular	DP, USB-A	Proprietary	N/A	N/A
	FIDN1MOD-HC-P10	Belkin Modular DP Single Head Host Cable 10'	10' ft / 3 m	Single	Host Only - Modular	DP, USB-A	Proprietary	N/A	N/A
	FIDN1MOD-HC-V06	Belkin Modular VGA w/Audio Single Head Host Cable 6'	6' ft / 1.8 m	Single	Host Only - Modular	VGA w/Audio, USB-A	Proprietary	N/A	N/A

Secure KVM/KM Part Number(s)	Cable Part Number	Cable Description	Length (ft/m)	Display(s)	Cable Type	Host Connector	SKVM/KM Host Connector	Console/ Display Connector	SKVM/KM Console/ Display Connector
F1DN202MOD-BA-4 F1DN204MOD-BA-4 F1DN208MOD-BA-4 F1DN202MOD-DD-4 F1DN202MOD-HH-4 F1DN202MOD-PP-4 F1DN204MOD-DD-4 F1DN204MOD-HH-4 F1DN204MOD-PP-4	F1DN2MOD-HC-D06	Belkin Modular DVI Dual Head Host Cable 6'	6' ft / 1.8 m	Dual	Host Only - Modular	2 x DVI, USB-A	Proprietary	N/A	N/A
	F1DN2MOD-HC-DP6	Belkin Modular DVI and DP Dual Head Host Cable 6'	6' ft / 1.8 m	Dual	Host Only - Modular	DP & DVI, USB-A	Proprietary	N/A	N/A
	F1DN2MOD-HC-H06	Belkin Modular HDMI Dual Head Host Cable 6'	6' ft / 1.8 m	Dual	Host Only - Modular	2 x HDMI, USB-A	Proprietary	N/A	N/A
	F1DN2MOD-HC-H10	Belkin Modular HDMI Dual Head Host Cable 10'	10' ft / 3 m	Dual	Host Only - Modular	2 x HDMI, USB-A	Proprietary	N/A	N/A
	F1DN2MOD-HC-HP6	Belkin Modular HDMI and DP Dual Head Host Cable 6'	6' ft / 1.8 m	Dual	Host Only - Modular	DP & HDMI, USB-A	Proprietary	N/A	N/A
	F1DN2MOD-HC-M06	Belkin Modular Mini DP Dual Head Host Cable 6'	6' ft / 1.8 m	Dual	Host Only - Modular	2 x Mini DP, USB-A	Proprietary	N/A	N/A
	F1DN2MOD-HC-P01	Belkin Modular DP Dual Head Host Cable 1'	1' ft / 0.3 m	Dual	Host Only - Modular	2 x DP, USB-A	Proprietary	N/A	N/A
	F1DN2MOD-HC-P06	Belkin Modular DP Dual Head Host Cable 6'	6' ft / 1.8 m	Dual	Host Only - Modular	2 x DP, USB-A	Proprietary	N/A	N/A
	F1DN2MOD-HC-P10	Belkin Modular DP Dual Head Host Cable 10'	10' ft / 3 m	Dual	Host Only - Modular	2 x DP, USB-A	Proprietary	N/A	N/A
	F1DN2MOD-HC-S06	Belkin Modular DP-MST Dual Head Host Cable 6'	6' ft / 1.8 m	Dual	Host Only - Modular	DP-MST, USB-A	Proprietary	N/A	N/A
F1DN2MOD-HC-V06	Belkin Modular VGA w/Audio Dual Head Host Cable 6'	6' ft / 1.8 m	Dual	Host Only - Modular	2 x VGA w/Audio, USB-A	Proprietary	N/A	N/A	

Secure KVM/KM Part Number(s)	Cable Part Number	Cable Description	Length (ft/m)	Display(s)	Cable Type	Host Connector	SKVM/KM Host Connector	Console/ Display Connector	SKVM/KM Console/ Display Connector
FIDN102MOD-BA-4 FIDN104MOD-BA-4 FIDN108MOD-BA-4	FIDN1MOD-CC-D03	Belkin Modular DVI Single Head Console Cable 3'	3' ft / 0.9 m	Single	Video Only - Modular	N/A	N/A	DVI	Proprietary
	FIDN1MOD-CC-D06	Belkin Modular DVI Single Head Console Cable 6'	6' ft / 1.8 m	Single	Video Only - Modular	N/A	N/A	DVI	Proprietary
	FIDN1MOD-CC-H03	Belkin Modular HDMI Single Head Console Cable 3'	3' ft / 0.9 m	Single	Video Only - Modular	N/A	N/A	HDMI	Proprietary
	FIDN1MOD-CC-H06	Belkin Modular HDMI Single Head Console Cable 6'	6' ft / 1.8 m	Single	Video Only - Modular	N/A	N/A	HDMI	Proprietary
	FIDN1MOD-CC-H10	Belkin Modular HDMI Single Head Console Cable 10'	10' ft / 3 m	Single	Video Only - Modular	N/A	N/A	HDMI	Proprietary
	FIDN1MOD-CC-P03	Belkin Modular DP Single Head Console Cable 3'	3' ft / 0.9 m	Single	Video Only - Modular	N/A	N/A	DP	Proprietary
	FIDN1MOD-CC-P06	Belkin Modular DP Single Head Console Cable 6'	6' ft / 1.8 m	Single	Video Only - Modular	N/A	N/A	DP	Proprietary
	FIDN1MOD-CC-P10	Belkin Modular DP Single Head Console Cable 10'	10' ft / 3 m	Single	Video Only - Modular	N/A	N/A	DP	Proprietary
	FIDN1MOD-CC-V06	Belkin Modular VGA w/Audio Single Head Console Cable 6'	6' ft / 1.8 m	Single	Video Only - Modular	N/A	N/A	VGA w/Audio	Proprietary

Secure KVM/KM Part Number(s)	Cable Part Number	Cable Description	Length (ft/m)	Display(s)	Cable Type	Host Connector	SKVM/KM Host Connector	Console/ Display Connector	SKVM/KM Console/ Display Connector
FIDN202MOD-BA-4 FIDN204MOD-BA-4 FIDN208MOD-BA-4	FIDN2MOD-CC-D03	Belkin Modular DVI Dual Head Console Cable 3'	3' ft / 0.9 m	Dual	Video Only - Modular	N/A	N/A	2 x DVI	Proprietary
	FIDN2MOD-CC-D06	Belkin Modular DVI Dual Head Console Cable 6'	6' ft / 1.8 m	Dual	Video Only - Modular	N/A	N/A	2 x DVI	Proprietary
	FIDN2MOD-CC-H03	Belkin Modular HDMI Dual Head Console Cable 3'	3' ft / 0.9 m	Dual	Video Only - Modular	N/A	N/A	2 x HDMI	Proprietary
	FIDN2MOD-CC-H06	Belkin Modular HDMI Dual Head Console Cable 6'	6' ft / 1.8 m	Dual	Video Only - Modular	N/A	N/A	2 x HDMI	Proprietary
	FIDN2MOD-CC-H10	Belkin Modular HDMI Dual Head Console Cable 10'	10' ft / 3 m	Dual	Video Only - Modular	N/A	N/A	2 x HDMI	Proprietary
	FIDN2MOD-CC-P03	Belkin Modular DP Dual Head Console Cable 3'	3' ft / 0.9 m	Dual	Video Only - Modular	N/A	N/A	2 x DP	Proprietary
	FIDN2MOD-CC-P06	Belkin Modular DP Dual Head Console Cable 6'	6' ft / 1.8 m	Dual	Video Only - Modular	N/A	N/A	2 x DP	Proprietary
	FIDN2MOD-CC-P10	Belkin Modular DP Dual Head Console Cable 10'	10' ft / 3 m	Dual	Video Only - Modular	N/A	N/A	2 x DP	Proprietary
	FIDN2MOD-CC-V06	Belkin Modular VGA w/Audio Dual Head Console Cable 6'	6' ft / 1.8 m	Dual	Video Only - Modular	N/A	N/A	2 x VGA w/Audio	Proprietary
FIDN102MOD-BA-4 FIDN104MOD-BA-4 FIDN108MOD-BA-4 FIDN202MOD-BA-4 FIDN204MOD-BA-4 FIDN208MOD-BA-4	FIDN-MOD-EXC-04	Belkin Modular Dual or Single Head Console Extension Cable 4'	4' ft / 1.8 m	Dual / Single	Video Only - Modular	N/A	N/A	N/A	N/A
	FIDN-MOD-EXH-04	Belkin Modular Dual or Single Head Host Extension Cable 4'	4' ft / 1.8 m	Dual / Single	Host Only - Modular	N/A	N/A	N/A	N/A
	FIDN2MOD-HC-U03	Belkin Modular USB-C Single/ Dual Head Host Cable 3'	3' ft / 0.3 m	Dual / Single	Host Only - Modular	USB-C	Proprietary	N/A	N/A
	FIDN-MOD-REXT-4	Belkin Modular Remote Control Extension Cable 4'	4' ft / 1.2 m	Dual / Single	Other - Modular	N/A	N/A	N/A	N/A
FIDN002MOD-KM-4 FIDN004MOD-KM-4	FIDN1MOD-USB06	Belkin Modular USB Cable for KM 6'	6' ft / 1.8 m	N/A	Host Only - Modular	USB-A	Proprietary	N/A	N/A

Learn More About Belkin's Cybersecurity Solutions



Support

Secure SKVM/SKM Support 800-282-2355

Belkin.com/cybersecurity | Belkinchat.com