



HP Poly Studio A2 White Table Microphone w/ Mounting Plate I/O cables (B22X4AA)

Overview

Bring exceptional clarity to the table

Make audio come alive in every meeting with a simple, scalable, cost-efficient table microphone. Effortlessly expand audio coverage and enable distraction-free communication while seamlessly scaling and deploying.



No distractions. Just clear conversation

Designed with 4 microphone elements, this innovative audio solution helps capture everything important with exceptional clarity, prioritizing the speaker and conversations, so remote participants receive high-quality, natural sound.

Amplify coverage, just like that

Effortlessly extend audio coverage across large spaces with a simple and scalable solution. Seamlessly daisy-chain up to 8 HP Poly Studio A2 Table Microphones[1] - no complex setups required.

Purposefully designed

Elevate the appearance of any conference room with a unique and compact design. Customize your audio setup exactly as you need it with versatile mounting options, unmatched cable management, and color options that complement any room aesthetic.

Built for a better tomorrow

Containing at least 60% recycled plastics[2] and shipped in paper-based packaging[3], this table microphone enables more impactful meetings with less impact on the environment.

Features

Precise audio capture

Don't miss out on anything important. Designed with 4 microphone elements that capture speech without distractions, the multi-directional audio pick up ensures all in-room participants are heard equally.

Scale up with ease

Say goodbye to complicated, cluttered setups with a solution that is built to quickly adapt and scale. Simply daisy chain up to 8 HP Poly Studio A2 Table Microphones for optimal room coverage and easily reconfigure as your needs change.^[1]

Clean setup, always

With versatile installation options, you can streamline or completely hide cable presence, giving you a clean setup that perfectly blends with any room aesthetics.

Unmatched clarity

Deliver consistent high quality, natural sound for your remote participants. Get conversational sound that is crystal-clear with expanded audio pick up enhanced by Poly AI-powered audio innovations.^[4]

Cabling done right

Revamp your collaborative spaces with this elegant audio solution. Get an immaculate setup with discreet cable management for tabletop installation. Neatly position and secure your device with the included magnetic mount.

Elegant and compact design

Instantly revamp the appearance of any conference table with a unique, elegant design and a compact and purposeful form factor available in white. Enjoy a clutter-free audio setup.

[1] HP Poly Studio A2 Table Microphone support varies by product: Poly Studio G62 supports up to 8; Poly Studio V72/X72 up to 4; Poly Studio V52/X52 up to 4; Poly Studio X32 up to 2; Poly Studio V12 supports 1. Microphone pickup range is up to 14 ft (4.3 m) in radius.

[2] Recycled plastic is expressed as a percentage of the total weight plastic. Post-consumer recycled is based on the definition set in the EPEAT standard for computers, IEEE 1680.1-2018 standard.

[3] Percent of paper-based packaging made from sustainably sourced, certified, and recycled fibers.

[4] HP Poly Studio A2 Table Microphone is compatible with currently available next generation Poly Studio G, V, and X Series products; future compatibility may vary by model.

Specifications

Dimensions (W x D x H)	92 x 92 x 24 mm
Dimensions (W x D x H)	3.6 x 3.6 x 9 in
Weight	120 g
Weight	0.25 lb
Ports	3-pin JST output; 4-pin JST input
Package dimensions (W x D x H)	168 x 140 x 67 mm
Package weight	470 g
Special features	Digital transport (up to 18 m between devices); Supports daisy-chain capability of up to 8 A2 table mics; Built on A2B technology
Sustainable impact specifications	Contains at least 60% recycled plastic content; Paper-based packaging
UPC number	(AB1) 199642005495; (ABT) 198828502681; (AC3) 198828502698
Manufacturer Warranty	HP standard one-year limited warranty
What's in the box	HP Poly Studio A2 Table Microphone (White); Mounting plate; JST to Phoenix input cable (6 m); JST to Phoenix daisy-chain output cable (2 m); JST to JST daisy-chain cable (1.8 m); Quick start guide; Safety guide; Warranty card

Additional specifications

Cable length	6 m
Cable length (imperial)	197 ft
Cartons per layer	8
Cartons per pallet	56 (air); 80 (ocean)
Color	White
Compatibility	Poly Studio G62: up to 8 Studio A2 table microphones; Poly Studio X72 and Poly Studio V72: up to 4 Studio A2 table microphones; Poly Studio X52 and Poly Studio V52: up to 4 Studio A2 table microphones; Poly Studio X32: up to 2 Studio A2 table microphones; Poly Studio V12: only 1 Studio A2 table microphone.
Datasheet photo 1	https://prism-pui-int.inc.hp.com/pro/PRO.Crystal.1/DAMHandler/Accessories/Studio_A2_aka_BB8_240703_White_OFF_Catalog_TransparentBG_Front.png
Datasheet photo 2	https://prism-pui-int.inc.hp.com/pro/PRO.Crystal.1/DAMHandler/Accessories/Studio_A2_aka_BB8_240703_White_OFF_Catalog_TransparentBG_FrontLeft.png
Datasheet photo 3	https://prism-pui-int.inc.hp.com/pro/PRO.Crystal.1/DAMHandler/Accessories/Studio_A2_aka_BB8_240703_White_OFF_Catalog_TransparentBG_FrontRight.png
Datasheet photo 5	https://prism-pui-int.inc.hp.com/pro/PRO.Crystal.1/DAMHandler/Accessories/Studio_A2_aka_BB8_240703_White_ON_Catalog_TransparentBG_Front.png
Management Software	Poly Lens ^[1]
Master carton dimension (imperial)	17.12 x 11.41 x 7.48 in
Master carton dimension (metric)	43.5 x 29 x 19 cm
Master carton weight (imperial)	14.1 lb
Master carton weight (metric)	6.4 kg
Microphone pickup range (imperial)	Up to 6 ft radius (Poly Noise Block AI off); Up to 14 ft radius (Poly Noise Block AI on)
Microphone pickup range (metric)	Up to 1.8 m radius (Poly Noise Block AI off); Up to 4.3 m radius (Poly Noise Block AI on)
Microphone type	Four uni-directional cardioid microphone elements
Multiple order quantity	12
Non-Operating Humidity Range	5 to 95%
Non-operating temperature - Celsius	-40 to 70 °C
Non-operating temperature - Fahrenheit	-40 to 158 °F
Operating altitude	3,048 m
Operating altitude	10,000 ft

Operating humidity range	15 to 80%
Operating temperature range	32 to 104 °F
Operating temperature range	0 to 40°C
Operating voltage	2 W
Package dimensions (W x D x H)	6.62 x 5.5 x 2.62 in
Package weight	1.04 lb
Pallet (layers)	7 (air); 10 (ocean)
Pallet dimensions	47.24 x 39.37 x 80.03 in (air); 47.24 x 39.37 x 57.59 in (ocean)
Pallet dimensions (W x D x H)	120 x 100 x 203.3 cm (ocean); 120 x 100 x 146.3 cm (air)
Pallet weight	824.08 lb
Pallet weight	373.8 kg
Products per pallet	672 (air); 960 (ocean)
Products per pallet layer	96
Sensitivity (microphone)	-35 dB (V/Pa) at 1 kHz
Signal-to-noise ratio	>68 dBA
UNSPSC code	52161520

[1] Poly Lens Manages the Audio Bridge through the primary Poly video device.

Services

Communication & Collaboration

★ : Recommended

Poly Support Services

1 Year Partner Poly+ Enterprise New Video Devices Category A	PVIDEOA160
1 Year Partner Poly+ Enterprise Renewal Video Devices Category A	PRVIDEOA160
1 Year Partner Poly+ HP Poly Studio A2 Audio Bridge	UJ9C5PV
1 Year Partner Poly+ HP Poly Studio A2 Table Microphone	UJ9B7PV
1 Year Poly Elite HP Poly Studio A2 Table Microphone	UJ9B9PV
1 Year Poly+ Enterprise New Video Devices Category A	PVIDEOA112
1 Year Poly+ Enterprise Renewal Video Devices Category A	PRVIDEOA112
3 Year Partner Poly+ HP Poly Studio A2 Audio Bridge	UJ9C6PV
3 Year Poly Elite HP Poly Studio A2 Table Microphone	UJ9C0PV
4 Year Poly+ HP Poly Studio A2 Audio Bridge	UL5W3PB
5 Year Poly+ HP Poly Studio A2 Audio Bridge	UL5W5PB
Service reactivation fee HP Poly Studio A2 Table Microphone for product less 1 Year out of support	UJ9C1PV
Service reactivation fee HP Poly Studio A2 Table Microphone for product more 1 Year out of support	UJ9C2PV

Disclaimer — Copyright

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Nov 24, 2025 3:36 PM UTC+0000