Panasonic



An entry-level 4K display that truly "communicates" with high-definition image quality.

TH-65EQ3

6 Models of 4K Displays Featuring High-Definition Image Quality
Combining the optimal performance and functions for use in conference rooms and classrooms.

Key Features

- High 4K Image Quality for Clear and Detailed Visuals
- Flexible Installation to Suit a Variety of Use Cases
- Scalability that enables cooperation with various systems

MEViX

4K PROFESSIONAL

18h Operation

Portrait

USB

4K Media Player

Panasonic

TH-65EQ3

https://eu.connect.panasonic.com/gb/en/professional-displays/th-65eq3

DISPLAY PANEL -> Screen Size	65-inch class (64.5-inch / 1638.9 mm)
DISPLAY PANEL -> Brightness (typ.)	500 cd/m^2
DISPLAY PANEL -> Aspect ratio	16:9
DISPLAY PANEL -> Effective Display Area (W x H)	1428.4 x 803.5 mm (56.23" x 31.63")
DISPLAY PANEL -> Resolution	3840 x 2160
DISPLAY PANEL -> Contrast Ratio (typ.)	1200:1
DISPLAY PANEL -> Response Time (typ.)	8.0 ms (G to G)
DISPLAY PANEL -> Viewing Angle(H / V)	178°/178° (CR > 10)
DISPLAY PANEL -> Panel Surface Treatment	Anti-glare type
DISPLAY PANEL -> Haze	25%
CONNECTION TERMINAL -> HDMI™ IN	HDMI™ Type A Connector x 3 (HDCP 2.2 supported)
CONNECTION TERMINAL -> PC IN	Mini D-sub 15-pin x 1 (Female)
CONNECTION TERMINAL -> SERIAL IN	D-sub 9-pin x 1, RS-232C Compatible
CONNECTION TERMINAL -> AUDIO 1 IN (L / R)	Stereo Mini Jack (M3) x 1
CONNECTION TERMINAL -> AUDIO OUT (L / R)	Pin Jack x 1
CONNECTION TERMINAL -> LAN	RJ45 x 1 10BASE-T/100BASE-TX
CONNECTION TERMINAL -> USB TYPE A	USB Connector Type A x 1 (DC 5 V / 2 A, USB 2.0 is supported)
CONNECTION TERMINAL -> RF In (ANTTENA / CABLE)	F Connector x 1
AUDIO -> Built in Speaker	20 W [10 W+10 W]
ELECTRICAL -> Power Supply	AC 110 - 240 V 50 Hz / 60 Hz
ELECTRICAL -> Power Consumption	TBD
ELECTRICAL -> Power Off Condition	Approx. 0.3 W
ELECTRICAL -> Stand-by Condition	Approx. 0.5 W
MECHANICAL -> Dimension(W)	1463 mm (57.58")
MECHANICAL -> Dimension(H)	838 mm (32.97")
MECHANICAL -> Dimension(D)	69 mm (2.72")
MECHANICAL -> Weight	TBD
MECHANICAL -> Bezel Width(T)	14.9 mm (0.59")
MECHANICAL -> Bezel Width(B)	14.9 mm (0.59")
MECHANICAL -> Bezel Width(L)	14.9 mm (0.59")
MECHANICAL -> Bezel Width(R)	14.9 mm (0.59")
MECHANICAL -> Pitch for Wall-Hanging / Screw / Screw hole depth	VESA Compliant 400 x 400 mm (15.8" x 15.8") / M8 / 20 mm (0.8")
INSTALLATION -> Orientation	Landscape / Portrait
INSTALLATION -> Tilting Angle	0 - 20 degrees forward with landscape setting
INSTALLATION -> Operating Time *5	18h /day
ENVIRONMENT -> Operating Environment(Temperature)	0°C to 40°C (32°F to 104°F) : for up to 0-1400 m (4593 ft) altitude 0°C to 35°C (32°F to 95°F): for between 1400 m (4593 ft) and 2800 m (9186 ft) altitude
ENVIRONMENTAL -> Operating Environment(Humidity) (No condensation)	20% to 80%
Footnote Description	Please contact your sales representative with regard to the tilt angle before installation. 1. Excluding handles