



Aggregation > Aggregation

Aggregation


USW-Aggregation

Datasheet

In The Box

Marketing Images

Installation Guide



^ Overview	
Dimensions	442 x 120 x 43.7 mm (17.4 x 4.7 x 1.7")
Port Layout	
└ 10G SFP+	8 (10G/1G)
Form Factor	Rack mount (1U)
^ Performance	
Switching Capacity	160 Gbps
Total Non-Blocking Throughput	80 Gbps
Forwarding Rate	119 Mpps
Supported VLANs	1,000
MAC Address Table Size	16,000
Packet Buffer Size	1.5 MB
Access Lists	
└ IPv4	128
└ MAC	128
^ Layer 2 Features	
LACP Port Aggregation	✓
STP & RSTP	✓
Advanced IGMP Configuration (Querier, Fast Leave, Router Port)	✓
IGMP Snooping	✓
802.1X Control	✓
MAC-Based ACLs & Device Isolation	✓
DHCP Snooping & Guarding	✓
Egress Rate Limit	✓
Flow Control	✓
Storm Control	✓
Multicast & Broadcast Rate Limiting	✓
MAC Address Blocking	✓
IP-Based ACLs & Network Isolation	✓
MAC-Based Port Restriction	✓
Port Isolation	✓
Port Mirroring	✓
Jumbo Frames	✓
LLDP-MED	✓
Voice VLAN	✓
Loop Protection	✓
Virtual Network Override	✓
^ Hardware	
Max. Power Consumption	36W (Including SFP modules)
Power Method	Universal Input, 100—240V AC, 50/60 Hz
Power Input Method	AC Input
Power Supply	AC/DC, internal, 36W
Supported Voltage Range	100—240V AC
Management	Ethernet AR
Heat Dissipation	102 BTU/hr
Weight	Without mounting brackets: 2.6 kg (5.8 lb) With mounting brackets: 2.7 kg (6 lb)
Enclosure Material	SGCC steel
Mount Material	SGCC steel
Supported Rack Depth	400~1200 mm (15.7~47.2")
LCM Display	1.3" touchscreen
ESD Protection	Air: ± 16kV, contact: ± 12kV
Ambient Operating Temperature	-5 to 40° C (23 to 104° F)
Ambient Operating Humidity	10 to 90% noncondensing
NDAA Compliant	✓
Certifications	CE, FCC, IC, Anatel: 04456-21-08356
^ Software	
Application Requirements	
└ UniFi Network	Version 5.14.12 and later

Company

Blog
Case Studies
Careers
Trust Center
Contact Us
Investors
Compliance

Training

Courses
Calendar
Trainers
Become a Trainer

Buy Now

Ubiquiti Store
Find a Distributor
Become a Distributor

Tools

WIFiman
UISP
UniFi Design Center
UISP Design Center
Downloads

Stay In Touch

Email

Subscribe

