Product Specification

1. Product Features



- 360° omnidirectional pickup with support for multi-device cascade expansion.
- One-Touch Mute Toggle – A gentle touch instantly toggles the microphone on or off.
- Standard IP-Based Protocol – Enables independent, visual control and management of each device via dedicated management software.
- Plug-and-play compatibility with the MAXHUB XBar series.
- Integrated AI audio algorithms, including AGC, AEC, and ambient noise reduction.
- Non-slip design with an optional desktop mounting bracket for enhanced stability and positioning.

2. Microphone

Quantity	8
Pickup Distance	3 m (Optimal Radius)
Type	Silicon Microphone

Frequency Range	100 Hz – 20 kHz
Microphone Unit Sensitivity	−37dBFS
Maximum Number of Devices in a Cascade	4 units

3. I/O ports

Port	Dual RJ45 Ports INPUT(RJ45): 52V / 0.24A OUTPUT(RJ45): 52V / 0.18A
Touch Button	Mute/Unmute the microphone
Indicator Light	Green Light: In meeting – microphone active. Red Light: In meeting – microphone muted. White Light: Standby mode.

4. Physical Specifications

Dimension (D × H)		ϕ112.5 × 30.3 mm
Dimension (package) (L × W × H)	1pcs	208 × 187 × 114 mm
	10pcs	595 × 395 × 250 mm
Net Weight		0.265 kg
Gross Weight	1pcs	0.9 kg
	10pcs	10.5 kg

5. Accessories

7.5 m (24.6 ft) Network Cable	×1

Cable Grommet	×1
Screw Kit	×1
Mounting Bracket	×1

6. Environmental Conditions

Operation Temperature	0℃~40℃
Operation Humidity	10%~90%RH
Storage Temperature	-20℃~60℃
Storage Humidity	10%~90%RH
Altitude	Below 5000 meters

7. Statement

Size and weight vary by configuration and manufacturing process, please refer to the actual product.

The product images are for illustrative purposes only and may slightly differ in appearance, colour, size, etc. from the actual product.

The description, illustrations, etc. in this document may subject to change in accordance with the latest product specification and performance.

Should the above-mentioned change in the document become necessary, the document may be updated without written notice.