



USB 2.0 A/B Cable

- Plug-and-Play for keyboards, mice, modems, printers, and other USB peripherals
- Transfer rate up to 480 Mbps
- Constructed with foil and braid shield to reduce EMI/RFI interference
- Twisted pair construction helps reduce crosstalk thus ensuring high-speed, error-free data transfer
- Available in various colors
- Lifetime Warranty

Specifications: USB 2.0 A/B Cable

Physical Characteristics:

Conductor 1 (x2)

Material:	Stranded Tinned Copper
Size:	28AWG (7/0.12 TC)
Insulation:	HD-PE
OD:	0.90mm
Color:	White/Green (twisted pair)

Conductor 2 (x2)

Material:	Stranded Tinned Copper
Size:	28AWG (7/0.12 TC)
Insulation:	SR-PVC
OD:	1.1mm
Color:	Red, Black

Drain Wire

Material:	Tinned Copper
Size:	28AWG (7/0.12 TC)

Shield 1

Material:	Aluminum Mylar Wrap
-----------	---------------------

Shield 2

Material:	Braided Copper
Coverage:	65%

Jacket

Material:	PVC
OD:	4.7mm

USB 2.0 A Connector

Gender:	Male
Insulation:	White PBT
Contact Material:	Gold Flash
Shell Material:	Nickel Plated

USB 2.0 B Connector

Gender:	Male
Insulation:	White PBT
Contact Material:	Gold Flash
Shell Material:	Nickel Plated

Hood Type

Molded

Approvals:



RoHS Compliant

Warranty:

Lifetime

Package Type:

Polybag



	Black	White	Blue	Green	Orange	Purple	Weight (lbs.)
1m USB 2.0 A/B Cable	28101	13171	—	—	—	—	0.13
2m USB 2.0 A/B Cable	28102	13172	35674	35667	35668	35671	0.19
3m USB 2.0 A/B Cable	28103	13400	35678	35669	35670	35675	0.28
5m USB 2.0 A/B Cable	28104	13401	—	—	—	—	0.30