

M4315-PRO & M4320-PRO

PROFESSIONAL HOME THEATER

Power Management with Interactive Control
and Real Time Monitoring



M4315-PRO and M4320-PRO

DEDICATED 15 AMP
OR 20 AMP
COMPONENTS



M4315-PRO
(15 Amp)

FEATURES:

- Eight Fully Controllable/Programmable Outlets via RS-232C or BlueBOLT™
- Linear Filtration with Four Isolated Outlet Banks
- Two Front Panel Programmable Reboot Buttons
- IP Control with BlueBOLT-CV1 and RS-232C Cards
- Sleek New Design Including Volt/Amp Meter, Outlet Status and Warning LED's
- Removable Rack Ears (Included)

BlueBOLT™

BlueBOLT™ Provides Web Based Remote Power Management to Monitor
and Control Your System - From Anywhere, 24/7.



M4320-PRO
(20 Amp)

www.panamax.com

PANAMAX®

M4315-PRO



M4320-PRO

M4320-PRO - Two 20 Amp Outlets and Six 15 Amp Outlets. 20 Amp detachable AC power cord (10 ft.).



M4315/4320-PRO SPECIFICATIONS

AC Power

Line Voltage.....	120V, 60Hz
Isolated Banks.....	2
Voltage Regulation.....	No
Total Outlets.....	9 outlets
High Current Outlets.....	2 outlets
Total Current Capacity.....	M4315-PRO 15 A (1800W) - M4320-PRO 20 A (2400W)
Voltage Protection Rating (UL 1449 3rd Edition, 3,000A).....	500V
Protection Modes.....	L-N, L-G, N-G
Initial Clamping Level.....	200V Peak, 141V RMS
Energy Dissipation.....	2700 Joules
Peak Impulse Current.....	135,000 Amps
Catastrophic Surge Circuit.....	Yes
Thermal Fusing.....	Yes
Auto-resetting Over-voltage shutoff.....	134 VAC ± 2 VAC
Auto-resetting Under-voltage shutoff.....	100 VAC ± 2 VAC
EMI/RFI Noise Filtration	
Banks 1, 2, 3.....	76db, 5KHz - 250 kHz
Bank 4, High Current Outlets.....	46 db, 250 KHz - 1 Mhz

LAN Protection

Clamping Level.....	60 ± 5V
Compatibility.....	10/100/1000 BASE-T
Jacks.....	RJ-45
Wires Protected.....	8-Wires

Telco Protection

Fuseless/Auto-resetting.....	Yes
Clamping Level.....	260V
Capacitance.....	30pf (approx.)
Suppression Modes.....	Metallic & Longitudinal
Connectors.....	RJ-11
Lines Protected.....	2-Wire, Pins 4 & 5

Universal Coax Protection

HD 1080 i/p Ready.....	Yes
Bidirectional.....	Yes
Shielded.....	Yes
Clamping Level.....	75V
Frequency Range.....	.0MHz - 2.2 GHz
Insertion Loss.....	< 0.5 dB
Connectors.....	Female "F", Gold Plated

Specifications subject to change due to product upgrades and improvements..

WARRANTIES*

\$5,000,000 Connected Equipment Limited Lifetime Warranty • Limited 3 Year Product Warranty

*Refer to actual warranty documentation for full details.


Why roll a truck when you can reboot from anywhere at anytime!

Reduce service calls and lock-ups with BlueBOLT™ technology.

Online Remote Power Management for Home Theater Systems

PROVIDES: Secure, hosted IP system control and monitoring for the M4315-PRO & M4320-PRO.

BlueBOLT™



Model: BlueBOLT-CV1
(Card Included)

WEIGHTS & MEASUREMENTS, QUANTITIES, UPC'S FOR ORDERING & SHIPPING

PRODUCT DIMENSIONS		Weight	
L 12.25" x W 17" x H 1.75"		12 lbs.	
19" wide with rack ears			
SINGLE UNIT CARTON			
Dimensions		Qty.	Weight
L 19.25" x W 21.25" x H 4.25"		1	17 lbs.
MASTER CARTON			
Dimensions		Qty.	Weight
L 20.25" x W 21.25" x H 10.75"		2	37 lbs.
UPC's SINGLE UNIT CARTON		UPC's MASTER CARTON	
M4315-PRO 050616008594		M4315-PRO 50 050616008599	
M4320-PRO 050616008600		M4320-PRO 50 050616008605	

MODELS: M4315-PRO, M4320-PRO



PANAMAX®

1690 Corporate Circle, Petaluma, CA. 94954 • 800-472-5555 • 707-283-5900

Fax 707-283-5901 • www.panamax.com