






In-Ceiling Recessed Motorized Retractable Projection Screens Comparison

Series Name	Evanesce B	Evanesce Tab-Tension B	Evanesce	Evanesce Tab-Tension	Evanesce Plus
Picture					
Applications	Home Cinema, Family Room, Training/Conference Room	Home Cinema, Family Room, Training/Conference Room	Home Cinema, Family Room, Training/Conference Room	Home Cinema, Family Room, Training/Conference Room	Large Training/Conference Room/ Auditoriums
Recommended room size	Small to Medium	Small to Medium	Small, Medium, Large	Small to Medium	Large
Screen Material	MaxWhite™ FG	CineWhite™	MaxWhite™ FG (AcousticPro AUHD)	CineWhite™	MaxWhite™ FG
Gain	1.1	1.1	1.1 (1.0)	1.1	1.1
Viewing Angle	180°	180°	180° (160°)	180°	180°
Size and Aspect Ratio	16:9 - 92"/100"/110"/120" 4:3 - 100"/120"	16:9 - 92"/100", 120"	4:3 - 90", 106" 16:9 - 90", 106", 112", 126" 16:10 - 100", 114", 120" 2.35:1 - 92", 101", 110", 122"	4:3 - 100", 120" 16:9 - 100", 106", 121", 135" 16:10 - 94", 114", 126"	4:3 - 150", 180", 200" 16:9 - 150", 180", 200"
4-sided black masking borders	Yes	Yes	Yes	Yes	Yes
Black Top Border Drop	8"	8"	Up to 24" extra top drop	8"	150"/180" = 12" 200" = 8"
Seamless	Yes	Yes	Yes	Yes	Yes
Fiberglass reinforced	Yes	N/A	Yes	N/A	Yes
Greenguard Certified	Yes	No	Yes	No	Yes
Flame Retardant	Complies with NFPA 701	N/A	Complies with NFPA 701	N/A	Complies with NFPA 701

Control System

Infrared Remote	Yes	Yes	Yes	Yes	Yes
Radio Frequency Remote	Yes	Yes	Yes	Yes	Yes
3-position wall switch	Yes	Yes	Yes	Yes	Yes
IR "eye" extended sensor	Yes	Yes	Yes	Yes	Yes
RJ45 input port	Yes	Yes	Yes	Yes	Yes
Wireless 5-12 volt trigger	Optional	Optional	Optional	Optional	Optional

Design and Installation

Housing Dimensions (WxH) in	3.1" x 3.0"	3.1" x 3.0"	3.9" x 4.6"	3.9" x 4.6"	5.3" x 5.9"
Method of Installation	In-ceiling Recessed - Above and Below access	In-ceiling Recessed - Above and Below access	In-ceiling Recessed - Above and Below access	In-ceiling Recessed - Above and Below access	In-ceiling Recessed - Above access only
Installation kit included	Yes	Yes	Yes	Yes	Yes
Motor Type and speed	Tubular (fast)	Tubular (fast)	Tubular (faster)	Tubular (faster)	Tubular (faster)
Plenum Rated	N/A	N/A	Yes	Yes	N/A

Manufacturer Suggested Retail Pricing (U.S. only)

From	\$762 - \$920	\$926 - \$1,136	\$978 - \$2,115	\$1,475 - \$2,420	\$2,262 - \$3,815
------	---------------	-----------------	-----------------	-------------------	-------------------