



ASSA ABLOY



Product Catalog 2022



Experience a safer
and more open world

660 Cabinet Lock

Electromechanical Cabinet Lock



The strongest
surface mounted,
multi-purpose
locking solution.

The 660 Cabinet Lock provides over 1,000 lbs of static holding force and offers options such as locked state monitoring and a preload release function for maximum flexibility for the most challenging conditions. Strong, convenient and flexible, it is ideal for corporate and government applications including lockers, cabinets and display cases.

Features

Standard Features

- All metal construction
- Adjustable mounting brackets with final lockdown feature
- 6 foot cable lead
- Fail Secure (standard)
- SecuriCare three-year, no-fault, no questions asked warranty

Optional Features

- **Preload** (up to 15 lbs)
- **LBSM** Locked state monitoring
- **LBSM Preload** Locked state monitoring with preload

Accessories

- **KO** Key override



SecuriCare
Warranty



Swinging
Door



Drawers



PoE
Friendly



Preload



ASSA ABLOY

660 Series Cabinet Lock

Specifications

Certifications

- RoHS compliant

Electrical

- 12 or 24 VDC $\pm$ 10%
 - 240 mA at 12 VDC / 120 mA at 24 VDC (continuous duty)
 - 700 mA at 12 VDC / 350 mA at 24 VDC (preload option)
- Monitored contact rating 25 V / 1 A


Holding Force

- Static strength 1,000 lbs
- Dynamic strength over 100 ft-lbs

Environmental

- Indoor use

Dimensions



How to Order

SERIES	VOLTAGE	OPTION (S)
660	– 12V	– LBSM – Preload
660 Cabinet Lock	12V 12 Volt 24V 24 Volt	(blank) No preload, no monitoring
		Preload Up to 15 lbs
		LBSM Locked state monitoring
		LBSM-20PK Locked state monitoring 20 Pack
		LBSM-Preload Locked state monitoring with preload