

CAT5e and CAT6 Feed-Through Patch Panels

Feed all your cables through these CAT5e or CAT6 patch panels.



FEATURES

- » RJ-45 plugs on both sides of the panels.
- » Meet CAT5e or CAT6 specs and provide patching without punching down the wires to the ports.
- » Work with either USOC, T568A, or T568B wiring.
- » Install in relay racks or comm cabinets.
- » The 24-port models include one cable management bar; the 48-port models include two. The bars enable cable management behind the panels.

OVERVIEW

The Feed-Through CAT5e and CAT6 Patch Panels provide patching without punching down the wires to the ports. They make connecting cables easy—just snap your patch cables' connectors into the panel's shielded or unshielded RJ-45 ports. The panels are ideal for use in relay racks or communications cabinets.

Models are available with 24 or 48 shielded or unshielded connectors for CAT5e or CAT6 cable.

What's included

- ♦ (1) patch panel
- ◆ (1) or (2) cable management bars (1 for JPM804A-R2, JPM808A-R2, JPM814A, and JPM818A; 2 for JPM806A-R2, JPM810A-R2, JPM816A, and JPM820A)
- ♦ (4) 10-32 cuphead screws
- ♦ (4) 12-24 cuphead screws
- (1) drain wire (JPM804A-R2, JPM806A-R2, JPM814A, and JPM816A only)
- ♦ (1) user's manual

Item

TECH SPECS

Compliance — TIA/EIA 568B.2 Construction — Steel Shielding — JPM804A-R2, JPM814A: (24) shielded RJ-45: JPM806A-R2, JPM816A: (48) shielded RJ-45 Wiring — Straight-through Connectors — JPM804A-R2, JPM814A: (24) shielded RJ-45 on front. (24) shielded RJ-45 on back: JPM806A-R2, JPM816A: (48) shielded RJ-45 on front. (48) shielded RJ-45 on back: JPM808A-R2, JPM818A: (24) unshielded RJ-45 on front. (24) unshielded RJ-45 on back; JPM810A-R2, JPM820A: (48) unshielded RJ-45 on front; (48) unshielded RJ-45 on back Size — JPM804A-R2, JPM808A-R2, JPM814A, JPM818A: 1.75"H (1U) x 19"W x 4.5"D (4.4 x 48.3 x 11.4 cm); JPM806A-R2, JPM810A-R2, JPM816A, JPM820A: 3.5"H (2U) x 19"W x 4.5"D (8.9 x 48.3 x 11.4 cm)

Weight — JPM804A-R2, JPM814A: 1.6 lb. (0.7 kg);

JPM806A-R2, JPM816A: 2.9 lb. (1.3 kg);

JPM808A-R2, JPM818A: 1.3 lb. (0.6 kg);

JPM810A-R2, JPM820A: 2.3 lb. (1 kg)

CAT5e Feed-Through Patch Panels Shielded 24-Port JPM804A-R2 48-Port JPM806A-R2 Unshielded 24-Port JPM808A-R2 48-Port JPM810A-R2 CAT6 Feed-Through Patch Panels Shielded 24-Port JPM814A 48-Port JPM816A Unshielded 24-Port JPM818A JPM820A 48-Port

Code

You might also need to order cable...

Shielded Twisted-Pair Patch Cable (STP) with
Snagless Boots, T568B, 4-Pair, RJ-45, CAT5e,
Stranded, PVC, 3-ft. (0.9-m)
Unshielded Twisted-Pair Cable
CAT5e 100-MHz Patch Cable, 4-Pair, Straight-Pinned,

PVC, Beige, 3-ft. (0.9-m) **EVNSL05E-0003**

GigaTrue® 550 CAT6 Patch Cable, No Boot, Beige,

3-ft. (0.9-m) **EVNSL625-0003**