


HP Engage 14t FHD No Stand+No VESA Monitor - 14t



*Product image may differ from actual product

HP Engage 14t FHD No Stand+No VESA Monitor - 14t

Product number	8X078AA
UPC number	197498410043
Swivel	No swivel
Port and connectors	1 SuperSpeed USB Type-C® 5Gbps signaling rate (up to 27W USB Power Delivery, Alt Mode DisplayPort™ 1.2) No
Speaker output power	2 x 1.5 W
Touch-enabled	Projected Capacitive technology
Pixels per inch (ppi)	157 ppi
Panel bit depth	8 bit
Vertical viewing angle	178°
Horizontal viewing angle	178°
Bezel	4-sided micro-edge
Tilt	–25 to +90°
Pivot	No pivot
Physical security	None
Height adjustment range	No height adjust
Hardness	3H
Screen treatment	Anti-glare
Integrated privacy filter	No
Flicker-free	No
Low blue light modes	Yes (Eyesafe® and TÜV certified)
Resolution (maximum)	FHD (1920 x 1080 @ 60 Hz)
Speaker output power	2 x 1.5 W
Product material	Yes, USB Type-C®
Management software	HP Display Center
Dimensions (W x D x H)	35 x 20.3 x 17.6 cm
Weight	2.5 kg
Package dimensions (W x D x H)	42.2 x 27.3 x 8.1 cm
Package weight	3.1 kg
Display size	35.56 cm (14")
Aspect ratio	16:9
Display type	VA
Pixel pitch	0.161 mm x 0.161 mm
Response time	25ms on/off
@@Brightness@@	400 nits
Contrast ratio	800:1
Product color	Black;
Resolution (maximum)	FHD (1920 x 1080 @ 60 Hz)
Resolutions supported	640 x 480; 720 x 400; 800 x 600; 1024 x 768; 1280 x 720; 1280 x 800; 1280 x 1024; 1366 x 768; 1440 x 900; 1600 x 900; 1600 x 1200; 1680 x 1050; 1920 x 1080
Display scan frequency (horizontal)	30–80 KHz
Display scan frequency (vertical)	50–76 Hz
Display features	On-screen controls; Touch enabled; Low blue light mode; Dual speakers (2W per channel); Anti-glare
Display User Control Options	Brightness; Information; Management; Power control; Input control; Menu control; Image; Color
Webcam	Yes, 5MP
Operating temperature range	5 to 35°C; 41 to 95°F
Operating humidity range	20 to 80% non-condensing
Ecolabels	EPEAT® registered;
Power consumption description	27 W (maximum), 12 W (typical), 0.5 W (standby)

HP Engage 14t FHD No Stand+No VESA Monitor - 14t

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.
December 2023
--

