


OVERVIEW



1. Power connector	5. Headphone / microphone combo jack (3.5mm)
2. USB 3.2 Gen 1	6. Ethernet (RJ-45)
3. HDMI	7. USB 2.0
4. USB-C 3.2 Gen 1	8. Kensington Nano Security Slot

PERFORMANCE

Processor

Processor Family

12th Generation Intel® Core™ i3 / i5 / i7 Processor

Processor**

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Memory Support	Processor Graphics
Core i3-1215U	6 (2 P-core + 4 E-core)	8	P-core 1.2GHz / E-core 0.9GHz	P-core 4.4GHz / E-core 3.3GHz	10MB	DDR4-3200	Intel UHD Graphics
Core i5-1235U	10 (2 P-core + 8 E-core)	12	P-core 1.3GHz / E-core 0.9GHz	P-core 4.4GHz / E-core 3.3GHz	12MB	DDR4-3200	Intel Iris® Xe Graphics
Core i7-1255U	10 (2 P-core + 8 E-core)	12	P-core 1.7GHz / E-core 1.2GHz	P-core 4.7GHz / E-core 3.5GHz	12MB	DDR4-3200	Intel Iris Xe Graphics

Operating System

Operating System**

- Windows® 11 Pro 64
- Windows 11 Home 64
- Windows 11 DG Windows 10 Pro 64
- No operating system

Graphics

Graphics**^[1]

Graphics	Type	Memory	TGP	Key Features
Intel Iris Xe Graphics	Integrated	Shared	Share CPU TDP	DirectX® 12
Intel UHD Graphics	Integrated	Shared	Share CPU TDP	DirectX 12

Notes:

- Intel Iris Xe Graphics capability requires system to be configured with Intel Core i5 or i7 processor and dual-channel memory. On the system with Intel Core i5 or i7 processor and single-channel memory, Intel Iris Xe Graphics will function as Intel UHD graphics.

Monitor Support

Monitor Support

Supports up to 3 independent displays (native display and 2 external monitors via HDMI® and USB-C)

- HDMI supports up to 3840x2160@30Hz
- USB-C supports up to 4096x2160@60Hz

Chipset

Chipset

Intel SoC (System on Chip) platform

Memory

Max Memory^[1]

- Up to 12GB (4GB soldered + 8GB SO-DIMM) DDR4-3200 offering
- Up to 16GB (8GB soldered + 8GB SO-DIMM) DDR4-3200 offering

Memory Slots

One memory soldered to systemboard, one DDR4 SO-DIMM slot, dual-channel capable

Memory Type

DDR4-3200

Notes:

- The max memory is based on the test results with current Lenovo® memory offerings. The system may support more memory as the technology develops.

Storage

Storage Support^[1]

- Model with 38Wh battery: up to two drives, 1x 2.5" HDD + 1x M.2 SSD
 - 2.5" HDD up to 1TB
 - M.2 2242 SSD up to 512GB
 - M.2 2280 SSD up to 512GB
- Model with 45Wh battery: one drive, 1x M.2 SSD
 - M.2 2242 SSD up to 512GB
 - M.2 2280 SSD up to 512GB

Storage Slot

- Model with 38Wh battery: one 2.5" drive slot + one M.2 slot
 - One 2.5" drive slot, supports 2.5" SATA HDD
 - One M.2 2280 PCIe® Gen 4x4 slot, supports M.2 2242/2280 SSD
- Model with 45Wh battery: one M.2 slot
 - One M.2 2280 PCIe Gen 4x4 slot, supports M.2 2242/2280 SSD

Storage Type^{***}

Disk Type	Interface	RPM	Offering
2.5" SATA HDD	SATA 6Gb/s	5.4K	1TB
M.2 2242 SSD	PCIe NVMe®, PCIe 3.0 x4	-	128GB / 256GB
M.2 2242 SSD	PCIe NVMe, PCIe 4.0 x4	-	256GB / 512GB
M.2 2280 SSD	PCIe NVMe, PCIe 3.0 x4	-	512GB

Notes:

1. The storage capacity supported is based on the test results with current Lenovo storage offerings. The system may support larger storage as the technology develops.

Removable Storage

Optical

None

Card Reader

No card reader

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 1.5W x2, Dolby® Audio™

Microphone

Dual array microphone with noise-cancelling

Camera

HD 720p, with privacy shutter, fixed focus

Battery

Battery^{**}

- Integrated Li-Polymer 38Wh battery, supports Rapid Charge (charge up to 80% in 1hr)
- Integrated Li-Polymer 45Wh battery, supports Rapid Charge (charge up to 80% in 1hr)

Max Battery Life^[1]

- Model with 38Wh battery:
 - MobileMark® 2018: up to 5.8 hr
 - Local video (1080p) playback@150nits: up to 8.2 hr
- Model with 45Wh battery:
 - MobileMark 2018: up to 7.1 hr
 - Local video (1080p) playback@150nits: up to 8.5 hr

Notes:

1. All battery life claims are approximate maximum and based on results using the MobileMark 2014, MobileMark 2018, JEITA 2.0, continuous 1080p video playback (with 150nits brightness and default volume level) or Google Power Load Test (PLT) battery-life benchmark tests. Actual battery life will vary and depends on many factors such as product configuration and usage, software use, wireless functionality, power management settings, and screen brightness. The maximum capacity of the battery will decrease with time and use.

Power Adapter

- Power Adapter**^[1]
- 65W round tip (3-pin) AC adapter, 100-240V, 50-60Hz
 - 65W USB-C (2-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
 - 65W USB-C (3-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz

Notes:

1. AC adapter offerings depend on the country.

DESIGN

Display

Display**^[1]

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle
14.0"	FHD (1920x1080)	None	TN	250 nits	Anti-glare	16:9	500:1	45% NTSC	90°
14.0"	FHD (1920x1080)	None	IPS	300 nits	Anti-glare	16:9	800:1	45% NTSC	170°

Touchscreen

Non-touch

Notes:

1. California Electronic Waste Recycling Fee
In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to <https://www.calrecycle.ca.gov/Electronics/Consumer>

Input Device

- Keyboard
- 6-row, spill-resistant, multimedia Fn keys
- Keyboard Backlight
- Non-backlight
- Touchpad
- Buttonless Mylar® surface multi-touch touchpad, supports Precision TouchPad (PTP), 62 x 104 mm (2.44 x 4.09 inches)

Mechanical^[1]

Dimensions (WxDxH)

324.2 x 215.2 x 19.9 mm (12.76 x 8.47 x 0.78 inches)

Weight

Starting at 1.43 kg (3.15 lbs)

- Case Color**
- Business black
 - Iron grey

- Surface Treatment**
- IMR (in-mold decoration by roller)
 - Texture

Case Material

PC + ABS (top), PC + ABS (bottom)

Notes:

1. The system dimensions and weight vary depending on configurations.

CONNECTIVITY

Network

Onboard Ethernet

Gigabit Ethernet, 1x RJ-45, supports Wake-on-LAN

WLAN + Bluetooth®**^[1]

- 802.11ac 2x2 Wi-Fi® + Bluetooth 5.0, M.2 card
- Wi-Fi 6, 802.11ax 2x2 Wi-Fi + Bluetooth 5.2, M.2 card

Notes:

1. Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitation

Ports^[1]

Standard Ports

- 1x USB 2.0
- 1x USB 3.2 Gen 1
- 1x USB-C 3.2 Gen 1 (support data transfer, Power Delivery 3.0, and DisplayPort™ 1.2)
- 1x HDMI, up to 2.5K/60Hz
- 1x Ethernet (RJ-45)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Power connector

Notes:

1. The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.
USB 2.0: 480 Mbit/s;
USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;
USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;
USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;
Thunderbolt™ 3/4: 40 Gbit/s;
FireWire 400: 400 Mbit/s;
FireWire 800: 800 Mbit/s

SECURITY & PRIVACY

Security

Security Chip

Firmware TPM 2.0 integrated in chipset

Physical Locks

Kensington® Nano Security Slot, 2.5 x 6 mm

Fingerprint Reader

No fingerprint reader

BIOS Security

- Power-on password
- Supervisor password
- Hard disk password
- Self-healing BIOS

Other Security

Camera privacy shutter

SERVICE

Warranty

Base Warranty**^[1]

- 1-year depot service
- 2-year (1-yr battery) depot service
- No base warranty

Notes:

1. More information of warranty policy, please access <https://pcsupport.lenovo.com/warranty>

ENVIRONMENTAL

Operating Environment

Temperature^[1]

- At altitudes up to 2438 m (8,000 ft)
 - Operating: 5°C to 35°C (41°F to 95°F)
 - Storage: 5°C to 43°C (41°F to 109°F)
- At altitudes above 2438 m (8,000 ft)
 - Maximum temperature when operating under the unpressurized condition: 31.3°C (88°F)

Humidity

- Operating: 8% to 95% at wet-bulb temperature 23°C (73°F)
- Storage: 5% to 95% at wet-bulb temperature 27°C (81°F)

Altitude

Maximum altitude (without pressurization): 3048 m (10,000 ft)

Notes:

1. When you charge the battery, its temperature must be no lower than 10°C (50°F).

ACCESSORIES

Bundled Accessories

Bundled Accessories

- Lenovo 15.6" laptop casual toploader, polyester, grey
- None

CERTIFICATIONS

Green Certifications

Green Certifications

- EPEAT™ Silver
- ENERGY STAR® 8.0
- ErP Lot 3
- RoHS compliant

Other Certifications

Other Certifications

TÜV Rheinland® Low Blue Light (Software Solution)

- Feature with ** means that only one offering listed under the feature is configured on selected models.
- Feature with *** means that one or more offerings listed under the feature could be configured on selected models.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.




- The specifications on this page may not be available in all regions, and may be changed or updated without notice.



intel



intel



intel



intel



intel



intel