

OVERVIEW



1. Kensington Security Slot	8. USB-B 3.2 Gen 1
2. Power Connector	9. HDMI 2.0
3. USB 3.2 Gen 1	10. DP 1.4
4. USB 3.2 Gen 1	11. USB 3.2 Gen 1 (BC 1.2)
5. Ethernet (RJ-45)	12. Audio-out (3.5mm)
6. Thunderbolt 4 Out	13. USB 3.2 Gen 1
7. Thunderbolt 4 In	

PERFORMANCE

Panel

Panel

3-side NearEdgeless, In-Plane Switching

Backlight

WLED

Display Size

31.5 inches

Max View Area

WxH: 697.3 x 392.2 mm

Resolution

3840 x 2160

Aspect Ratio

16:9

Pixel Pitch

0.182 x 0.182 mm

Dot / Pixel Per Inch

140 dpi

Brightness

350 nits

Contrast Ratio

- Contrast Ratio: 1000:1
- Dynamic Contrast Ratio: 3M:1

View Angle (H / V)

Horizontal: 178°, Vertical: 178°

Response Time

- Extreme Mode: 4 ms
- Normal Mode: 6 ms

Refresh Rate

60Hz

Color Gamut

- 100% sRGB
- 95% DCI-P3

Color Support

1.07 Billion

Color Depth

10-bit (8+FRC)

Anti-glare

Support

Operating System

Operating System

- Windows® 10 Support
- Windows 11 Support

Multi-Media

Camera

- Optional Modular Camera Support
- ThinkVision® MC 60 monitor webcam (Some models only)

Speakers

Optional Modular Soundbar support (MS30 Monitor Soundbar)

Power Supply

Power Consumption

- 29.5 watts typical, 193.7 watts max
- Sleep / Off mode: <0.5W
- Switch-off Mode: <0.3W
- Energy Star Power On: 32.9W
- Energy Star TEC: 114.9kWh
- Internal Power Supply

Voltage Required

AC 100 to 240 V (50-60Hz)

Special Features

Special Features

- Factory Calibration: Avg. Delta E<2
- Picture In Picture (PIP) / Picture By Picture (PBP) Support
- KVM Switch
- Natural Low Blue Light
- Lenovo® ThinkColour (Lenovo Display Control Center) Support
ThinkColour can only be used with Windows 10 and Windows 11
- Smart Power
The Smart Power function intelligently detects overall power consumption and dynamically manages the power delivery to each device

DESIGN

Mechanical

ThinkCentre® M Series Support

ThinkCentre M Series Tiny Support
For supporting Tiny devices, additional Tiny Clamp Bracket Mounting Kit III (PN: 4XF1K72399) are needed (sold separately).

Bezel Width

- Side: 2mm
- Top / Bottom: 2mm / 18.6mm

Cable Management

Support

Case Color

Raven black

Dimensions (WxDxH)^[1]

Models	Dimensions
Highest Position	714.2 x 234.6 x 599.5 mm (28.12 x 9.24 x 23.60 inches)
Lowest Position	714.2 x 234.6 x 444.5 mm (28.12 x 9.24 x 17.50 inches)
Unpacked Head Only	714.2 x 59.5 x 420.9 mm (28.12 x 2.34 x 16.57 inches)

Packaging Dimensions (WxDxH)

950.0 x 148.0 x 525.0 mm (37.40 x 5.83 x 20.67 inches)

Weight^[2]

Models	Weight
Monitor With Stand	10.1 kg (22.2 lbs)
Monitor Head Only	7.2 kg (15.8 lbs)

Packaging Weight

14.4 kg (31.7 lbs)

Mounting

Supports VESA mount 100mm

Stand

Supports -5° to +23.5° tilt, left & right 45 swivel, -90° to +90° pivot, up to 155mm lift

In the Box

- Monitor with Stand
- 1x Power cable (1.8m)
- 1x Thunderbolt™ 4 cable (1.0m, 40Gbps)
- 1x DP Cable (1.8m)
- 1x HDMI® cable (1.8m)
- 1x USB-A to USB-B Cable (1.8m)
- Factory Calibration Report
- Quick Setup Guide
- Warranty Booklet

Notes:

1. The system dimensions may vary depending on configurations.
2. The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Network

Ethernet

Support 10M / 100M / 1000M

Ports

Rear Ports^[1]

- 1x Thunderbolt 4 In (Up to 100W), USB upstream
- 1x Thunderbolt 4 Out (Up to 27W), USB downstream
- 1x HDMI 2.0
- 1x DisplayPort™ 1.4
- 1x USB-B 3.2 Gen 1, USB upstream
- 4x USB 3.2 Gen 1 (1x BC 1.2), USB downstream
- 1x Ethernet (RJ-45)
- 1x audio-out (3.5mm)

Notes:

1. Listed are maximum capacity of power delivery. Actual capacity of power delivery may vary depending upon devices connected or monitor configuration, and may decline with downstream USB ports connected or higher brightness setting.

SECURITY & PRIVACY

Security

Physical Locks

Kensington® Security Slot™

SERVICE

Warranty

Base Warranty

3-year courier or carry-in service

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

- EPEAT™ Gold Registered^[2]
- ENERGY STAR® Certified
- TCO Certified 9.0
- TCO edge 2.0
- Volatile Organic Compound Certification
- RoHS compliant

Notes:

1. The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.
2. EPEAT is registered where applicable, please see <https://www.epeat.net> for registration status by country.

Other Certifications**Other Certifications**

- Eyesafe® Certified 2.0
- TÜV Rheinland® Eye Comfort Certification
- TÜV Rheinland Low Blue Light (Hardware Solution)

- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

