



ULTRA-SECURE WIRELESS DECT™ HEADSET SYSTEM

BENEFITS

- Exceeds enterprise security expectations – designed to meet the highest level DECT™ Security Step C enhanced with Military level FIPS 140-2 listed features, such as 256-bit AES encryption
- Deploy more headsets with ease—up to 2x better density compared to other DECT™ headsets
- Keep nearby conversations private with a noise-canceling microphone enhanced with Poly Acoustic Fence technology that meets Microsoft Teams Open Office specification
- Crystal clear audio quality with latest DECT™ compression and modulation techniques without impacting user density

SAVI 7300 OFFICE SERIES

A armor up with Savi 7300 Office Series to keep conversations private. The ultra-secure DECT™ wireless headset is the perfect choice for financial, medical, government and contact centers or anywhere sensitive conversations happen. Relax knowing calls are protected—it's designed to meet the highest-level DECT™ security Step C, with military-grade 256-bit AES encryption for maximum security. Combined with Poly Acoustic Fence technology and Microsoft Teams Open Office spec, conversations always stay clear, private and protected. And with up to 2x better density than other DECT™ headsets, interference isn't a thing.

- Up to 2x more density than other DECT™ headsets
- First Poly Microsoft Teams certified DECT™ headset with dedicated Microsoft Teams button
- Meets Microsoft Teams Open Office specification
- Noise-canceling microphone with Poly Acoustic Fence technology
- Up to 580 ft/180 m line-of-sight range

SAVI 7300 OFFICE SERIES



SAVI 7320



SAVI 7310

SPECIFICATIONS

CONNECTS TO

- Desk phone and PC

RECOMMENDED FOR

- Professionals using desk phone and PC communications

WIRELESS

- Technology: DECT™ 6.0 – North America only
- Technology: DECT™ – Outside North America
- Range: Line of sight up to 590 ft/180 m; Typical office environment up to 180 ft/55 m
- Security: Designed to meet Security step C - the highest level from the DECT™ Forum
- Encryption: Military level FIPS 140-2 listed 256-AES encryption
- Authentication: 128-bit AES
- Density: Up to 2x more density than other DECT™ headsets
- Power: Adaptive power control to maximize user density

BATTERY

- Battery Capacity: 500mAh (Savi 7310 and Savi 7320)
- Battery Type: Technician replaceable lithium ion polymer
- Talk time: up to 13 hours
- Charge time: two hours full charge
- Standby time: up to 52 hours

RECEIVE FREQUENCY RESPONSE

- Wideband 100 - 6800Hz
- Multimedia 20Hz - 20kHz

HEARING PROTECTION

- SoundGuard DIGITAL: protects against sound levels above 118dBA; G616 antistartle (during calls) detects and eliminates any large sudden increase in signal level; Time-weighted average prevents average daily noise exposure from exceeding 85dBA¹

MICROPHONE AND TECHNOLOGY

- Noise cancelling with Acoustic Fence Technology
- Meets Microsoft Teams Open Office requirements

HEADSET CONTROLS AND LIGHTS

- Call answer/end, mute volume +/-, power on/off
- Combined call answer/end and Microsoft Teams button, mute volume +/-, power on/off (Microsoft Teams version only)
- In call indicator
- Multiple voice prompts—chosen language configurable via software

HEADSET BASE

- Desk phone, softphone selector buttons
- Microsoft Teams button (Microsoft Teams version only)
- Incoming call ringer (configured via software)

HEADSET WEIGHT

- Savi 7320 Over-the-head (binaural): 160 g /5.64 oz
- Savi 7310 Office Over-the-head (monaural): 120 g /4.23 oz

APPLICATIONS SUPPORTED

- Plantronics Hub application on desktop
- Plantronics Manager Pro (Asset Management and Adoption, Health and Safety Suites—see Supported Devices for full list of supported reports)
- Microsoft Teams Certified²

¹Requires Plantronics Hub software to enable SoundGuard DIGITAL features

² Microsoft Teams versions only

LEARN MORE

To learn more information about Savi 7300 Office Series, visit poly.com