







POLY UNIFIED COMMUNICATIONS PORTFOLIO



With a focus on clear, consistent, and reliable voice collaboration, Poly is dedicated to partnering with enterprises to provide superior audio devices for unified communication deployments. The Poly Unified Communications Portfolio offers a broad range of solutions for diverse working styles, with high-quality audio and world-class technical support.

SPECIFICATIONS

	 VOYAGER 8200 UC	 VOYAGER FOCUS 2 UC SERIES	 VOYAGER FOCUS UC	 VOYAGER 6200 UC	 VOYAGER 5200 OFFICE AND UC SERIES	 VOYAGER 4300 UC SERIES
CONNECTS TO	PC + smartphone/tablet	UC: PC + smartphone/tablet + desk phone (requires Voyager Office base, available as an accessory, sold separately)	PC + smartphone /tablet	PC + smartphone/tablet	UC: PC and smartphone/tablet Office one-way: desk phone + smartphone/tablet Office two-way: desk phone + PC + smartphone/tablet	PC + smartphone/tablet + desk phone (requires Voyager Office base, available as an accessory, sold separately)
RECOMMENDED FOR	Professionals working in a distracting environment at home or in the office	Professionals on calls all day in noisy home or office environments	Professionals on calls all day in noisy home or office environments	Professionals who want flexibility to be ready to take a call and easily remove earbuds when collaborating face-to-face	Mobile professionals who want to make and take calls hands free without noise disruption in and out of the office	Professionals who prefer the freedom of hands free calls all day at home or in the office
WEARING STYLE	Over-the-head (stereo)	Over-the-head (stereo)	Over-the-head (stereo)	Neckband	Over-the-ear	Over-the-head (monaural or stereo)
ROAMING RANGE¹	Up to 98 ft/30 m	UC: Up to 164 ft/50 m With Office Base: Up to 300 ft/91 m	Up to 98 ft/30 m	Up to 98 ft/30 m	UC: up to 98 ft/30 m Office: up to 250 ft/75 m (Line of sight)	UC: Up to 164 ft/50 m With Office Base: Up to 300 ft/91 m
WIRELESS FREQUENCY	Bluetooth® v 5.0	Bluetooth v5.1	Bluetooth v 4.0	Bluetooth v 5.0	Bluetooth v5.0	Bluetooth v 5.2
AUDIO PERFORMANCE	Dual-mode active noise canceling (ANC), mobile wideband compatibility, A2DP, AVRCP, DSP, HFP, HSP	Advanced digital hybrid active noise canceling (ANC), immersive audio, wideband (voice), hi-fi stereo, A2DP, AVRCP, DSP, HFP, HSP	Active noise canceling (ANC), immersive audio, wideband (voice), hi-fi stereo, A2DP, AVRCP, DSP, HFP, HSP	Active noise canceling (ANC), A2DP, DSP	PC and mobile (HFP 1.6) wideband, echo cancellation, A2DP, DSP	Wideband (voice), hi-fi stereo, A2DP, AVRCP, HSP, HFP
HEARING PROTECTION	SoundGuard DIGITAL, G616, TWA	SoundGuard DIGITAL, G616, TWA	SoundGuard DIGITAL, G616, TWA	SoundGuard DIGITAL, G616, TWA	SoundGuard	SoundGuard DIGITAL, G616, TWA
MICROPHONE NOISE REDUCTION	Boomless four-mic performance for dynamic noise reduction	Noise canceling with Acoustic Fence technology. Meets Microsoft Teams Open Office requirements	Three mics offer dynamic noise reduction	Four boomless omnidirectional mics for dynamic noise reduction	Four omni-directional mics with WindSmart technology	Flexible noise canceling boom with dual microphone Acoustic Fence technology
CALL CONTROL	Call answer/ignore/end, mute, volume +/-	Call answer/end, mute, volume +/-	Call answer/ignore/end, mute, volume +/-	Call answer/end, mute, volume +/-	Call answer/ignore/end, mute, volume +/-	Call answer/ignore/end, mute, volume +/-
TALK TIME²	Up to 20 hours talk time; 24 hours listen time	Up to 19 hours (Can also be used as a wired headset)	Up to 12 hours	Up to 9 hours talk time; 16 hours listen time	Up to 7 hours	Up to 24 hours ⁴ , (Can also be used as a wired headset)
MODEL³	Combined standard and Microsoft Teams certified version within the same SKU	Standard and Microsoft Teams Certified versions	Standard and Microsoft Teams Certified versions	Combined standard and Microsoft Teams certified version within the same SKU	Office: Standard and Microsoft Teams Certified versions UC: Combined standard and Microsoft Teams Certified version within the same SKU	Standard and Microsoft Teams Certified versions

1. Features adaptive power, which optimizes for range and talk time to save battery life and maximize density.

2. Performance depends on battery type and may vary by device.

3. For full list of available models, please visit www.poly.com

4. When used with BT700 USB adapter

5. Unlimited talk time with deluxe charging cradle kit, comes standard with Savi 8245 office and UC Series. Available as an accessory with 8240 Office and UC Series.

**SAVI 8200 OFFICE SERIES****SAVI 8200 UC SERIES****SAVI 7300 OFFICE SERIES****BLACKWIRE 8225****BLACKWIRE 5200 SERIES****BLACKWIRE 3300 SERIES**

CONNECTS TO	Desk phone + PC + smartphone/tablet	PC	Desk phone + PC	PC/Desk phone via USB-A/USB-C	PC via USB/USB-C + smartphone/tablet via 3.5 mm	PC via USB/USB-C, connects to mobile devices and tablets via 3.5 mm (BW3315/BW3325) and devices that support USB-C
RECOMMENDED FOR	Professionals using a variety of desk phone, smartphone, and PC communication	Professionals using PC communication	Professionals using desk phone and PC communications	Professionals in a distracting environment looking for a premium corded solution	Professionals who need a plug and play experience	Professionals who need a value plug and play experience
WEARING STYLE	Over-the-head (monaural or stereo), convertible	Over-the-head (monaural or stereo), convertible	Over-the-head (monaural or stereo)	Over-the-head (stereo)	Over-the-head (monaural or stereo)	Over-the-head (monaural or stereo)
ROAMING RANGE¹	Line of sight: 590 ft/180 m Typical office environment: 180 ft/55 m	Line of sight: 590 ft/180 m Typical office environment: 180 ft/55 m	Line of sight: up to 590 ft/180 m Typical office environment: up to 180 ft/55 m	N/A	N/A	N/A
WIRELESS FREQUENCY	DECT™ (Security Certified) Bluetooth v 4.2	DECT™ (Security Certified)	DECT™ (Security Certified) with 256-AES encryption	N/A	N/A	N/A
AUDIO PERFORMANCE	PC wideband, hi-fi stereo, and active noise canceling (ANC) (Savi 8220), A2DP, HFP	PC wideband, hi-fi stereo, and active noise canceling (ANC) (Savi 8220)	PC wideband, hi-fi stereo	Advanced Hybrid active noise canceling (ANC), hi-fi stereo	Immersive audio ((Blackwire 5220), dynamic EQ, wideband voice, hi-fi stereo, echo cancellation	Immersive audio and hi-fi stereo (BW3320/BW3325), Dynamic EQ, wideband voice, echo cancellation
HEARING PROTECTION	SoundGuard DIGITAL, G616, TWA	SoundGuard DIGITAL, G616, TWA	SoundGuard DIGITAL, G616, TWA	SoundGuard DIGITAL, anti-startle, TWA	SoundGuard DIGITAL, G616, TWA	SoundGuard, G616
MICROPHONE NOISE REDUCTION	Noise-canceling with close conversation limiting	Noise-canceling with close conversation limiting	Noise-cancelling with Acoustic Fence Technology. Meets Microsoft Teams Open office requirements	Noise-canceling with Acoustic Fence technology	Noise-canceling	Noise - Canceling
CALL CONTROL	Call answer/end, mute, volume +/-	Call answer/end, mute, volume +/-	Call answer/end, mute volume +/-	PC call answer/end, mute, volume +/-	Call answer/end, mute, volume +/-	Call answer/end, mute, volume +/-
TALK TIME²	Up to 13 hours (Savi 8210 & Savi 8220); Up to 7 hours (Savi 8240); Unlimited (Savi 8245)	Up to 13 hours (Savi 8210 & Savi 8220); Up to 7 hours (Savi 8240) ⁵ ; Unlimited (Savi 8245) ⁵	Up to 13 hours	N/A	N/A	N/A
MODEL*	Standard and Microsoft Teams Certified versions	Standard and Microsoft Teams Certified versions	Standard and Microsoft Teams Certified versions	Standard and Microsoft Teams Certified versions	Combined standard and Microsoft Teams Certified versions within the same SKU	Standard and Microsoft Teams Certified Versions

TECHNOLOGY LEGEND**A2DP**

A Bluetooth profile that allows high-quality audio content to be streamed from one device to another. Listen to streaming media, music, and navigation through your headset.

Active Noise Canceling (ANC)

Technology that reverses surrounding sound waves to cancel low-frequency noise in order to isolate and minimize ambient noise the user can hear.

Acoustic Fence

Technology that uses a noise canceling microphone and an additional omnidirectional microphone to block out background noise.

Adaptive Power

Automatically downshifts to low power when the wireless headset is close to the base to save battery life and maximize density.

Advanced (Digital) Hybrid Active Noise Canceling

Uses four microphones and three ANC settings (off/mid/high) for greater background noise reduction compared to standard ANC.

Close Conversation Limiting

Technology that optimizes your voice, while minimizing nearby background noise.

Digital Signal Processing (DSP)

Mathematical manipulation of an information signal to actively reduce background noise for improved sound quality, including equalization, acoustic echo cancellation, noise reduction, and audio leveling.

Dynamic EQ

Optimizes voice quality on calls and automatically adjusts EQ settings when listening to music or for multimedia playback.

Hi-Fi Stereo

Full-range, dual-channel audio playback capable of frequencies from 20 to more than 20,000 Hz.

Immersive Audio

Specially designed ear cushions and headband reduce background noise for increased clarity and comfort.

Microsoft Teams Certified

For devices to be certified, they need to meet Microsoft's audio requirements to ensure users get the best audio experience, they also must include a dedicated Teams button to instantly bring to the foreground Microsoft Teams for streamlined communications.

Smart Sensor Technology

Built-in sensors deliver automatic functionality, such as answering a call by placing the headset on and automatically transferring calls between smartphone and headset.

SoundGuard

Acoustic limiting for protection against sounds exceeding 118 dBA per Telecom Industry Standards.

SoundGuard DIGITAL

All the benefits of SoundGuard plus anti-startle protection, which detects and eliminates sudden increases in sound, and time-weighted average (TWA) control, which prevents average daily sound exposure from exceeding 85 dBA.

Wideband

Frequency range up to 6,800 Hz. Meets TIA-920 standard for genuine wideband response.