

POLY ROVE 30 DECT™ HANDSET



SPECIFICATIONS

DECT™ FREQUENCY

- 1920-1930 MHz (North America SKU)
- 1880-1900 MHz (EU/ANZ/UK SKU)

HANDSET DISPLAY

- 2.4" TFT color LCD with backlight display (240 x 320 pixels 64K)
- Unicode UTF-8-character support
- Multilingual user interface including US English, UK English, Czech, Danish, Dutch, French, German, Italian, Norwegian, Polish, Portuguese, Russian, Spanish, Swedish, Serbian, Slovenia, and Turkish

AUDIO FEATURES

- Full-duplex conversations, acoustic echo cancellation and background noise suppression
- Frequency response—150 Hz-7 kHz for handset, optional headset and hands-free speakerphone modes

TELEPHONY FEATURES

- Multiple Lines Support for Handsets (20 lines per HS)
- Up to 2 call appearances
- Shared call/bridged line appearance
- Distinctive incoming call treatment/call waiting
- Call timer and call waiting
- Call transfer, hold, pickup, call resume
- Called, calling, connected party information
- Local or network based three-way audio conferencing
- One-touch speed dial, redial
- Missed Call Notifications
- Do Not Disturb (DND) function
- Intercom

- Enhanced Call Park
- Caller ID enable/disable
- Call forward on busy, on no answer, unconditional
- Message Waiting Indicator (MWI)
- 10 Alarm Profiles
- Out of voice band DTMF (RFC 2833)
- Out of voice band DTMF (SIP INFO METHOD)
- Call progress tone generation
- Daylight Savings Time support—worldwide
- Dedicated push to talk (PTT), mute and volume control buttons
- 3 soft keys and 4 programmable line keys
- 20 distinctive ringtones
- OTA (Over the Air) upgrade
- Advanced noise cancellation

HEADSET AND HANDSET COMPATIBILITY

- Dedicated 3.5 mm standard headset port
- Compliant with ADA Section 508 Subpart B1194.23 (all)
- Hearing aid compatible handset for magnetic coupling to hearing aids

HANDSET POWER

- External Universal AC adapter (5V 1A DC)
- One (1) 1100mAh Li-ion battery (rechargeable and replaceable)
- Up to 18 hours talk time
- Up to 300 hours standby time

POLY ROVE 30 DECT™ HANDSET COMES WITH:

- Handset
- Charging Cradle
- 1100mAh Li-ion Battery
- Belt Clip
- Quick Start Card
- Safety Sheet²
- Power Adapter

COMPLIANCE

- USA FCC
- Canada IC RSS
- EEA CE
- AU/NZ RCM
- NZ Telepermit
- Hong Kong HKCA
- Singapore IMDA TS CT-CTS
- ROHS compliant
- ENERGY STAR

SAFETY

- UL 62368-1
- CE Mark
- CAN/CSA C22.2 No 62368-1
- EN 60950-1 and 62368-1
- IEC 60950-1 and 62368-1
- AS/NZS 60950.1 and 62368.1

OPERATING CONDITIONS

- Temperature: -10 to +55°C (+14 to +131°F)
- Relative humidity: 5% to 95%, non-condensing
- Storage Temperature: -40 to +70°C (-40 to +158° F)

WEIGHT

- Handset: 0.168 kg
- Handset charging cradle: 0.065 kg

UNIT BOX DIMENSIONS (W X H X D)/WEIGHT

- Handset box dimensions: 176 x 163 x 44 (mm)
- Handset box weight: 0.365 kg
(with product, accessory, and documents)

MASTER CARTON QUANTITY

- 10

COUNTRY OF ORIGIN

- China

WARRANTY

- 1-year limited warranty

POLY ROVE 40 DECT™ HANDSET



SPECIFICATIONS

DECT™ FREQUENCY

- 1920-1930 MHz (North America SKU)
- 1880-1900 MHz (EU/ANZ/UK SKU)

HANDSET DISPLAY

- 2.4" TFT color LCD with backlight display (240 x 320 pixels 64K)
- Unicode UTF-8-character support
- Multilingual user interface including US English, UK English, Czech, Danish, Dutch, French, German, Italian, Norwegian, Polish, Portuguese, Russian, Spanish, Swedish, Serbian, Slovenia, and Turkish

AUDIO FEATURES

- Full-duplex conversations, acoustic echo cancellation and background noise suppression
- Frequency response—150 Hz-7 kHz for handset, optional headset and hands-free speakerphone modes

TELEPHONY FEATURES

- Multiple Lines Support for Handsets (20 lines per HS)
- Up to 2 call appearances
- Shared call/bridged line appearance
- Distinctive incoming call treatment/call waiting
- Call timer and call waiting
- Call transfer, hold, pickup, call resume
- Called, calling, connected party information
- Local or network based three-way audio conferencing
- One-touch speed dial, redial
- Missed Call Notifications
- Do Not Disturb (DND) function
- Intercom

- Enhanced Call Park
- Caller ID enable/disable
- Call forward on busy, on no answer, unconditional
- Message Waiting Indicator (MWI)
- Vibrate Mode
- Alarm/Emergency Button
- 10 Alarm Profiles
- Built-in Bluetooth for Bluetooth Headset
- Out of voice band DTMF (RFC 2833)
- Out of voice band DTMF (SIP INFO METHOD)
- Call progress tone generation
- Daylight Savings Time support—worldwide
- Dedicated push to talk (PTT), mute and volume control buttons
- 3 soft keys and 4 programmable line keys
- 20 distinctive ringtones
- OTA (Over the Air) upgrade
- Advanced noise cancellation

HEADSET AND HANDSET COMPATIBILITY

- Dedicated 3.5 mm standard headset port
- Bluetooth® headset compatibility
- Compliant with ADA Section 508 Subpart B1194.23 (all)
- Hearing aid compatible handset for magnetic coupling to hearing aids

HANDSET POWER

- External Universal AC adapter (5V 1A DC)
- One (1) 1100mAh Li-ion battery (rechargeable and replaceable)
- Up to 18 hours talk time
- Up to 300 hours standby time

POLY ROVE 40 DECT™ HANDSET COMES WITH:

- Handset
- Charging Cradle
- 1100mAh Li-ion Battery
- Belt Clip
- Quick Start Card
- Safety Sheet*
- Power Adapter

COMPLIANCE

- USA FCC
- Canada IC RSS
- EEA CE
- AU/NZ RCM
- NZ Telepermit
- Hong Kong HKCA
- Singapore IMDA TS CT-CTS
- ROHS compliant
- ENERGY STAR

SAFETY

- UL 62368-1
- CE Mark
- CAN/CSA C22.2 No 62368-1
- EN 60950-1 and 62368-1
- IEC 60950-1 and 62368-1
- AS/NZS 60950.1 and 62368.1

OPERATING CONDITIONS

- Temperature: -10 to +55°C (+14 to +131°F)
- Relative humidity: 5% to 95%, non-condensing
- Storage Temperature: -40 to +70°C (-40 to +158° F)

WEIGHT

- Handset: 0.171 kg
- Handset charging cradle: 0.066 kg

UNIT BOX DIMENSIONS (W X H X D)/WEIGHT

- Handset box dimensions: 176 x 163 x 44 (mm)
- Handset box weight: 0.379 kg
(with product, accessory, and documents)

MASTER CARTON QUANTITY

- 10

COUNTRY OF ORIGIN

- China

WARRANTY

- 1-year limited warranty

¹Most software-enabled features and capabilities must be supported by the server. Please contact your IP PBX/softswitch vendor or service provider for a list of supported features.

²Safety sheets are only included in EU units.

LEARN MORE

For more information on Poly Rove Family, visit poly.com/rove